

Jumpers

for 0.6-0.64 mm wire wrap pins and Ø 0.6-0.7 mm

art. no.	no. of contacts	surface	version	grid			
CAB 4 G ...	2	0.1 µm gold	closed	2.54			
CAB 4 Z ...	2	5.0 µm tin	closed	2.54			
CAB 5 05 G ...	2	0.5 µm gold	closed, hole for probe trip	5.08			
CAB 5 10 G ...	2	1.0 µm gold	closed, hole for probe trip	5.08			
CAB 5 Z ...	2	5.0 µm tin	closed, hole for probe trip	5.08			
CAB 6 05 G ...	2	0.5 µm gold	open, suitable for miniature test probes	2.54			
CAB 6 10 G ...	2	1.0 µm gold	open, suitable for miniature test probes	2.54			
CAB 6 Z ...	2	5.0 µm tin	open, suitable for miniature test probes	2.54			
CAB 9 G ...	2	0.1 µm gold	tag, open	2.54			
<p>please indicate:</p> <p>... colour</p> <p>B = blue</p> <p>G = grey</p> <p>R = red</p> <p>S = black</p>							

Colour "grey" except for CAB 9.

The flexible contacts are shorting two pins. The jumpers can be mounted behind and next to each other.

Male headers 2.54 SMD
 Male headers 2.54 solder
 Male headers 2.54 press-fit
 Male headers 2.00 SMD

→ G -
 → G
 → G
 → G -

Male headers 2.00 solder
 Technical data
 Special male & female headers
 Jump. links 2.00 & 2.54 solder

→ G -
 → G 73 - 76
 → G 18
 → G

A

Jumpers

 for square 0.5 mm and \varnothing 0.4-0.5 mm

B




C

D

E

F

G

art. no.	no. of contacts	surface	version	grid		
CAB 10 G S	2	0.1 μ m gold	open, suitable for miniature test probes	2.00		
CAB 11 G S	2	0.1 μ m gold	open, suitable for miniature test probes	2.00		
CAB 14 G S	2	<0,1 μ m gold	tag, open, suitable for miniature test probes	2.00		

colour:

black

H


 for square 0.3-0.4 mm and \varnothing 0.4-0.5 mm

I

K

L

M

art. no.	no. of contacts	surface	version	grid		
CAB 15 G S	2	<0,1 μ m gold	closed, tag	1.27		

colour:

black

N

G 3
Technical data

 High-prec. male head. 1.27 solder
 High-prec. male headers 1.27 SMD
 Male headers 1.27 solder

 → G 73 - 76
 → G
 → G
 → G -

 Male headers 1.27 SMD
 Male headers 2.00 solder
 Male headers 2.00 SMD

 → G
 → G -
 → G -