



Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 11

Loctite 7061

sds no. : 232327
V004.1

Revision: 23.02.2012
printing date: 15.03.2012

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Loctite 7061

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
Cleaner

1.3. Details of the supplier of the safety data sheet

Henkel Limited
2 Bishop Square Business Park
AL109EY Herfordshire Hatfield

Great Britain

Phone: +44 1606 593933

Fax-no.: +44 1606 863762

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (DPD):

F+ - Extremely flammable

R12 Extremely flammable.

Xi - Irritant

R36 Irritating to eyes.

R66 Repeated exposure may cause skin dryness or cracking.

R67 Vapours may cause drowsiness and dizziness.

2.2. Label elements

Label elements (DPD):

Xi - Irritant



F+ - Extremely flammable

**Risk phrases:**

- R12 Extremely flammable.
- R36 Irritating to eyes.
- R66 Repeated exposure may cause skin dryness or cracking.
- R67 Vapours may cause drowsiness and dizziness.

Safety phrases:

- S16 Keep away from sources of ignition - No smoking.
- S23 Do not breathe vapour.
- S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
- S37 Wear suitable gloves.
- S61 Avoid release to the environment. Refer to special instructions/Safety data sheets.

Additional labeling:

- Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50 °C. Do not pierce or burn, even after use. Do not spray on a naked flame or any incandescent material. Keep away from sources of ignition - No smoking. Keep out of the reach of children
- For consumer use only: S2 Keep out of the reach of children
- S46 If swallowed, seek medical advice immediately and show this container or label.

2.3. Other hazards

- The aerosol container is under pressure. Do not expose to high temperatures.

SECTION 3: Composition/information on ingredients**General chemical description:**

Cleaner

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Acetone 67-64-1	200-662-2	> 50- < 100 %	Flammable liquids 2 H225 Specific target organ toxicity - single exposure 3 H336 Serious eye irritation 2 H319
Ethanol denatured 64-17-5	200-578-6	> 20- < 50 %	No data available.
Propan-2-ol 67-63-0	200-661-7 01-2119457558-25	> 1- < 5 %	Flammable liquids 2 H225 Serious eye irritation 2 H319 Specific target organ toxicity - single exposure 3 H336
Carbon dioxide 124-38-9	204-696-9	> 2,5- < 10 %	No data available.

For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.

Declaration of ingredients according to DPD (EC) No 1999/45:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Acetone 67-64-1	200-662-2	> 50 - < 100 %	R66 Xi - Irritant; R36 F - Highly flammable; R11 R67
Ethanol 64-17-5	200-578-6 01-2119457610-43	> 20 - < 50 %	F - Highly flammable; R11
Propan-2-ol 67-63-0	200-661-7 01-2119457558-25	> 1 - < 5 %	Xi - Irritant; R36 F - Highly flammable; R11 R67
Carbon dioxide 124-38-9	204-696-9	> 2,5 - < 10 %	

For full text of the R-Phrases indicated by codes see section 16 'Other Information'.
Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures**4.1. Description of first aid measures****Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.
Seek medical advice.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.
Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Vapors may cause drowsiness and dizziness.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media:**

Carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

None known

5.2. Special hazards arising from the substance or mixture

None
Oxides of carbon, oxides of nitrogen, irritating organic vapors.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid skin and eye contact.
Ensure adequate ventilation.

6.2. Environmental precautions

Do not let product enter drains.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.
For large spills absorb onto inert absorbent material and place in sealed container for disposal.
Dispose of contaminated material as waste according to Chapter 13.

6.4. Reference to other sections

See advice in chapter 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Use only in well-ventilated areas.
Vapours should be extracted to avoid inhalation.
Keep away from sources of ignition - no smoking.

Hygiene measures:

Good industrial hygiene practices should be observed.
Wash hands before work breaks and after finishing work.
Do not eat, drink or smoke while working.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, well-ventilated place.
Keep away from heat and direct sunlight.

7.3. Specific end use(s)

Cleaner

SECTION 8: Exposure controls/personal protection**8.1. Control parameters**

Valid for
Great Britain

Ingredient	ppm	mg/m ³	Type	Category	Remarks
ACETONE 67-64-1	500	1.210	Time Weighted Average (TWA):		EH40 WEL
ACETONE 67-64-1	1.500	3.620	Short Term Exposure Limit (STEL):		EH40 WEL
ACETONE 67-64-1	500	1.210	Time Weighted Average (TWA):	Indicative	ECLTV
ETHANOL 64-17-5	1.000	1.920	Time Weighted Average (TWA):		EH40 WEL
Carbon dioxide 124-38-9					
CARBON DIOXIDE 124-38-9	15.000	27.400	Short Term Exposure Limit (STEL):		EH40 WEL
CARBON DIOXIDE 124-38-9	5.000	9.150	Time Weighted Average (TWA):		EH40 WEL
CARBON DIOXIDE 124-38-9	5.000	9.000	Time Weighted Average (TWA):	Indicative	ECLTV
PROPAN-2-OL 67-63-0	500	1.250	Short Term Exposure Limit (STEL):		EH40 WEL
PROPAN-2-OL 67-63-0	400	999	Time Weighted Average (TWA):		EH40 WEL

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Ethanol 64-17-5	aqua (freshwater)		0,96 mg/l				
Ethanol 64-17-5	aqua (marine water)		0,79 mg/l				
Ethanol 64-17-5	aqua (intermittent releases)		2,75 mg/l				
Ethanol 64-17-5	sediment (freshwater)				3,6 mg/kg		
Ethanol 64-17-5	soil				0,63 mg/kg		
Ethanol 64-17-5	STP		580 mg/l				
Ethanol 64-17-5	oral				720 mg/kg		
Propan-2-ol 67-63-0	aqua (freshwater)		140,9 mg/l				
Propan-2-ol 67-63-0	aqua (marine water)		140,9 mg/l				
Propan-2-ol 67-63-0	sediment (freshwater)				552 mg/kg		
Propan-2-ol 67-63-0	sediment (marine water)				552 mg/kg		
Propan-2-ol 67-63-0	soil				28 mg/kg		

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Ethanol 64-17-5	worker	inhalation	Acute/short term exposure - local effects		1900 mg/m3	
Ethanol 64-17-5	worker	dermal	Long term exposure - systemic effects		343 mg/kg bw/day	
Ethanol 64-17-5	worker	inhalation	Long term exposure - systemic effects		950 mg/m3	
Ethanol 64-17-5	general population	inhalation	Acute/short term exposure - local effects		950 mg/m3	
Ethanol 64-17-5	general population	dermal	Long term exposure - systemic effects		206 mg/kg bw/day	
Ethanol 64-17-5	general population	inhalation	Long term exposure - systemic effects		114 mg/m3	
Ethanol 64-17-5	general population	oral	Long term exposure - systemic effects		87 mg/kg bw/day	
Propan-2-ol 67-63-0	worker	dermal	Long term exposure - systemic effects		888 mg/kg	
Propan-2-ol 67-63-0	worker	inhalation	Long term exposure - systemic effects		500 mg/m3	
Propan-2-ol 67-63-0	general population	dermal	Long term exposure - systemic effects		319 mg/kg	
Propan-2-ol 67-63-0	general population	inhalation	Long term exposure - systemic effects		89 mg/m3	
Propan-2-ol 67-63-0	general population	oral	Long term exposure - systemic effects		26 mg/kg	

8.2. Exposure controls:

Respiratory protection:

Use only in well-ventilated areas.

Hand protection:

Please note that in practice the working life of chemical resistant gloves may be considerably reduced as a result of many influencing factors (e.g. temperature). Suitable risk assessment should be carried out by the end user. If signs of wear and tear are noticed then the gloves should be replaced.

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Wear protective glasses.

Skin protection:

Wear suitable protective clothing.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	liquid, aerosol colourless
Odor	characteristic
pH	not applicable
Initial boiling point	-78 °C (-108.4 °F)
Flash point	-19 °C (-2.2 °F)
Decomposition temperature	No data available / Not applicable
Vapour pressure	233 mbar
Density (20 °C (68 °F))	0,79 g/cm ³
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Miscible
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	
lower	2,6 % (V)
upper	15 % (V)
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

Ignition temperature 425 °C (797 °F)

SECTION 10: Stability and reactivity

10.1. Reactivity

Reaction with strong acids.
Reacts with strong oxidants.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable

10.5. Incompatible materials

No data available.

10.6. Hazardous decomposition products

Irritating organic vapours.

SECTION 11: Toxicological information

11.1. Information on toxicological effects**General toxicological information:**

The preparation is classified based on the conventional method outlined in Article 6(1)(a) of Directive 1999/45/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Oral toxicity:

This material is considered to have low toxicity if swallowed.

Inhalative toxicity:

May cause headache and dizziness.

Skin irritation:

Solvent may remove essential oils from the skin making it susceptible to attack from other chemicals.

Eye irritation:

Irritating to eyes.

Acute toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Acetone 67-64-1	LD50	5.800 mg/kg	oral	4 h	rat	
	LC50	76 mg/l	inhalation		rat	
	LD50	> 15.688 mg/kg	dermal		rabbit	
Ethanol 64-17-5	LD50	13.700 mg/kg	oral	4 h	rat	
	LC50	124,7 mg/l	inhalation		rat	
	LDLo	20.000 mg/kg	dermal		rabbit	
Propan-2-ol 67-63-0	LD50	5.338 mg/kg	oral	4 h	rat	
	LC50	72,6 mg/l	inhalation		rat	
	LD50	12.870 mg/kg	dermal		rabbit	

Skin corrosion/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Ethanol 64-17-5	not irritating		rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)
Propan-2-ol 67-63-0	slightly irritating	4 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Acetone 67-64-1	irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)
Ethanol 64-17-5	Category II		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)
Propan-2-ol 67-63-0	moderately irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

Hazardous components CAS-No.	Result	Test type	Species	Method
Ethanol 64-17-5	not sensitising	Guinea pig maximisation test	guinea pig	
Propan-2-ol 67-63-0	not sensitising	Buehler test	guinea pig	

Germ cell mutagenicity:

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Acetone 67-64-1	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Ethanol 64-17-5	negative negative	bacterial reverse mutation assay (e.g Ames test) in vitro mammalian chromosome aberration test	with and without without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Propan-2-ol 67-63-0	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		

Repeated dose toxicity

Hazardous components CAS-No.	Result	Route of application	Exposure time / Frequency of treatment	Species	Method
Acetone 67-64-1	NOAEL=2500 ppm	oral: drinking water	13 weeks	rat	
Propan-2-ol 67-63-0	NOAEL=1500	inhalation	13 weeks 6 hours/day, 5 days/week	mouse	

SECTION 12: Ecological information**General ecological information:**

Do not empty into drains / surface water / ground water.

The preparation is classified based on the conventional method outlined in Article 6(1)(a) of Directive 1999/45/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Mobility:

The product evaporates readily.

Persistence and Biodegradability:

No data available.

Bioaccumulative potential:

No data available.

12.1. Toxicity

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Acetone 67-64-1	LC50	8.120 mg/l	Fish	96 h	Pimephales promelas	OECD Guideline 203 (Fish, Acute Toxicity Test)
Acetone 67-64-1	EC50	6.098,4 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Ethanol 64-17-5	LC50	14,2 g/l	Fish	96 h	Pimephales promelas	OECD Guideline 203 (Fish, Acute Toxicity Test)
Ethanol 64-17-5	EC50	9.268 - 14.221 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Ethanol 64-17-5	EC50	> 5.000 mg/l	Algae	7 d	Scenedesmus quadricauda	OECD Guideline 201 (Alga, Growth Inhibition Test)
Propan-2-ol 67-63-0	LC50	9.640 mg/l	Fish	96 h	Pimephales promelas	OECD Guideline 203 (Fish, Acute Toxicity Test)
Propan-2-ol 67-63-0	EC50	13.299 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Propan-2-ol 67-63-0	EC50	> 1.000 mg/l	Algae	96 h	Scenedesmus subspicatus (new name: Desmodesmus subspicatus)	OECD Guideline 201 (Alga, Growth Inhibition Test)

12.2. Persistence and degradability

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
Acetone 67-64-1	readily biodegradable	aerobic	81 - 92 %	EU Method C.4-E (Determination of the "Ready" Biodegradability Closed Bottle Test)
Ethanol 64-17-5	readily biodegradable	aerobic	80 - 85 %	OECD Guideline 301 D (Ready Biodegradability: Closed Bottle Test)
Propan-2-ol 67-63-0	readily biodegradable	aerobic	95 %	OECD Guideline 301 E (Ready biodegradability: Modified OECD Screening Test)

12.3. Bioaccumulative potential / 12.4. Mobility in soil

Hazardous components CAS-No.	LogKow	Bioconcentration factor (BCF)	Exposure time	Species	Temperature	Method
Acetone 67-64-1	0,24					
Ethanol 64-17-5	-0,31					
Propan-2-ol 67-63-0	0,05					OECD Guideline 107 (Partition Coefficient (n-octanol / water), Shake Flask Method)

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product disposal:
Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:
Disposal must be made according to official regulations.

Waste code
14 06 03 Other solvents and solvent mixtures

SECTION 14: Transport information

Road transport ADR:

Class:	2
Packaging group:	
Classification code:	5F
Hazard ident. number:	
UN no.:	1950
Label:	2.1
Technical name:	AEROSOLS
Tunnelcode:	(D)

Railroad transport RID:

Class:	2
Packaging group:	
Classification code:	5F
Hazard ident. number:	23
UN no.:	1950
Label:	2.1
Technical name:	AEROSOLS
Tunnelcode:	

Inland water transport ADN:

Class:	2
Packaging group:	
Classification code:	5F
Hazard ident. number:	
UN no.:	1950
Label:	2.1
Technical name:	AEROSOLS

Marine transport IMDG:

Class:	2.1
Packaging group:	
UN no.:	1950
Label:	2.1
EmS:	F-D ,S-U
Seawater pollutant:	-
Proper shipping name:	AEROSOLS

Air transport IATA:

Class:	2.1
Packaging group:	
Packaging instructions (passenger)	203
Packaging instructions (cargo)	203
UN no.:	1950
Label:	2.1
Proper shipping name:	Aerosols, flammable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content (1999/13/EC)	91,89 %
-----------------------------	---------

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- R11 Highly flammable.
- R36 Irritating to eyes.
- R66 Repeated exposure may cause skin dryness or cracking.
- R67 Vapours may cause drowsiness and dizziness.
- H225 Highly flammable liquid and vapor.
- H319 Causes serious eye irritation.
- H336 May cause drowsiness or dizziness.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

This safety data sheet was prepared in accordance with Council Directive 67/548/EEC and its subsequent amendments, and Commission Directive 1999/45/EC.