



Specifications:

Description	: Sub-miniature cable, 7-2-2C, to Def Stan 61-12 (Part 4)
Conductors	: 0.22 mm ² (7/0.2 mm) annealed copper bunch, meeting the requirements of BS 6360, class 5 : Maximum resistance (completed cable) at 20°C : 92 Ω/km
Insulation	: Type 2 PVC compound to BS 7655 : Minimum radial thickness : 0.25 mm : Minimum core diameter : 1.15 mm : Maximum core diameter : 1.25 mm
Lay up	: 2 cores, red and blue : Polyester tape
Screen	: 0.1 mm tinned annealed copper braid : Minimum filling factor : 0.7
Sheath	: Type 6 PVC compound to BS 7655 : Minimum radial thickness : 0.3 mm : Minimum overall diameter : 3.6 mm : Maximum overall diameter : 4.1 mm
Service Data	: For local interconnection between instruments and electronic equipment : Not suitable for direct connection to mains power supplies : Maximum working voltage : 440 V ac rms : Nominal capacitance : core to core : 105 pF/m : core to screen : 195 pF/m : Maximum (conductor) operating temperature : 70°C : Approximate mass / unit length : 24.5 kg/km

Specifications:

Description	: Sub-miniature cable, 7-2-3C, to Def Stan 61-12 (Part 4)
Conductors	: 0.22 mm ² (7/0.2 mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5 : Maximum resistance (completed cable) at 20°C : 92 Ω/km
Insulation	: Type 2 PVC compound to BS 7655 : Minimum radial thickness : 0.25 mm : Minimum core diameter : 1.15 mm : Maximum core diameter : 1.25 mm
Lay up	: 3 cores, red, blue and green : Polyester tape
Screen	: 0.1 mm tinned annealed copper braid : Minimum filling factor : 0.7
Sheath	: Type 6 PVC compound to BS 7655 : Minimum radial thickness : 0.3 mm : Minimum overall diameter : 3.8 mm : Maximum overall diameter : 4.3 mm
Service Data	: For local interconnection between instruments and electronic equipment : Not suitable for direct connection to mains power supplies : Maximum working voltage : 440 V ac rms : Nominal capacitance : core to core : 100 pF/m : core to screen : 180 pF/m : Maximum (conductor) operating temperature : 70°C : Approximate mass / unit length : 29 kg/km

Specifications:

Description	: Sub-miniature cable, 7-2-4C, to Def Stan 61-12 (Part 4)
Conductors	: 0.22 mm ² (7/0.2 mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5 : Maximum resistance (completed cable) at 20°C : 92 Ω/km
Insulation	: Type 2 PVC compound to BS 7655 : Minimum radial thickness : 0.25 mm : Minimum core diameter : 1.15 mm : Maximum core diameter : 1.25 mm
Lay up	: 4 cores, red, blue, green and yellow : Polyester tape
Screen	: 0.1 mm tinned annealed copper braid : Minimum filling factor : 0.7
Sheath	: Type 6 PVC compound to BS 7655 : Minimum radial thickness : 0.3 mm : Minimum overall diameter : 4.1 mm : Maximum overall diameter : 4.6 mm
Service Data	: For local interconnection between instruments and electronic equipment : Not suitable for direct connection to mains power supplies : Maximum working voltage : 440 V ac rms : Nominal capacitance : core to core : 100 pF/m : core to screen : 170 pF/m : Maximum (conductor) operating temperature : 70°C : Approximate mass / unit length : 32 kg/km

Specifications:

Description	: Sub-miniature cable, 7-2-6C, to Def Stan 61-12 (Part 4)
Conductors	: 0.22 mm ² (7/0.2 mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5 : Maximum resistance (completed cable) at 20°C : 92 Ω/km
Insulation	: Type 2 PVC compound to BS 7655 : Minimum radial thickness : 0.25 mm : Minimum core diameter : 1.15 mm : Maximum core diameter : 1.25 mm
Lay up	: 6 cores, (dummy centre), red, blue, green, yellow, white and black : Polyester tape
Screen	: 0.15 mm tinned annealed copper braid : Minimum filling factor : 0.7
Sheath	: Type 6 PVC compound to BS 7655 : Minimum radial thickness : 0.35 mm : Minimum overall diameter : 5.3 mm : Maximum overall diameter : 5.9 mm
Service Data	: For local interconnection between instruments and electronic equipment : Not suitable for direct connection to mains power supplies : Maximum working voltage : 440 V ac rms : Nominal capacitance : core to core : 100 pF/m : core to screen : 170 pF/m : Maximum (conductor) operating temperature : 70°C : Approximate mass / unit length : 56 kg/km

Specifications:

Description	: Sub-miniature cable, 7-2-8C, to Def Stan 61-12 (Part 4), a.f.a.a
Conductors	: 0.22 mm ² (7/0.2 mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5 : Maximum resistance (completed cable) at 20°C : 92 Ω/km
Insulation	: Type 2 PVC compound to BS 7655 : Minimum radial thickness : 0.25 mm : Minimum core diameter : 1.15 mm : Maximum core diameter : 1.25 mm
Lay up	: 8 cores, (dummy centre), red, blue, green, yellow, white, black, brown and violet : Polyester tape
Screen	: 0.15 mm tinned annealed copper braid : Minimum filling factor : 0.7
Sheath	: Type 6 PVC compound to BS 7655 : Minimum radial thickness : 0.35 mm : Minimum overall diameter : 5.8 mm : Maximum overall diameter : 6.3 mm
Service Data	: For local interconnection between instruments and electronic equipment : Not suitable for direct connection to mains power supplies : Maximum working voltage : 440 V ac rms : Nominal capacitance : core to core : 100 pF/m : core to screen : 170 pF/m : Maximum (conductor) operating temperature : 70°C : Approximate mass / unit length : 56 kg/km

Specifications:

Description	: Sub-miniature cable, 7-2-10C, to Def Stan 61-12 (Part 4), a.f.a.a
Conductors	: 0.22 mm ² (7/0.2 mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5 : Maximum resistance (completed cable) at 20°C : 92 Ω/km
Insulation	: Type 2 PVC compound to BS 7655 : Minimum radial thickness : 0.25 mm : Minimum core diameter : 1.15 mm : Maximum core diameter : 1.25 mm
Lay up	: 10 cores : Centre : Red and blue : Outer : Green, yellow, white, black, brown, violet, orange and pink : Polyester tape
Screen	: 0.15 mm tinned annealed copper braid : Minimum filling factor : 0.7
Sheath	: Type 6 PVC compound to BS 7655 : Minimum radial thickness : 0.35 mm : Minimum overall diameter : 6.3 mm : Maximum overall diameter : 6.9 mm
Service Data	: For local interconnection between instruments and electronic equipment : Not suitable for direct connection to mains power supplies : Maximum working voltage : 440 V ac rms : Nominal capacitance : core to core : 100 pF/m : core to screen : 170 pF/m : Maximum (conductor) operating temperature : 70°C : Approximate mass / unit length : 75 kg/km

Specifications:

Description	: Sub-miniature cable, 7-2-12C, to Def Stan 61-12 (Part 4)
Conductors	: 0.22 mm ² (7/0.2 mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5 : Maximum resistance (completed cable) at 20°C : 92 Ω/km
Insulation	: Type 2 PVC compound to BS 7655 : Minimum radial thickness : 0.25 mm : Minimum core diameter : 1.15 mm : Maximum core diameter : 1.25 mm
Lay up	: 12 cores : Centre : Red, blue and green : Outer : Yellow, white, black, brown, violet, orange, pink, turquoise and grey : Polyester tape
Screen	: 0.15 mm tinned annealed copper braid : Minimum filling factor : 0.7
Sheath	: Type 6 PVC compound to BS 7655 : Minimum radial thickness : 0.35 mm : Minimum overall diameter : 6.6 mm : Maximum overall diameter : 7.2 mm
Service Data	: For local interconnection between instruments and electronic equipment : Not suitable for direct connection to mains power supplies : Maximum working voltage : 440 V ac rms : Nominal capacitance : core to core : 100 pF/m : core to screen : 170 pF/m : Maximum (conductor) operating temperature : 70°C : Approximate mass / unit length : 84 kg/km

Specifications:

Description	: Sub-miniature cable, 7-2-15C, to Def Stan 61-12 (Part 4), a.f.a.a
Conductors	: 0.22 mm ² (7/0.2 mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5 : Maximum resistance (completed cable) at 20°C : 92 Ω/km
Insulation	: Type 2 PVC compound to BS 7655 : Minimum radial thickness : 0.25 mm : Minimum core diameter : 1.15 mm : Maximum core diameter : 1.25 mm
Lay up	: 15 cores : Centre : Red, blue, green : Outer : White, black, brown, violet, orange, pink, turquoise, grey, red / blue, green / red and yellow / red : Polyester tape
Screen	: 0.15 mm tinned annealed copper braid : Minimum filling factor : 0.7
Sheath	: Type 6 PVC compound to BS 7655 : Minimum radial thickness : 0.45 mm : Minimum overall diameter : 7.4 mm : Maximum overall diameter : 8 mm
Service Data	: For local interconnection between instruments and electronic equipment : Not suitable for direct connection to mains power supplies : Maximum working voltage : 440 V ac rms : Nominal capacitance : core to core : 100 pF/m : core to screen : 170 pF/m : Maximum (conductor) operating temperature : 70°C : Approximate mass / unit length : 102 kg/km

Specifications:

Description	: Sub-miniature cable, 7-2-18C, to Def Stan 61-12 (Part 4)
Conductors	: 0.22 mm ² (7/0.2 mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5 : Maximum resistance (completed cable) at 20°C : 92 Ω/km
Insulation	: Type 2 PVC compound to BS 7655 : Minimum radial thickness : 0.25 mm : Minimum core diameter : 1.15 mm : Maximum core diameter : 1.25 mm
Lay up	: 18 cores (dummy centre) : (1 st layer) : Red, blue, green, yellow, white and black : (2 nd layer) : Brown, violet, orange, pink, turquoise, grey, red / blue, green / red, yellow / red, white / red, red / black and red / brown : Polyester tape
Screen	: 0.15 mm tinned annealed copper braid : Minimum filling factor : 0.7
Sheath	: Type 6 PVC compound to BS 7655 : Minimum radial thickness : 0.45 mm : Minimum overall diameter : 7.9 mm : Maximum overall diameter : 8.5 mm
Service Data	: For local interconnection between instruments and electronic equipment : Not suitable for direct connection to mains power supplies : Maximum working voltage : 440 V ac rms : Nominal capacitance : core to core : 100 pF/m : core to screen : 170 pF/m : Maximum (conductor) operating temperature : 70°C : Approximate mass / unit length : 116 kg/km

Specifications:

Description	: Sub-miniature cable, 7-2-20C, to Def Stan 61-12 (Part 4), a.f.a.a
Conductors	: 0.22 mm ² (7/0.2 mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5 : Maximum resistance (completed cable) at 20°C : 92 Ω/km
Insulation	: Type 2 PVC compound to BS 7655 : Minimum radial thickness : 0.25 mm : Minimum core diameter : 1.15 mm : Maximum core diameter : 1.25 mm
Lay up	: 20 cores (dummy centre) : Centre : Red : (1 st layer) : Blue, green, yellow, white and black : (2 nd layer) : Violet, orange, pink, turquoise, grey, red / blue, green / red, yellow / red, white / red, red / black, red / brown, yellow / blue and white / blue : Polyester tape
Screen	: 0.15 mm tinned annealed copper braid : Minimum filling factor : 0.7
Sheath	: Type 6 PVC compound to BS 7655 : Minimum radial thickness : 0.45 mm : Minimum overall diameter : 8.3 mm : Maximum overall diameter : 8.9 mm
Service Data	: For local interconnection between instruments and electronic equipment : Not suitable for direct connection to mains power supplies : Maximum working voltage : 440 V ac rms : Nominal capacitance : core to core : 100 pF/m : core to screen : 170 pF/m : Maximum (conductor) operating temperature : 70°C : Approximate mass / unit length : 126 kg/km

Specifications:

Description	: Sub-miniature cable, 7-2-25C, to Def Stan 61-12 (Part 4)
Conductors	: 0.22 mm ² (7/0.2 mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5 : Maximum resistance (completed cable) at 20°C : 92 Ω/km
Insulation	: Type 2 PVC compound to BS 7655 : Minimum radial thickness : 0.25 mm : Minimum core diameter : 1.15 mm : Maximum core diameter : 1.25 mm
Lay up	: 25 cores : 1 st layer : Red, blue and green : 2 nd layer : Yellow, white, black, brown, violet, orange, pink and turquoise : 3 rd layer : Grey, red / blue, green / red, yellow / red, white / red, red / black, red / brown, yellow / blue, white / blue, blue / black, orange / blue, yellow / green, white / green and orange / green : Polyester tape
Screen	: 0.15 mm tinned annealed copper braid : Minimum filling factor : 0.7
Sheath	: Type 6 PVC compound to BS 7655 : Minimum radial thickness : 0.45 mm : Minimum overall diameter : 9.2 mm : Maximum overall diameter : 9.8 mm
Service Data	: For local interconnection between instruments and electronic equipment : Not suitable for direct connection to mains power supplies : Maximum working voltage : 440 V ac rms : Nominal capacitance : core to core : 90 pF/m : core to screen : 160 pF/m : Maximum (conductor) operating temperature : 70°C : Approximate mass / unit length : 152 kg/km

Specifications:

Description	: Sub-miniature cable, 7-2-36C, to Def Stan 61-12 (Part 4)
Conductors	: 0.22 mm ² (7/0.2 mm) tinned annealed copper bunch, meeting the requirements of BS 6360, class 5 : Maximum resistance (completed cable) at 20°C : 92 Ω/km
Insulation	: Type 2 PVC compound to BS 7655 : Minimum radial thickness : 0.25 mm : Minimum core diameter : 1.15 mm : Maximum core diameter : 1.25 mm
Lay up	: 36 cores (dummy centre) : 1 st layer : Red, blue, green, yellow, white and black : 2 nd layer : Brown, violet, orange, pink, turquoise, grey, red / blue, green / red, yellow / red, white / red, red / black and red / brown : 3 rd layer : Yellow / blue, white / blue, blue / black, orange / blue, green / blue, grey / blue, yellow / green, white / green, green / black, orange / green, grey / green, yellow / brown, white / brown, brown / black, grey / brown, yellow / violet, violet / black and white / violet : Polyester tape
Screen	: 0.15 mm tinned annealed copper braid : Minimum filling factor : 0.7
Sheath	: Type 6 PVC compound to BS 7655 : Minimum radial thickness : 0.5 mm : Minimum overall diameter : 10.4 mm : Maximum overall diameter : 11.2 mm
Service Data	: For local interconnection between instruments and electronic equipment : Not suitable for direct connection to mains power supplies : Maximum working voltage : 440 V ac rms : Nominal capacitance : core to core : 90 pF/m : : core to screen : 160 pF/m : Maximum (conductor) operating temperature : 70°C : Approximate mass / unit length : 202 kg/km

Part Number Table

Description	Part Number
Cable, DEF 7-2-2C, 2Core, 25 m	7000510
Cable, DEF 7-2-2C, 2Core, 100 m	7000514
Cable, DEF 7-2-3C, 3Core, 25 m	7000529
Cable, DEF 7-2-3C, 3Core, 100 m	7000534
Cable, DEF 7-2-4C, 4Core, 25 m	7000513
Cable, DEF 7-2-4C, 4Core, 100 m	7000516
Cable, DEF 7-2-4C, 4Core, 500 m	7-2-4 SCREENED
Cable, DEF 7-2-6C, 6Core, 25 m	7000532
Cable, DEF 7-2-6C, 6Core, 100 m	7000536
Cable, DEF 7-2-8C, 8Core, 25 m	7000545
Cable, DEF 7-2-8C, 8Core, 100 m	7000549
Cable, DEF 7-2-10C, 10Core, 25 m	860201 25M
Cable, DEF 7-2-10C, 10Core, 100 m	860201 100M
Cable, DEF 7-2-12C, 12Core, 25 m	7000560
Cable, DEF 7-2-12C, 12Core, 100 m	860004 100M
Cable, DEF 7-2-15C, 15Core, 25 m	7001249
Cable, DEF 7-2-15C, 15Core, 100 m	700125
Cable, DEF 7-2-18C, 18Core, 25 m	7001263
Cable, DEF 7-2-18C, 18Core, 100 m	7001264
Cable, DEF 7-2-20C, 20Core, 25 m	MC7220C-25M RI-BLK
Cable, DEF 7-2-20C, 20Core, 100 m	MC7220C-100M RI-BLK
Cable, DEF 7-2-25C, 25Core, 25 m	MC7225C-25M RI-BLK
Cable, DEF 7-2-25C, 25Core, 100 m	860006 100M
Cable, DEF 7-2-36C, 36Core, 25 m	860007 25M
Cable, DEF 7-2-36C, 36Core, 100 m	860007 100M

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2011.