

---

Item no.: 280-107  
Product description: 2-conductor earth terminal block

---



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm <sup>2</sup> ]	0.08 - 2.5 mm <sup>2</sup>
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP®CONNECTION
Weight	8.169 g
Color	green-yellow
Wiring type	Side-entry
No. of connection Points	2
No. of potentials	1
Height	30.5 mm
Height	1.2 in
Width	5 mm
Width	0.197 in
Depth	45 mm
Depth	1.77 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35





Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
280-107	ABS	05-HG476175/3-PDA			2,5
280-107	BV	07436/C0	800	24	2,5
280-107	CCA	NL5855			2,5
280-107	CSA	154112-1536071			28-12
280-107	DNV	E-10423	800	24	2,5
280-107	GL	17295-00HH			2,5
280-107	KEMA	2082859.07			2,5
280-107	KR	HMB05880-EL001	800	26	2,5
280-107	LR	91/20112(E6)	800	24	2,5
280-107	PRS	TE/1718/880590/08			2,5
280-107	RMR	11130002	800	24	2,5
280-107	UR	E45172			28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected