

---

Item no.: 284-601  
Product description: 2-conductor through terminal block

---



Produkt kann von Bild abweichen / product may differ

Packing unit 25 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm <sup>2</sup> ]	0.2 - 10 mm <sup>2</sup>
Cross section [AWG]	24 - 8 AWG
Connection method	CAGE CLAMP®CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	57 A
Weight	19.1 g
Color	grey
Wiring type	Front-entry
No. of connection Points	2
No. of potentials	1
Height	33.5 mm
Height	1.32 in
Width	10 mm
Width	0.394 in
Depth	69 mm
Depth	2.72 in

Strip length from	12 mm
Strip length to	13 mm
Strip length	0.49 in
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
284-601	ABS	05-HG476175/3-PDA	800	57	10
284-601	BV	07436/C0			0,2-10
284-601	CCA	NL5918	800	57	10
284-601	CSA	154112-1536073	600	40	24-8
284-601	DNV	E-10423	800	57	10
284-601	GL	17295-00HH	800	57	10
284-601	KEMA	2085859.13	800	57	10
284-601	KR	HMB05880-EL001	800	63	10
284-601	LR	91/20112(E6)	800	57	10
284-601	PRS	TE/1718/880590/08	800	57	10
284-601	RMR	11130002	800	57	10
284-601	UR	E45172	600	50	24-8

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected