


---

Item no.: 280-580  
Product description: SENSOR TERMINAL BLOCK for 4-conductor sensors

---



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm <sup>2</sup> ]	0.08 - 2.5 mm <sup>2</sup>
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	400 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	20 A
Weight	15 g
Color	gray
Wiring type	Angled Type
No. of connection Points	6
No. of potentials	4
Height	63.5 mm
Height	2.5 in
Width	5 mm
Width	0.197 in
Depth	90.5 mm
Depth	3.56 in

Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
280-580	CCA	NL6351	400	20	0,08-2,5
280-580	CSA	154112-1536071	300	15	28-12
280-580	KEMA	2113617.01	400	20	0,08-2,5
280-580	UR	E45172	300	15	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected