
Item no.: 283-107
Product description: 2-CONDUCTOR GROUND TERMINAL BLOCK



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.2 - 16 mm ²
Cross section [AWG]	24 - 6 AWG
Connection method	CAGE CLAMP [®] CONNECTION
Weight	42.004 g
Color	green-yellow
Wiring type	Side-entry
No. of connection Points	2
No. of potentials	1
Height	45.5 mm
Height	1.79 in
Width	12 mm
Width	0.472 in
Depth	58 mm
Depth	2.28 in
Strip length from	16 mm
Strip length to	17 mm
Strip length	0.65 in
Mounting	TS 35

Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
283-107	ABS	05-HG476175/3-PDA			16
283-107	BV	07436/C0			0,2-16
283-107	CCA	NL5917			
283-107	CSA	154112-1536072			24-6
283-107	DNV	E-10423	800	76	16
283-107	GL	17295-00HH			16
283-107	KEMA	2082859.12			
283-107	KR	HMB05880-EL001	800	85	16
283-107	LR	91/20112(E6)	800	76	16
283-107	PRS	TE/1718/880590/08			
283-107	RMR	11130002	800	76	16
283-107	UR	E45172			24-6

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected