

ESK 300 / ESK 300C  
EnOcean Starter Kit



## Important Notes

This information describes the type of component and shall not be considered as assured characteristics. No responsibility is assumed for possible omissions or inaccuracies. Circuitry and specifications are subject to change without notice. For the latest product specifications, refer to the EnOcean website: <http://www.enocean.com>.

As far as patents or other rights of third parties are concerned, liability is only assumed for modules, not for the described applications, processes and circuits. EnOcean does not assume responsibility for use of modules described and limits its liability to the replacement of modules determined to be defective due to workmanship. Devices or systems containing RF components must meet the essential requirements of the local legal authorities. The modules must not be used in any relation with equipment that supports, directly or indirectly, human health or life or with applications that can result in danger for people, animals or real value. Components of the modules are considered and should be disposed of as hazardous waste. Local government regulations are to be observed.

Packing: Please use the recycling operators known to you. By agreement we will take packing material back if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or that we are not obliged to accept, we shall have to invoice you for any costs incurred.

**This evaluation kit and its components are intended for use for evaluation, demonstration or engineering development purposes only.** It is not considered to be a finished end product fit for consumer use. Persons handling this developer kit must have electronics expertise and observe good engineering practice standards. As such, the goods being provided are not intended to be complete in terms of required design, marketing, and/or manufacturing related protective considerations, including product safety and environmental measures typically found in end products that incorporate such electronic components or circuit board. EnOcean does not reliable consequences for any HW or SW changes/modifications of the developer board done by the developer.

**Important notice for users in Japan:** This developer kit is not certified as confirming to technical regulations of radio law of Japan. If you use this kit in Japan, you are required by Radio Law of Japan to follow the instructions below with respect to this product: Use this product in a shielded room or any other test facility as defined in the notification #173 issued by Ministry of Internal Affairs and Communications on March 28, 2006, based on sub-section 1.1 of article 6 of the "Rule for Enforcement of Radio Law of Japan". Use this kit only after you obtained the license of "Test Radio Station" as provided in Radio Law of Japan with respect to this product, or use of this product only after you obtained the technical regulations conformity certification as provided in radio law of Japan with respect to this product. Do not transfer this product, unless you give the same notice above to the transferee. Please note that if you could not follow the instructions above, you will be subject to penalties of Radio Law of Japan.



**Observe precautions! Electrostatic sensitive devices!**

## 1 Introduction

The EnOcean Starter Kit has been designed to demonstrate EnOcean's energy harvesting and ultra low power radio technology. The ESK 300 comes with two electro-mechanical push button generators for switches and a solar powered temperature sensor. Radio telegrams sent by the self-powered sensors are received via USB dongle and visualized via DolphinView Basic PC software.



## 2 ESK 300(C) Content

- User Manual
- USB 300(C): USB Stick Gateway
- PTM 200(C): Self powered push button switch
- Rocker: Rocker push button switch
- STM 330(C): Self-powered temperature sensor
- ECO 200: Push button energy generator
- PTM 330(C): Push button radio module
- Housing example from SEMD<sup>\*)</sup>
- Housing example from BSC GmbH<sup>\*)</sup>


\*) Optional components depend on local distribution.



### 3 First Steps

#### 3.1 DolphinView Basic

- EnOcean DolphinView Basic visualizes and interprets EnOcean radio telegrams. It receives messages via USB 300, shows telegram content and interprets EnOcean Equipment Profiles (EEP).




- Please register for your personal account at: <http://www.enocean.com/registration/>
- Download DolphinView Basic from EnOcean's Software download website: <http://www.enocean.com/en/download/>
- Execute the DolphinView Basic setup program and follow instructions
- Connect the USB 300 to your PC or notebook
- Execute DolphinView Basic and press the connect button

### 3.2 PTM 200 – Push-Button Switch for Building Automation

The push-button radio transmitter module enables the implementation of wireless remote controls without batteries. Key applications are wall-mounted flat rocker switches with 1 or 2 rockers, as well as handheld remote controls with up to 4 single push-buttons.

- Radio telegrams will be received via USB 300 and shown by DolphinView Basic
- Press rocker to send switch telegram -> PTM 200 will be shown in node list
- Select node and press "Set Profile" button to interpret Equipment Profile
- Press rocker on I-side (marking on PTM 200) to send "switch on telegram"
- Press rocker on O-side (marking on PTM 200) to send "switch off telegram"
- Release rocker to send switch telegram "Energy Bow: release"


The screenshot shows the DolphinView Basic software interface. On the left, the 'Node List' pane shows a workspace with one node selected, ID: 001F0685, Device: 2685. On the right, the 'EEP View' pane shows the 'EnOcean Equipment Profile' for this node. The profile includes fields for RORG (DfS: RPS Telegram), PLINC (DfD: Rocker Switch, 2 Rocker), and TYPE (DfD: Light and blind Control - Application Style 1). Below the profile, the 'Data Telegram Interpretation' section is expanded, showing the following configuration:

- 1) Rocker 1st action: Button AI: "Switch light on" or "Dim light down" or "Move blind closed"
- Energy Bow: pressed
- Rocker 2nd action: Button AI: "Switch light on" or "Dim light down" or "Move blind closed"
- 2nd Action: No 2nd action
- Number of buttons pressed simultaneously (other bit combinations are not valid): no button
- Energy Bow: released

### 3.3 ECO 200 & PTM 330 – Push Button Generator & Radio Module

The ECO 200 is an energy converter for linear motion. It can be used to power the PTM 330 radio module. The energy output at every actuation is sufficient to transmit 3 sub-telegrams with a free field range of 300m. Possible applications are miniaturized switches and sensors in building technology and industrial automation.


- Radio telegrams will be received via USB 300 and shown by DolphinView Basic
- Press spring to send telegram -> PTM 330 will be shown in the node list
- Select node and press "Set Profile" button to interpret Equipment Profile
- Press spring to send telegram "Energy Bow: pressed"
- Pull spring to send telegram "Energy Bow: release"



### 3.4 STM 330 – Self-powered Temperature Sensor

The STM330 is a solar powered module that is optimised for wireless, maintenance-free temperature sensors and room operating panels. It can be extended with a plug'n play humidity sensor.

- Radio telegrams will be received via USB 300 and shown by DolphinView Basic
- Turn the STM 300 with solar cell faced up to get light, indoor light will be sufficient
- Configure\*) DolphinView Basic with EnOcean Equipment Profile with following values and press "Set Profile" button:
  - RORG: 0x0A5 4BS Telegram
  - FUNC: 0x02 Temperature Sensor
  - TYPE: 0x05 Temperature Sensor Range 0°C to +40°C
- Press the STM 330 button to send sensor telegram
- The STM 330 sends temperature values every ~1.000s (during darkness for ~100h)




\*) OEM manufacturer can enable EnOcean automatic learn procedure by configuring sensor type and manufacturer ID of STM 330. Developers can do this by using EDK 300 and EDK 31x.

## 4 Push Button Switch Examples (Optional)

Depending on your locality the ESK 300 will be delivered with housing examples for PTM 330 and the ECO 200. This demonstrates how EnOcean's energy harvesting and ultra low power radio technology can be implemented within various environments.


### Switch frame from the company SEMD

- Clip ECO 200 into SEMD plastic frame
- Clip PTM 330 on top of ECO 200
- Push tongue to send telegrams
- If you are interested in developing switches with SEMD please call: +49 9302 9899990



### Switch housing from company BSC GmbH

- Clip PTM 330 and antenna into upper part
- Clip ECO 200 with spring inside the gap of the arm into bottom part
- Put four spacers into the corner of ECO 200 and close housing with screws
- Push arm to send a telegram
- If you are interested in developing switches with BSC GmbH please call: +49 6452 91400



## 5 References

- USB 300: [http://www.enocean.com/en/enocean\\_modules/usb-300-oem/](http://www.enocean.com/en/enocean_modules/usb-300-oem/)
- USB 300C: [http://www.enocean.com/en/enocean\\_modules\\_315mhz/usb-300c-oem/](http://www.enocean.com/en/enocean_modules_315mhz/usb-300c-oem/)
- PTM 200: [http://www.enocean.com/en/enocean\\_modules/ptm-200/](http://www.enocean.com/en/enocean_modules/ptm-200/)
- PTM 200C: [http://www.enocean.com/en/enocean\\_modules\\_315mhz/ptm-200c/](http://www.enocean.com/en/enocean_modules_315mhz/ptm-200c/)
- STM 330: [http://www.enocean.com/en/enocean\\_modules/stm-330/](http://www.enocean.com/en/enocean_modules/stm-330/)
- STM 330C: [http://www.enocean.com/en/enocean\\_modules\\_315mhz/stm-330c/](http://www.enocean.com/en/enocean_modules_315mhz/stm-330c/)
- ECO 200: [http://www.enocean.com/en/enocean\\_modules/eco-200/](http://www.enocean.com/en/enocean_modules/eco-200/)
- PTM 330: [http://www.enocean.com/en/enocean\\_modules/ptm330/](http://www.enocean.com/en/enocean_modules/ptm330/)
- PTM 330C: [http://www.enocean.com/en/enocean\\_modules\\_315mhz/ptm330c/](http://www.enocean.com/en/enocean_modules_315mhz/ptm330c/)
- SEMD frame: Call +49 9302 9899990
- BSC housing: Call +49 6452 91400

Software can be found at: [www.enocean.com/download](http://www.enocean.com/download)

Additional information: <http://www.enocean.com/knowledge-base/>

Technical support: [support@enocean.com](mailto:support@enocean.com)

For developing hardware and software with EnOcean technology  
we recommend using our developer kits:

[http://www.enocean.com/de/enocean\\_module/edk-300/](http://www.enocean.com/de/enocean_module/edk-300/)

## 6 Content

### 868MHz Version

	User Manual	
	USB 300	USB Gateway
	PTM 200	Self powered push button switch
	Rocker	Rocker for push button switch
	STM 330	Self-powered temperature sensor
	ECO 200	Push button energy generator
	PTM 330	Radio module for push button
	SEMD Example Housing	
	BSC GmbH Example Housing	

### 315MHz Version

	User Manual	
	USB 300C	USB Gateway
	PTM 200C	Self powered push button switch
	Rocker	Rocker for push button switch
	STM 330C	Self-powered temperature sensor
	ECO 200	Push button energy generator
	PTM 330C	Radio module for push button
	SEMD Example Housing	
	BSC GmbH Example Housing	



## ENOCEAN

EnOcean is the originator of patented energy harvesting wireless sensor technology. The company manufactures and markets maintenance-free wireless sensor solutions for use in buildings and industrial installations. EnOcean solutions are based on miniaturized energy converters, ultra-lowpower electronic circuitry and reliable wireless. Combining these elements enables EnOcean and its product partners to offer sensor systems that are fundamental for energy-efficient buildings and innovative industry.

[www.enocean.com](http://www.enocean.com)

## CONTACT

Our value-added distributors provide customers with applications support and technical expertise.

[www.enocean.com/distributor](http://www.enocean.com/distributor)

SET UP ON THE ENOCEAN STANDARD FOR ENERGY HARVESTING WIRELESS SENSOR SOLUTIONS.



[www.enocean.com](http://www.enocean.com)