














1				2				3				4				5																																																																																																																																																																																																			
																CHARACTERISTICS MATERIAL Insulator material : LCP Flammability rating : UL94-V0 Colour : Black Contact pin : Brass (CuZn) Surface of solder tail plating : Tin Plated Flange nut : Brass - M2.5																																																																																																																																																																																																			
																<table><tr><th>Poles</th><th>A</th></tr><tr><td>2</td><td>5.08</td></tr><tr><td>3</td><td>10.16</td></tr><tr><td>4</td><td>15.24</td></tr><tr><td>5</td><td>20.32</td></tr><tr><td>6</td><td>25.40</td></tr><tr><td>7</td><td>30.48</td></tr><tr><td>8</td><td>35.56</td></tr><tr><td>9</td><td>40.64</td></tr><tr><td>10</td><td>45.72</td></tr><tr><td>11</td><td>50.80</td></tr><tr><td>12</td><td>55.88</td></tr></table>								Poles	A	2	5.08	3	10.16	4	15.24	5	20.32	6	25.40	7	30.48	8	35.56	9	40.64	10	45.72	11	50.80	12	55.88																																																																																																																																																																				
Poles	A																																																																																																																																																																																																																		
2	5.08																																																																																																																																																																																																																		
3	10.16																																																																																																																																																																																																																		
4	15.24																																																																																																																																																																																																																		
5	20.32																																																																																																																																																																																																																		
6	25.40																																																																																																																																																																																																																		
7	30.48																																																																																																																																																																																																																		
8	35.56																																																																																																																																																																																																																		
9	40.64																																																																																																																																																																																																																		
10	45.72																																																																																																																																																																																																																		
11	50.80																																																																																																																																																																																																																		
12	55.88																																																																																																																																																																																																																		
								ENVIRONMENTAL Operating temperature : -40°C up to 105°C Compliance : Lead free and RoHS								SOLDERING Solder temperature : Reflow process as per JEDEC J-020D-STD																																																																																																																																																																																																			
								ELECTRICAL Current rating : 10A Working voltage : 300 Vac Dielectric withstanding voltage : 4 kVac/min Contact resistance : 20 mΩ max								STANDARD  Certified : E315414 / Model number 7015																																																																																																																																																																																																			
								MECHANICAL Pitch : 5.08mm								PACKAGING Tape & Reel																																																																																																																																																																																																			
<table><tr><td colspan="4">RoHS Compliant</td><td colspan="4"></td><td colspan="4">PROJECTION:</td><td colspan="4">GENERAL TOLERANCE</td><td colspan="4"></td></tr><tr><td>G</td><td></td><td></td><td></td><td colspan="4"></td><td colspan="4"></td><td colspan="4">.X = +/- 0.2</td><td colspan="4"></td></tr><tr><td>F</td><td></td><td></td><td></td><td colspan="4"></td><td colspan="4"></td><td colspan="4">.XX = +/- 0.15</td><td colspan="4"></td></tr><tr><td>E</td><td></td><td></td><td></td><td colspan="4"></td><td colspan="4"></td><td colspan="4"></td><td colspan="4"></td></tr><tr><td>D</td><td></td><td></td><td></td><td colspan="4"></td><td colspan="4"></td><td colspan="4"></td><td colspan="4"></td></tr><tr><td>C</td><td></td><td></td><td></td><td colspan="4"></td><td colspan="4">APPROVAL: RJ</td><td colspan="4">UNIT: MM</td><td colspan="4">DESCRIPTION: SERIE 7015B - 5.08MM CLOSED HORIZONTAL PCB HEADER -</td><td colspan="4">SIZE</td></tr><tr><td>B</td><td>19-DEC-11</td><td>6917015500xx</td><td>QL</td><td colspan="4"></td><td colspan="4"></td><td colspan="4">SCALE: 2/1</td><td colspan="4">THR TYPE WITH FLANGES</td><td colspan="4"></td></tr><tr><td>A</td><td>14-SEP-11</td><td>PDF</td><td>QL</td><td colspan="4"></td><td colspan="4"></td><td colspan="4">SHEET: 1/2</td><td colspan="4">WERI PART NO: 691 701 550 0xx B</td><td colspan="4">A4</td></tr><tr><td>REV</td><td>DATE</td><td>FILE</td><td>BY</td><td colspan="4"></td><td colspan="4"></td><td colspan="4">DRAW: QUENTIN</td><td colspan="4"></td><td colspan="4"></td></tr></table>																RoHS Compliant								PROJECTION:				GENERAL TOLERANCE								G												.X = +/- 0.2								F												.XX = +/- 0.15								E																				D																				C								APPROVAL: RJ				UNIT: MM				DESCRIPTION: SERIE 7015B - 5.08MM CLOSED HORIZONTAL PCB HEADER -				SIZE				B	19-DEC-11	6917015500xx	QL									SCALE: 2/1				THR TYPE WITH FLANGES								A	14-SEP-11	PDF	QL									SHEET: 1/2				WERI PART NO: 691 701 550 0xx B				A4				REV	DATE	FILE	BY									DRAW: QUENTIN											
RoHS Compliant								PROJECTION:				GENERAL TOLERANCE																																																																																																																																																																																																							
G												.X = +/- 0.2																																																																																																																																																																																																							
F												.XX = +/- 0.15																																																																																																																																																																																																							
E																																																																																																																																																																																																																			
D																																																																																																																																																																																																																			
C								APPROVAL: RJ				UNIT: MM				DESCRIPTION: SERIE 7015B - 5.08MM CLOSED HORIZONTAL PCB HEADER -				SIZE																																																																																																																																																																																															
B	19-DEC-11	6917015500xx	QL									SCALE: 2/1				THR TYPE WITH FLANGES																																																																																																																																																																																																			
A	14-SEP-11	PDF	QL									SHEET: 1/2				WERI PART NO: 691 701 550 0xx B				A4																																																																																																																																																																																															
REV	DATE	FILE	BY									DRAW: QUENTIN																																																																																																																																																																																																							

1				2		3		4		5		A																																																																																																																
						1. 10 sprocket hole pitch cumulative tolerance ± 0.20 2.Carrier camber is within 1 mm in 250 mm. 3.Material : Black Conductive Polystyrene Alloy. Transparent anti-static PET 4.All dimensions meet EIA-481-C requirements. 5.Thickness : 0.50 ± 0.05 mm. 6.Component load per 13" reel : 250 pcs.																																																																																																																						
										<table><tr><th rowspan="2">Poles</th><th rowspan="2">A</th><th colspan="4">Dimension</th><th rowspan="2">Reel / carton</th><th rowspan="2">Carton dimensions (cm)</th><th rowspan="2">Quantity / Carton</th></tr><tr><th>W1(mm)</th><th>W2(mm)</th><th>W3(mm)</th><th>W4(mm)</th></tr><tr><td>2</td><td>5.08</td><td>36.4</td><td>32</td><td>32</td><td>28.4</td><td>10</td><td>33.5 x 33.5 x 40</td><td>2500</td></tr><tr><td>3</td><td>10.16</td><td>60.4</td><td>56</td><td>56</td><td>52.4</td><td>6</td><td>33.5 x 33.5 x 40</td><td>1500</td></tr><tr><td>4</td><td>15.24</td><td>60.4</td><td>56</td><td>56</td><td>52.4</td><td>6</td><td>33.5 x 33.5 x 40</td><td>1500</td></tr><tr><td>5</td><td>20.32</td><td>60.4</td><td>56</td><td>56</td><td>52.4</td><td>6</td><td>33.5 x 33.5 x 40</td><td>1500</td></tr><tr><td>6</td><td>25.40</td><td>60.4</td><td>56</td><td>56</td><td>52.4</td><td>6</td><td>33.5 x 33.5 x 40</td><td>1500</td></tr><tr><td>7</td><td>30.48</td><td>92.4</td><td>88</td><td>88</td><td>84.4</td><td>4</td><td>33.5 x 33.5 x 40</td><td>1000</td></tr><tr><td>8</td><td>35.56</td><td>92.4</td><td>88</td><td>88</td><td>84.4</td><td>4</td><td>33.5 x 33.5 x 40</td><td>1000</td></tr><tr><td>9</td><td>40.64</td><td>92.4</td><td>88</td><td>88</td><td>84.4</td><td>4</td><td>33.5 x 33.5 x 40</td><td>1000</td></tr><tr><td>10</td><td>45.72</td><td>92.4</td><td>88</td><td>88</td><td>84.4</td><td>4</td><td>33.5 x 33.5 x 40</td><td>1000</td></tr><tr><td>11</td><td>50.80</td><td>92.4</td><td>88</td><td>88</td><td>84.4</td><td>4</td><td>33.5 x 33.5 x 40</td><td>1000</td></tr><tr><td>12</td><td>55.88</td><td>92.4</td><td>88</td><td>88</td><td>84.4</td><td>4</td><td>33.5 x 33.5 x 40</td><td>1000</td></tr></table>		Poles	A	Dimension				Reel / carton	Carton dimensions (cm)	Quantity / Carton	W1(mm)	W2(mm)	W3(mm)	W4(mm)	2	5.08	36.4	32	32	28.4	10	33.5 x 33.5 x 40	2500	3	10.16	60.4	56	56	52.4	6	33.5 x 33.5 x 40	1500	4	15.24	60.4	56	56	52.4	6	33.5 x 33.5 x 40	1500	5	20.32	60.4	56	56	52.4	6	33.5 x 33.5 x 40	1500	6	25.40	60.4	56	56	52.4	6	33.5 x 33.5 x 40	1500	7	30.48	92.4	88	88	84.4	4	33.5 x 33.5 x 40	1000	8	35.56	92.4	88	88	84.4	4	33.5 x 33.5 x 40	1000	9	40.64	92.4	88	88	84.4	4	33.5 x 33.5 x 40	1000	10	45.72	92.4	88	88	84.4	4	33.5 x 33.5 x 40	1000	11	50.80	92.4	88	88	84.4	4	33.5 x 33.5 x 40	1000	12	55.88	92.4	88	88	84.4	4	33.5 x 33.5 x 40	1000	B
Poles	A	Dimension				Reel / carton	Carton dimensions (cm)	Quantity / Carton																																																																																																																				
		W1(mm)	W2(mm)	W3(mm)	W4(mm)																																																																																																																							
2	5.08	36.4	32	32	28.4	10	33.5 x 33.5 x 40	2500																																																																																																																				
3	10.16	60.4	56	56	52.4	6	33.5 x 33.5 x 40	1500																																																																																																																				
4	15.24	60.4	56	56	52.4	6	33.5 x 33.5 x 40	1500																																																																																																																				
5	20.32	60.4	56	56	52.4	6	33.5 x 33.5 x 40	1500																																																																																																																				
6	25.40	60.4	56	56	52.4	6	33.5 x 33.5 x 40	1500																																																																																																																				
7	30.48	92.4	88	88	84.4	4	33.5 x 33.5 x 40	1000																																																																																																																				
8	35.56	92.4	88	88	84.4	4	33.5 x 33.5 x 40	1000																																																																																																																				
9	40.64	92.4	88	88	84.4	4	33.5 x 33.5 x 40	1000																																																																																																																				
10	45.72	92.4	88	88	84.4	4	33.5 x 33.5 x 40	1000																																																																																																																				
11	50.80	92.4	88	88	84.4	4	33.5 x 33.5 x 40	1000																																																																																																																				
12	55.88	92.4	88	88	84.4	4	33.5 x 33.5 x 40	1000																																																																																																																				
RoHS Compliant				PROJECTION: 		GENERAL TOLERANCE .X = ± 0.2 .XX = ± 0.15				DESCRIPTION: SERIE 7015B - 5.08MM CLOSED HORIZONTAL PCB HEADER - THR TYPE WITH FLANGES WERI PART NO: 691 701 550 0xx B		SIZE A4	C																																																																																																															
G F E D C B A REV DATE FILE BY				APPROVAL: RJ		UNIT: MM SCALE: SHEET: 2/2 DRAW: QUENTIN				D																																																																																																																		