

MG24115Supplementary Protector Multi 9 (C60N) 8A,
1-Pole, 240 Vac, DIN Rail (35mm)

by Schneider Electric

List Price \$101.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.****Technical Characteristics**

General Application	Overcurrent protection within appliances or electrical equipment where branch circuit breaker protection is provided or not required
Ampere Rating	8A
Width	0.71 Inches (18mm)
Short Circuit Current Rating	10kA@120/240VAC - 5kA@277VAC
For Use With	OEM Panels
Trip Curve	B Curve - Magnetic operates between 3.2 to 4.8 tim
Specific Application	Protection for sensitive equipment (computers, electronic devices etc.)
Marketing Trade Name	Multi 9
Type	C60N
Approvals	UL 1077 Recognized, IEC 60947-2 Rated
Voltage Rating	240VAC
Wire Size	#14 to #4 AWG (Cu)
Mounting Type	DIN Rail (35mm)
Depth	3.00 Inches (76mm)
Circuit Breaker Type	Standard
Weight	3.85 Ounces
Height	3.19 Inches (81mm)
Number of Poles	1-Pole

Shipping and Ordering

Category	00908 - Supplemental Circuit Protectors, 1 Pole: 15 - 63 Amp, 2 Pole: 1 - 63 Amp, 3 Pole: 1 - 63 Amp, 4 Pole: 1 - 63 Amp, Type Multi 9 C60
Discount Schedule	DE2
GTIN	00785901880158
Package Quantity	1
Weight	0.26 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 03/27/2012 09:12:57