

Enhanced FG & Freq. Counter Kit - Senior Technician

● 76-220



FEATURES:

- Convenient Interconnection Kit
- High Quality Components
- Works with All Popular Instruments
- Gold Plated Contacts
- Storage Pouch
- Includes 50Ω Feed-thru Terminator

ENHANCED INTERCONNECTION KIT FOR RF TESTING WITH FUNCTION GENERATORS OR FREQUENCY COUNTERS:

Tenma's enhanced function generator & frequency counter accessory kit, model 76-220, provides users the necessary interconnection cables and adapters to begin using their instrument.


The kit includes 1 each of, 1-meter BNC and 1-meter BNC to IC clips cable assemblies, 2 between-and in-series BNC, N-Type coaxial adapters, 1 BNC to banana plug adapter, and 1 BNC 50Ω feed-thru terminator, just the right accessories for function generator or frequency counter work in education, design, performance verification or calibration.

Model 76-220, Enhanced Function Generator & Frequency Counter Kit is suitable for instruments from Agilent®, B&K Precision®, Rohde & Schwarz®, Tektronix® and many others. Find this and other instrument accessories at our web site www.mcmelectronics.com.

APPLICATIONS:

- R&D Laboratories
- Production Test Stations
- Service & Repair Facilities
- Educational Test Benches

KIT CONTENTS:



Item.	Description	Model	Qty.	Frequency Range	VSWR Max.
1.	BNC Cable Assembly, 100cm (40")	76-556	1	DC - 1 GHz	1.20:1 @ 1 GHz
2.	BNC Cable w/IC Clips, 100cm (40")	76-570	1	DC - 1 GHz	N/A
3.	BNC Tee, female-male-female	76-512	1	DC - 4 GHz	N/A
4.	BNC female to Double Banana Plugs	76-550	1	N/A	N/A
5.	BNC Feed-Thru Terminator, 2W	76-566	1	DC - 1 GHz	1.20:1 @ 1 GHz
6.	BNC female to N Type male	76-540	1	DC - 4 GHz	1.30:1 @ 4 GHz

SPECIFICATIONS:

- Impedance - 50 Ω
- Frequency Range - see table
- VSWR Max - see table
- Working temperature - -20° to $+80^{\circ}$ C
- Connectors: BNC
Body - Brass, Nickel Plated
Dielectric - PTFE & Delrin[®]
Center Contact - Brass, Gold Plated