

D4 WOOD ADHESIVE

Page: 1

Compilation date: 26/5/11

Revision No: 2

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: D4 WOOD ADHESIVE

Product code: D41,05

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.3. Details of the supplier of the safety data sheet

Company name: EVERBUILD BUILDING PRODUCTS LTD

SITE 41, KNOWSTHORPE WAY

CROSS GREEN INDUSTRIAL ESTATE

LEEDS

- WEST YORKSHIRE
- LS9OSW
- ENGLAND
- Tel: 0044 113 240 3456
- Fax: 0044 113 240 0024
- Email: pault@everbuild.co.uk

1.4. Emergency telephone number

Emergency tel: 0044 113 240 3456 (office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CHIP: This product has no classification under CHIP.

Classification under CLP: This product has no classification under CLP.

2.2. Label elements

Label elements under CHIP:

Hazard symbols: No significant hazard.

2.3. Other hazards

PBT: This substance is not identified as a PBT substance.

Section 3: Composition/information on ingredients

3.1. Substances

Chemical identity: D4 WOOD ADHESIVE

D4 WOOD ADHESIVE

Page: 2

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Turn leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

D4 WOOD ADHESIVE

Section 7: Handling and storage

7.1. Precautions for safe handling

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area. Keep container tightly closed. Store in original containers between +5 and +25°C. Storage outside these paramaters will dramatically reduce shelf life and invalidates all product warrenties.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

ALUMINIUM CHLORIDE, ANHYDROUS

Workplace exposure limits:

Respirable dust

State	8 hour TWA:	15 min. STEL:	8 hour TWA:	15 min. STEL:
UK	2mg/m3	-	-	-

8.2. Exposure controls

Respiratory protection: Respiratory protection not required.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Colour: V	Vhi	e

- Odour: Pleasant
- Viscosity: Viscous

Boiling point/range°C: 100

Relative density: 1.03-1.07

pH: 3.5-5

9.2. Other information

Section 10: Stability and reactivity

D4 WOOD ADHESIVE

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat. Protect from frost

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values: Not applicable.

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: Not applicable.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This substance is not identified as a PBT substance.

D4 WOOD ADHESIVE

Page: 5

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal of packaging: Dispose of as normal industrial waste.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product is not classified for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information:	This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.
	* indicates text in the SDS which has changed since the last revision.
Legal disclaimer:	The above information is believed to be correct but does not purport to be all inclusive
	and shall be used only as a guide. This company shall not be held liable for any
	damage resulting from handling or from contact with the above product.