

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000181](#)
Status: **Active**
Overview: [minifit_jr](#)
Description: 4.20mm Pitch Mini-Fit® Crimp Terminal, Female, Phosphor Bronze, Gold (Au), 18-24 AWG, Reel

Documents:

Drawing (PDF)	Packaging Specification PK-5556-001 (PDF)
Product Specification PS-5556-001 (PDF)	Test Summary TS-5556-002 (PDF)
Product Specification PS-5556-002 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	5556
Application	Power
Crimp Quality Equipment	Yes
Overview	minifit_jr
Product Name	Mini-Fit®

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

Electrical


Current - Maximum per Contact	9A
Voltage - Maximum	600V

Material Info

Old Part Number	5556-PBGSP
-----------------	------------

Reference - Drawing Numbers

Packaging Specification	PK-5556-001
Product Specification	PS-5556-001, PS-5556-002
Sales Drawing	SD-5556-GSP*
Test Summary	TS-5556-002



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[5556Series](#)

Mates With

[5558](#) Mini-Fit® Crimp Male Terminals. Mini-Fit Jr.™ Header, Dual Row, [5566](#) , [5569](#)

Use With

[5557](#) Mini-Fit Jr.™ Receptacle Housing, [30067](#) Mini-Fit® TPA, [42474](#) Mini-Fit® BMI Panel Mount, [44516](#) Mini-Fit® BMI Slide and Lock Panel Mount

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
FineAdjust™ Applicator for insulation OD	0639002600

2.50-2.95mm - 18-24
 AWG
 FineAdjust™ 0639002900
 Applicator for
 insulation OD
 1.65-2.05mm - 18-24
 AWG
 FineAdjust™ 0639015600
 Applicator for
 insulation OD
 1.90-2.30mm - 18-24
 AWG
 FineAdjust™ 0639023900
 Applicator for
 insulation OD
 1.40-1.70mm - 18-24
 AWG
 FineAdjust™ 0639024800
 Applicator for
 insulation OD
 2.50-2.95mm
 optimized for 18
 AWG only
 FineAdjust™ 0639024900
 Applicator for
 insulation OD
 2.30-2.60mm - 18-24
 AWG
 T2 Terminator™ 0639102600
 for insulation OD
 2.50-2.95mm - 18-24
 AWG
 T2 Terminator™ 0639115600
 for insulation OD
 1.90-2.30mm - 18-24
 AWG
 T2 Terminator™ 0639123900
 for insulation OD
 1.40-1.70mm - 18-24
 AWG
 T2 Terminator™ 0639124800
 for insulation OD
 2.50-2.95mm
 optimized for 18
 AWG only
 T2 Terminator™ 0639124900
 for insulation OD
 2.30-2.60mm - 18-24
 AWG
 T2 Terminator™ for 0639102900
 insulation OD 1.65
 – 2.05mm – 18 – 24
 AWG
 Hand Crimp Tool for 0638190900
 Mini-Fit™ Jr. Male
 and Female Crimp
 Terminals, 16-24
 AWG
 Extraction Tool 0011030044

Japan

Description	Product #
Applicator for M211A Bench Press, 18-24 AWG, for 5556 and 5558 Crimp Terminal	<u>0570223000</u>

Side-Feed Applicator 0570223200
For Full-Auto
Machine

This document was generated on 02/08/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION