

## High-Efficiency Heavy Duty Tip (#7546-100)

Diameter is 3/16" or .188".

Note: High-Efficiency tips heat up faster and provide more than 20% more soldering time than our standard tips.

High-Efficiency tips reach soldering temperature in less than 10 seconds and reach a tip temperature of approximately 900°F.