

70 mm Illuminated Stackable Beacons

1. Select from one to five stackable light lens units (or up to four light lens units with one audible sounder)
2. Select LED lamp for lens unit (LED lamp color must match color of the lens unit)
3. Select one base unit with cover
4. Select accessories (not required)





Lens Unit Type or Audible Sounder	Voltage	Color	Catalog No.	+	LED Lamp	Catalog No.	+	Base Unit (required)	Catalog No.	+	Accessories (not required)	Catalog No.				
Strobe Light – with Integrated Flash Discharge (must mount in top position)	24 VAC/DC	○ White	XVBC8B7					Base Unit and Cover	XVBC21	+	Side Entry Wiring Adapter with Cable Gland	XVBC14				
		● Orange	XVBC8B5			½ in. NPT Conduit Adapter	XVBC00									
		● Green	XVBC8B3										Support Base	XVBC00		
		● Red	XVBC8B4												80 mm Long Tube	XVBZ02
		● Yellow	XVBC8B8													
		● Blue	XVBC8B6												780 mm Long Tube	XVBZ04
	120 VAC	○ White	XVBC8G7								Bracket for Wall Mounting	XVBC14				
		● Orange	XVBC8G5													
		● Green	XVBC8G3													
		● Red	XVBC8G4													
		● Yellow	XVBC8G8													
		● Blue	XVBC8G6													
Flashing Light (must order LED lamp separately)	24 VAC/DC	○ White	XVBC4B7	○ White	DL1BDB1											
		● Orange	XVBC4B5	● Orange	DL1BDB5											
		● Green	XVBC4B3	● Green	DL1BDB3											
		● Red	XVBC4B4	● Red	DL1BDB4											
		● Yellow	XVBC4B8	● Yellow	DL1BDB8											
		● Blue	XVBC4B6	● Blue	DL1BDB6											
	120 VAC	○ White	XVBC4G7	○ White	DL1BDG1											
		● Orange	XVBC4G5	● Orange	DL1BDG5											
		● Green	XVBC4G3	● Green	DL1BDG3											
		● Red	XVBC4G4	● Red	DL1BDG4											
		● Yellow	XVBC4G8	● Yellow	DL1BDG8											
		● Blue	XVBC4G6	● Blue	DL1BDG6											
Steady Light (must order LED lamp separately)	24 VAC/DC	○ White	XVBC37	○ White	DL1BDB1											
		● Orange	XVBC35	● Orange	DL1BDB5											
		● Green	XVBC33	● Green	DL1BDB3											
		● Red	XVBC34	● Red	DL1BDB4											
		● Yellow	XVBC38	● Yellow	DL1BDB8											
		● Blue	XVBC36	● Blue	DL1BDB6											
	120 VAC	○ White	XVBC37	○ White	DL1BDG1											
		● Orange	XVBC35	● Orange	DL1BDG5											
		● Green	XVBC33	● Green	DL1BDG3											
		● Red	XVBC34	● Red	DL1BDG4											
		● Yellow	XVBC38	● Yellow	DL1BDG8											
		● Blue	XVBC36	● Blue	DL1BDG6											
Audible Sounder (must mount in lowest position)	24 VAC/DC	—	XVBC9B	—	—											
	120 VAC	—	XVBC9M	—	—											

All devices must be the same voltage rating

Simple Selector

50 mm and 70 mm Illuminated Beacons



Selling Points

- Provides 360°, instant communication
- Allows customer assembly using separate parts and common accessories
- Zero-maintenance LED lights protected against short circuits, overvoltage, reverse polarity and electromagnetic interference
- NEMA 1, 4X (indoor), 12 and IP65 rated for indoor use
- UL listed, CSA certified and CE marked

50mm Stackable Tower Lights

1. Select from one to five stackable light lens units (or up to four light lens units with one audible sounder)
2. Select LED lamps for each beacon. LED lamp color must match color of the beacon
3. Select one base unit with cover (required)
4. Select accessories (not required)

Note: All 50 mm light lens units and audible sounders are off-white color (not black color as depicted).



Lens Unit Type or Audible Sounder	Voltage	Color	Catalog No.
Steady Light Lens (must order LED lamp separately)	24 VAC/DC	○ Clear	XVPC37W
		● Orange	XVPC35W
		● Green	XVPC33W
		● Red	XVPC34W
		● Yellow	XVPC38W
		● Blue	XVPC36W
		○ Clear	XVPC37W
	120 VAC	● Orange	XVPC35W
		● Green	XVPC33W
		● Red	XVPC34W
		● Yellow	XVPC38W
		● Blue	XVPC36W
		○ Clear	XVPC37W
		● Orange	XVPC35W
Flashing Light (must order LED lamp separately)	24 VAC/DC	○ Clear	XVPC37W
		● Orange	XVPC35W
		● Green	XVPC33W
		● Red	XVPC34W
		● Yellow	XVPC38W
		● Blue	XVPC36W
		○ Clear	XVPC37W
	120 VAC	● Orange	XVPC35W
		● Green	XVPC33W
		● Red	XVPC34W
		● Yellow	XVPC38W
		● Blue	XVPC36W
		○ Clear	XVPC37W
		● Orange	XVPC35W
Strobe Light with Integrated Flash Discharge	24 VAC/DC	○ White	XVPC6B7W
		● Orange	XVPC6B5W
		● Green	XVPC6B3W
		● Red	XVPC6B4W
		● Yellow	XVPC6B8W
		● Blue	XVPC6B6W
		○ White	XVPC6G7W
	120 VAC	● Orange	XVPC6G5W
		● Green	XVPC6G3W
		● Red	XVPC6G4W
		● Yellow	XVPC6G8W
		● Blue	XVPC6G6W
		○ White	XVPC6B7W
		● Orange	XVPC6B5W
Audible Sounder ten-tone Selections (must mount on top)	24 VAC/DC	75-85 decibels	XVPC09BW
	120 VAC	75-85 decibels	XVPC09GW

LED Lamp	Catalog No.
○ White	DL1BDB1
● Orange	DL1BDB5
● Green	DL1BDB3
● Red	DL1BDB4
● Yellow	DL1BDB8
● Blue	DL1BDB6
○ White	DL1BDG1
● Orange	DL1BDG5
● Green	DL1BDG3
● Red	DL1BDG4
● Yellow	DL1BDG8
● Blue	DL1BDG6
○ White	DL1BKB1
● Orange	DL1BKB5
● Green	DL1BKB3
● Red	DL1BKB4
● Yellow	DL1BKB8
● Blue	DL1BKB6
○ White	DL1BKG1
● Orange	DL1BKG5
● Green	DL1BKG3
● Red	DL1BKG4
● Yellow	DL1BKG8
● Blue	DL1BKG6

Base Unit (Required)	Catalog No.
Base Unit and Cover	XVPC21W

Accessories (not Required)	Catalog No.
Mounting Base and Tube	
112 mm Long Tube	XVBC02W
250 mm Long Tube	XVBC03W
400 mm Long Tube	XVBC04W
Wall Mounting Bracket	XVPC12W
LED Lamp Removal Tool	XVPCX13

All devices must be the same voltage rating

70 mm Illuminated Non-Stackable Beacons

1. Select one non-stackable illuminated beacon
2. Select one LED lamp. LED lamp color must match color of the beacon
3. Select accessories (not required)



Lamp Operation	Voltage	Color	Catalog No.
Steady Beacon (must order LED lamp separately)	24 VAC/DC	○ Clear	XVBL37
		● Orange	XVBL35
		● Green	XVBL33
		● Red	XVBL34
		● Yellow	XVBL38
		● Blue	XVBL36
		○ Clear	XVBL37
	120 VAC	● Orange	XVBL35
		● Green	XVBL33
		● Red	XVBL34
		● Yellow	XVBL38
		● Blue	XVBL36
		○ Clear	XVBL37
		● Orange	XVBL35
Flashing Beacon (must order LED lamp separately)	24 VAC/DC	○ Clear	XVBL4B7
		● Orange	XVBL4B5
		● Green	XVBL4B3
		● Red	XVBL4B4
		● Yellow	XVBL4B8
		● Blue	XVBL4B6
		○ Clear	XVBL4M7
	120 VAC	● Orange	XVBL4M5
		● Green	XVBL4M3
		● Red	XVBL4M4
		● Yellow	XVBL4M4
		● Blue	XVBL4M6
		○ Clear	XVBL4M7
		● Orange	XVBL4M5
Strobe Light Beacon (LED lamp included)	24 VAC/DC	○ Clear	XVBL8B7
		● Orange	XVBL8B5
		● Green	XVBL8B3
		● Red	XVBL8B4
		● Yellow	XVBL8B8
		● Blue	XVBL8B6
		○ Clear	XVBL8M7
	120 VAC	● Orange	XVBL8M5
		● Green	XVBL8M3
		● Red	XVBL8M4
		● Yellow	XVBL8M8
		● Blue	XVBL8M6
		○ Clear	XVBL8M7
		● Orange	XVBL8M5

All devices must be the same voltage rating

LED Lamp	Catalog No.
○ Clear	DL1BDB1
● Orange	DL1BDB5
● Green	DL1BDB3
● Red	DL1BDB4
● Yellow	DL1BDB8
● Blue	DL1BDB6
○ Clear	DL1BDG1
● Orange	DL1BDG5
● Green	DL1BDG3
● Red	DL1BDG4
● Yellow	DL1BDG8
● Blue	DL1BDG6
○ Clear	DL1BDB1
● Orange	DL1BDB5
● Green	DL1BDB3
● Red	DL1BDB4
● Yellow	DL1BDB8
● Blue	DL1BDB6
○ Clear	DL1BDG1
● Orange	DL1BDG5
● Green	DL1BDG3
● Red	DL1BDG4
● Yellow	DL1BDG8
● Blue	DL1BDG6

Adapter for Side Entry Wiring	Catalog No.
Side Entry Wiring Adapter with Cable Gland	XVBC14
1/2 in. NPT Conduit Adapter	XVBC00
Support Base	
80 mm Long Tube	XVBZ02
380 mm Long Tube	XVBZ03
780 mm Long Tube	XVBZ04
Bracket for Wall Mounting	XVPC12W