



# PCB TERMINAL BLOCKS

## 6.35mm Pitch High Power Rising Clamp Terminal

- 2 & 3 pole double interlocking mechanism for increased strength
- Moulded in green UL94-V0 flame retardant PA
- Professional rising clamp terminals
- 0.2-6.0mm<sup>2</sup> (30-10AWG) solid & stranded cable
- Guided pin alignment
- Captive screws
-  approved


CTB04VY




TYPE NO.	POLES	LENGTH
CTB04VY/2	2	12.7mm
CTB04VY/3	3	19.1mm
CTB04VY/4	4	25.4mm
CTB04VY/5	5	31.8mm
CTB04VY/6	6	38.1mm
CTB04VY/7	7	44.5mm
CTB04VY/8	8	50.8mm
CTB04VY/9	9	57.2mm
CTB04VY/10	10	63.5mm
CTB04VY/11	11	69.9mm
CTB04VY/12	12	76.2mm

### SPECIFICATION

Rating	32A/400V UL=24A/300V, VDE&IMQ=32A/450V
Dielectric strength	≥2kV
Impulse withstand voltage	6kV
Working temperature	110°C
Moulding	UL94-V0 flame retardant PA
Pin/terminal	Tinned, nickel plated brass
Clamp	Zinc plated steel
Screw/torque	M3 steel zinc plated, 0.5Nm
Recommended PCB hole size	ø1.1mm



## 9.52mm Pitch High Power Rising Clamp Terminal

- 2 & 3 pole double interlocking mechanism for increased strength
- Moulded in green UL94-V0 flame retardant PA
- Professional rising clamp terminals
- 0.2-6.0mm<sup>2</sup> (30-10AWG) solid & stranded cable
- Guided pin alignment
- Captive screws
-  approved

CTB04VZ



TYPE NO.	POLES	LENGTH
CTB04VZ/2	2	12.7mm
CTB04VZ/3	3	19.1mm
CTB04VZ/4	4	25.4mm
CTB04VZ/5	5	31.8mm
CTB04VZ/6	6	38.1mm
CTB04VZ/7	7	44.5mm
CTB04VZ/8	8	50.8mm
CTB04VZ/9	9	57.2mm
CTB04VZ/10	10	63.5mm
CTB04VZ/11	11	69.9mm
CTB04VZ/12	12	76.2mm

### SPECIFICATION

Rating	32A/630V UL=24A/300V, VDE&IMQ=32A/750V
Dielectric strength	≥2kV
Impulse withstand voltage	6kV
Working temperature	110°C
Moulding	UL94-V0 flame retardant PA
Pin/terminal	Tinned, nickel plated brass
Clamp	Zinc plated steel
Screw/torque	M3 steel zinc plated, 0.5Nm
Recommended PCB hole size	ø1.1mm

