



T50R9M4

Cable Tie, 50 lb. 7.9" Max. Bun. Dia. 1.97", PA66, Natural, 1000/pk

Article Number: 111-04862

Part Number: T50R9M4

Type: T50R




Website Feedback

Base Data

Part No.	T50R9M4
Type	T50R
Color	Natural (NA)
Features	HellermannTyton manufactures a full line of high quality cable ties in a variety of styles, sizes, materials, and colors. HellermannTyton cable ties are engineered and manufactured for maximum performance and quality.
Application	Used to bundle and secure wire and cable.
Application Method	Quick, simple fixing by hand or with HellermannTyton tensioning tools
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Variant	Inside Serrated


Product Dimensions



Min. Tensile Strength	50lbs / 225N
Length (L)	7.9" / 200mm
Width (W)	.18" / 4.6mm
Min. Ø Bundle	.06" / 1.5mm

Max. Ø Bundle 1.97" / 50.0mm

Material and Specifications

Material	Polyamide 6.6 (PA66)
US MILSPEC	MS3367-1-9
CSA Certified	No
Flammability	UL94 V2
Material Specification	HF
Operating Temperature	-40 °C to +85 °C, intermittent +105 °C (for 500 h)
ROHS Conformity	 RoHS
Specification	UL ZODZ2.E64139
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes

Logistic and Packaging

Pkg. Qty.	1000
Carton Qty.	5000
EAN code	4031026274676
UPC	089306089414

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)
7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512