

SAFETY DATA SHEET ULTRASOLVE

1 IDENTIFICATION OF THE MATERIAL AND SUPPLIER

PRODUCT NAME ULTRASOLVE
PRODUCT NO. EULS01L/ 05L/ 25L
APPLICATION Cleaning Product
SUPPLIER H K WENTWORTH PTY LIMITED
 P.O. BOX 339
 BROOKVALE, NSW 2100
 AUSTRALIA
 TEL: 02 9938 1566
 FAX: 02 9938 1467
 GENERAL MANAGER
EMERGENCY TELEPHONE Tel: 029938 1566 between 8.30am and 5.00pm EST

2 HAZARDS IDENTIFICATION

HAZARD ID

Highly flammable.

Vapours may cause drowsiness and dizziness.

Harmful: may cause lung damage if swallowed.

Irritating to eyes and skin.

Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

HAZARD ID 2

The above phrases are the risks associated with the product

STATEMENT OF HAZARDOUS NATURE

HAZARDOUS SUBSTANCE (According to criteria of NOHSC). DANGEROUS GOODS (According to ADG Code).

SAFETY PHRASES

S9	Keep container in a well-ventilated place.
S16	Keep away from sources of ignition - No smoking.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S51	Use only in well-ventilated areas.
S24/25	Avoid contact with skin and eyes.

DG CLASS

Class 3: Flammable liquids.

PACKING GROUP II

UN NO. 1993

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
CYCLOHEXANE	203-806-2	110-82-7	30-60%	F;R11 Xn;R65 Xi;R38 R67 N;R50/53
PROPAN-2-OL	200-661-7	67-63-0	10-30%	F;R11 Xi;R36 R67
1-METHOXY-2-PROPANOL	203-539-1	107-98-2	10-30%	R10
HEXANE MIXTURE OF ISOMERS (MAX 5% n-HEXANE (203-777-6))			5-10%	F;R11 Xn;R65 Xi;R38 R67 N;R51/53
HEPTANE	205-563-8	142-82-5	1-5%	F;R11 Xn;R65 Xi;R38 R67 N;R50/53
HEXANE-norm	203-777-6	110-54-3	1-5%	F;R11 Repr3;R62 Xn;R65,R48/20 Xi;R38 R67 N;R51/53

ULTRASOLVE

COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels Ingredients are registered on AICS

4 FIRST-AID MEASURES

NOTES TO THE PHYSICIAN

Treat symptomatically

INHALATION

Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention.

INGESTION

DO NOT INDUCE VOMITING! Remove victim immediately from source of exposure. Rinse mouth thoroughly. Provide rest, warmth and fresh air. Get medical attention immediately!

SKIN CONTACT

Remove affected person from source of contamination. Remove contaminated clothing. Wash the skin immediately with soap and water. Get medical attention if irritation persists after washing.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Contact physician if irritation persists.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

Fire can be extinguished using: Foam. Dry chemicals, sand, dolomite etc.

SPECIAL FIRE FIGHTING PROCEDURES

Avoid breathing fire vapours. Cool containers exposed to flames with water until well after the fire is out. Keep run-off water out of sewers and water sources. Dike for water control.

6 ACCIDENTAL RELEASE MEASURES

SPILL CLEAN UP METHODS

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Clean-up personnel should use respiratory and/or liquid contact protection. Absorb in vermiculite, dry sand or earth and place into containers.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Avoid spilling, skin and eye contact. Keep away from heat, sparks and open flame. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level. Use explosion proof electric equipment.

STORAGE PRECAUTIONS

Flammable/combustible - Keep away from oxidisers, heat and flames. Store in tightly closed original container in a cool, dry well-ventilated place. Keep in original container.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	LT - ppm	LT - mg/m3	ST - ppm	ST - mg/m3
1-METHOXY-2-PROPANOL	ES-TWA	100 ppm	369 mg/m3	150 ppm	553 mg/m3
CYCLOHEXANE		300 ppm	1030 mg/m3		
HEPTANE		400 ppm	1640 mg/m3	500 ppm	2050 mg/m3
HEXANE-norm	ES-TWA	20 ppm	72 mg/m3		
PROPAN-2-OL	ES-TWA	400 ppm	983 mg/m3	500 ppm	1230 mg/m3

INGREDIENT COMMENTS

Australian exposure limits are: LT= ES-TWA and ST= ES STEL

PROTECTIVE EQUIPMENT



ULTRASOLVE

ENGINEERING MEASURES

Provide adequate general and local exhaust ventilation.

RESPIRATORY EQUIPMENT

Respiratory protection must be used if air contamination exceeds acceptable level.

HAND PROTECTION

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

EYE PROTECTION

Wear approved chemical safety goggles where eye exposure is reasonably probable.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

HYGIENE MEASURES

DO NOT SMOKE IN WORK AREA! Wash at the end of each work shift and before eating, smoking and using the toilet. Wash promptly with soap & water if skin becomes contaminated. Promptly remove any clothing that becomes contaminated. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Liquid Clear		
COLOUR	Colourless		
ODOUR	Organic solvents.		
SOLUBILITY	Insoluble in water		
BOILING POINT (°C)	>80	RELATIVE DENSITY	0.78 @ 20 °c
FLASH POINT (°C)	0 CC (Closed cup).	AUTO IGNITION TEMPERATURE (°C)	>200
FLAMMABILITY LIMIT - LOWER(%)	0.7	FLAMMABILITY LIMIT - UPPER(%)	8.3

10 STABILITY AND REACTIVITY

STABILITY

Stable under normal temperature conditions.

CONDITIONS TO AVOID

Avoid heat. Avoid contact with oxidisers or reducing agents.

HAZARDOUS DECOMPOSITION PRODUCTS

Fire creates: Toxic gases/vapours/fumes of: Carbon monoxide (CO). Carbon dioxide (CO2).

11 TOXICOLOGICAL INFORMATION

INHALATION

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea.

INGESTION

May cause discomfort if swallowed.

SKIN CONTACT

Irritating to skin. Product has a defatting effect on skin. Prolonged contact may cause dryness of the skin.

EYE CONTACT

Irritating to eyes.

ROUTE OF ENTRY

Inhalation. Skin absorption.

12 ECOLOGICAL INFORMATION

ECOTOXICITY

Dangerous for the environment if discharged into watercourses.

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements.

ULTRASOLVE

14 TRANSPORT INFORMATION



UK ROAD CLASS	3		
PROPER SHIPPING NAME	FLAMMABLE LIQUID, N.O.S. (CYCLOHEXANE, PROPAN-2-OL)		
ADG CLASS	Class 3: Flammable liquid		
UN NO.	1993	UK ROAD PACK GR.	II
ADR CLASS NO.	3	DG CLASS	Class 3: Flammable liquids.
PACKING GROUP	II	HAZARD No. (ADR)	33
ADR LABEL NO.	3	HAZCHEM CODE	3YE
CEFIC TEC(R) NO.	30GF1-I+II, 30GF1-sp	RID CLASS NO.	3
RID PACK GROUP	II	UN NO. SEA	1993
IMDG CLASS	3	IMDG PAGE NO.	3230
IMDG PACK GR.	II	EMS	F-E, S-E
MFAG	See Guide	MARINE POLLUTANT	No.
UN NO. AIR	1993	AIR CLASS	3
AIR PACK GR.	II		

15 REGULATORY INFORMATION

LABELLING



Harmful



Highly Flammable



Dangerous for the environment

CONTAINS

CYCLOHEXANE

RISK PHRASES

R11	Highly flammable.
R36/38	Irritating to eyes and skin.
R50/53	Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R67	Vapours may cause drowsiness and dizziness.
R65	Harmful: may cause lung damage if swallowed.

SAFETY PHRASES

S9	Keep container in a well-ventilated place.
S16	Keep away from sources of ignition - No smoking.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S51	Use only in well-ventilated areas.
S24/25	Avoid contact with skin and eyes.

GUIDANCE NOTES

Exposure Standards for Atmospheric Contaminants in the Occupational Environment [NOHSC:1003 (1995)]

NATIONAL REGULATIONS

National Model Regulations for the Control of Workplace Hazardous Substances [NOHSC:1005(1994)]

National Code of Practice for the Control of Workplace Hazardous Substances [NOHSC:2007(1994)]

National Code of Practice for the Preparation of Material Safety Datasheets [NOHSC:2011(2003)]

Approved Criteria for Classifying Hazardous Substances [NOHSC:1008 (2004) and List of Designated Hazardous Substances

ULTRASOLVE

POISONS SCHEDULE NUMBER NONE

16 OTHER INFORMATION

REVISION DATE NOVEMBER 2007

REV. NO./REPL. SDS GENERATED 0

SDS NO. 10620

RISK PHRASES IN FULL

R10	Flammable.
R11	Highly flammable.
R36	Irritating to eyes.
R38	Irritating to skin.
R48/20	Harmful: danger of serious damage to health by prolonged exposure through inhalation.
R50/53	Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R62	Possible risk of impaired fertility.
R65	Harmful: may cause lung damage if swallowed.
R67	Vapours may cause drowsiness and dizziness.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.