
Item no.: 283-101
Product description: 2-CONDUCTOR THROUGH TERMINAL BLOCK



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.2 - 16 mm ²
Cross section [AWG]	24 - 6 AWG
Connection method	CAGE CLAMP [®] CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	76 A
Weight	27.594 g
Color	gray
Wiring type	Side-entry
No. of connection Points	2
No. of potentials	1
Height	45.5 mm
Height	1.79 in
Width	12 mm
Width	0.472 in
Depth	58 mm
Depth	2.28 in

Strip length from	16 mm
Strip length to	17 mm
Strip length	0.65 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
283-101	ABS	05-HG476175/3-PDA	800	76	6,0
283-101	BV	07436/Co	800	76	6,0
283-101	CCA	NL5917	800	76	16
283-101	CSA	154112-1536072	600	90	24-6
283-101	DNV	E-10423	800	76	6,0
283-101	GL	17295-00HH	800	76	16
283-101	KEMA	2082859.12	800	76	16
283-101	KR	HMB05880-EL001	800	85	16
283-101	LR	91/20112(E6)	800	76	6,0
283-101	PRS	TE/1718/880590/08	800	76	16
283-101	RMR	11130002	800	76	6,0
283-101	UR	E45172	600	65	24-6

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected