

# Heavy duty switch terminal blocks with blade

## Double compression clamp





DIN 1 - DIN 3

End stop	th. 9,0 mm	<b>BADL</b>	V0	<b>0199 408.02</b>
End stop	th. 9,1 mm	<b>BAM</b>		<b>0103 002.26</b>
<i>Other end stops : See Accessories section</i>				
Rail	35 x 7,5 x 1	<b>PR30</b>	prepunched	<b>0173 220.05</b>
Rail	35 x 15 x 2,3	<b>PR4</b>		<b>0168 500.12</b>
Rail	35 x 15 x 1,5	<b>PR5</b>	prepunched	<b>0101 598.26</b>
Rail	32 x 15	<b>PR1Z2</b>		<b>0163 050.04</b>
<i>Other rails : See Accessories section</i>				

### Notes

The use of some accessories may decrease the block's voltage rating. For more information, consult us.

### Accessories


1		1 End section	grey	<b>FEM6.4A</b>	th. 3 mm	<b>0116 629.22</b>
			beige	<b>FEM4A V0</b>	th. 3 mm	<b>0196 629.23</b>
2		2 Test plug		<b>FC2</b>	DIA. 2 mm	<b>0007 865.26</b>
3		3 Comb type jumper bar	35 A	<b>PC61</b>	10 poles	<b>0163 311.22</b>
4		4 IDC jumper		<b>AD2,5</b>		<b>0114 205.20</b>



R See section on markers marking method



## M 4/6.SNBT.4A

Spacing 6 mm + 0,05 (.238")



6 mm block - switch connection by short blade equipped with 2 test socket screws DIA. 2 mm / .079"



Color	Type	Part numbers
Grey	 <b>M 4/6.SNBT.4A</b>	<b>0115 480.11</b>
Beige V0	 <b>M 4/6.SNBT.4A.V0</b>	<b>0195 480.12</b>

### Characteristics

Wire size	IEC		UL	CSA
	NFC	DIN		
Compression Solid wire	0,5-4 mm <sup>2</sup>		22-10 AWG	
clamp Stranded wire	0,5-4 mm <sup>2</sup>		22-10 AWG	

Voltage			
Rated	320 V	600 V	
Pulse	4 kV		
Pollution degree	3		

Current			
Rated	10 A	10 A	

Wire size			
Rated / Gauge	4 mm <sup>2</sup> / A4	10 AWG	
Wire stripping length	Recomm. screwdriver	Recomm. torque	Protection
9,5 mm .374 "	4 mm .157"	0.5-0.6 Nm 4.4-5.3 lb.in	IP 20 NEMA 1

Type	Part numbers
<b>FEM6.4A</b>	th. 3 mm <b>0116 629.22</b>
<b>FEM4A V0</b>	th. 3 mm <b>0196 629.23</b>
<b>FC2</b>	DIA. 2 mm <b>0007 865.26</b>
<b>PC61</b>	10 poles <b>0163 311.22</b>
<b>AD2,5</b>	<b>0114 205.20</b>

(1) Sides of block (6) RC610 on blade