

Field bus components

FBCon PA CG 2way

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



The FBCon Fieldbus distributor is available in the industry and EEx (ia) version. They are used for coupling from 1 to 8 field devices or sensors.

They are connected via spur lines. The connection to the spur line can be made with an M12 plug or directly via an EMC cable gland. Communication and device power feed are transferred by a common 2-wire line.

The distributors offer the following features irrespective of the version:

- Tension-clamp connection system
- Overvoltage protection for the main line
- Current limiter for each branch line
- EMC cable gland
- M12 plug-in connectors
- External earthing contact
- Interruption-free bus operation
- Industrial version
- Bus termination integrated (not EX)
- ATEX explosion-proof version
- Pressure-equalising element
- Protection degrees IP65, IP66, IP67
- Stainless steel versions
- PROFIBUS-PA compatible

General ordering data

Order No.	8564100000
Type	FBCon PA CG 2way
Version	Standard distributor, 2-way distributor, IP 66
GTIN (EAN)	4032248236725
Qty.	1 pc(s).

**Field bus components
FBCon PA CG 2way**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

Dimensions

Length	98 mm	Width	64 mm
Height	37 mm		

Temperatures

Ambient temperature	-40 °C...+85 °C	Storage temperature	
---------------------	-----------------	---------------------	--

Technical data

Bus line connection via	Tension clamp connection	Bus system	Profibus-PA
Cable gland	branch line CG	Colour	Grey
Connection type PE	Spur line with cable gland	Contact carrier material	Brass
Contact material	CuZnAu	Housing main material	Al - Si 12
Number of contact sockets	2	Protection degree	IP 66
Type of mounting	surface-mounted	Version	Aluminium enclosure

Classifications

ETIM 2.0	EC000214	ETIM 3.0	EC000214
ETIM 4.0	EC001604	UNSPSC	26-12-16-03
eClass 4.1	27-25-02-01	eClass 5.1	27-25-02-01
eClass 6.0	27-24-26-08	eClass 7.0	27-24-26-08

Approvals

Approvals



Downloads

Declaration of Conformity [K328_01_10.pdf](#)