



**NOTE 1 - ATTACHMENT TYPE**

- 00 - NO EYELET OR RING
- 01-05 - EYELET REF. (SEE TABLE 2)
- 09-25 - RING REF. (SEE TABLE 3)
- S09-S25 - SPLIT RING REF. (SEE TABLE 3)
- CF - SUPPLIED WITH CRIMP FERRULE



**100P237-17-1-C**  
NO ATTACHMENT VERSION



**100P237-17-1-C-EO**  
EYELET ONLY VERSION  
(EYELET SIZE OPTIONS NOT AVAILABLE)

EXAMPLE PART NUMBER: 100P237-17-1-C-WR4-17	
100P237 =	POLAMCO SERIES
F =	INSERT F FOR FLUOROSILICONE GASKET (STANDARD GASKET MATERIAL: SILICONE)
17 =	SHELL SIZE (TABLE 1)
1 =	MATERIAL (ALUMINIUM ALLOY)
C =	PLATING: (TABLE 6)
WR =	LANYARD TYPE: (TABLE 4)
4 =	LANYARD LENGTH (IN INCHES) +1,0"/-0" TOLERANCE
17 =	ATTACHMENT REF. (SEE NOTE 1)


DRAWN K.SHEPPARD SALES APPR DESIGN APPR QUAL APPR ISSUE 9 WEIGHT —	DATE 17/08/2011 DCR 4423 GENERAL TOL LINEAR +/-0.1MM ANGULAR +/- 1°	3RD ANGLE PROJECTION NOT TO SCALE THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.	 <b>POLAMCO</b> WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP	PAGE 1 OF 2	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES NCAGE CODE U5792 DRAWING NO: P10270
ASSY USED ON: MIL-DTL-38999 SERIES III TITLE: <b>PLUG PROTECTION CAP</b> PART NUMBER: <b>100P237 SERIES</b>					

TABLE 1		
SHELL SIZE	A MAX	B THREAD
09	21,0	0.625-0.1P-0.3L-TS
11	24,5	0.750-0.1P-0.3L-TS
13	28,0	0.875-0.1P-0.3L-TS
15	30,0	1.000-0.1P-0.3L-TS
17	34,0	1.1875-0.1P-0.3L-TS
19	37,0	1.250-0.1P-0.3L-TS
21	40,0	1.375-0.1P-0.3L-TS
23	43,0	1.500-0.1P-0.3L-TS
25	47,0	1.625-0.1P-0.3L-TS

TABLE 2	
EYELET REF.	F
01	3,2
02	3,7
03	4,3
04	5,3
05	6,4



TABLE 3		
RING REF.	SPLIT RING REF.	E
09	S09	15,1
11	S11	18,0
13	S13	19,4
15	S15	22,6
17	S17	25,8
19	S19	28,8
21	S21	32,0
23	S23	34,1
25	S25	40,1

TABLE 4	
CODE	LANYARD TYPE
WR	NYLON COVERED (CLEAR) STAINLESS STEEL WIRE ROPE
TC	TEFLON COVERED (CLEAR) STAINLESS STEEL WIRE ROPE
WG	TEFLON COVERED (OLIVE DRAB) STAINLESS STEEL WIRE ROPE
WB	TEFLON COVERED (BLACK) STAINLESS STEEL WIRE ROPE
WRB	PVC COVERED (BLACK) STAINLESS STEEL WIRE ROPE
LC	LINK CHAIN
BK	BLACK CORD
VGB	1,5 mm BLACK POLYESTER CORD EQV. TO DIN83330-E1,5
B	BEAD CHAIN
R	OLIVE DRAB POLYESTER CORD
NB	OLIVE DRAB NYLON CORD
NK	BLACK NYLON CORD
WRB	PVC COVERED (BLACK) STAINLESS STEEL WIRE ROPE
LC	LINK CHAIN
BK	BLACK CORD
VGB	1,5mm BLACK POLYESTER CORD EQV. TO DIN83330-E1,5
B	BEAD CHAIN
R	OLIVE DRAB POLYESTER CORD
NB	OLIVE DRAB NYLON CORD
NK	BLACK NYLON CORD

TABLE 5	
CODE	MATERIAL
1	ALUMINIUM
2	NICKEL ALUMINIUM BRONZE
4	STAINLESS STEEL
7	BLACK ACETAL
74	COMPOSITE

TABLE 6	
PLATING CODE	PLATING DESCRIPTION
B	CADMIUM, OLIVE DRAB (5-10 MICRONS) QQ-P-416, TYPE II, CLASS 3 OVER ELECTROLESS NICKEL
C	ELECTROLESS NICKEL, AMS-C-26074, CLASS 4, GRADE B
G	BLACK ANODISE, SULPHURIC, PER MIL-A-8625, TYPE II, CLASS 2
J	PASSIVATE, PER QQ-P-35 OR MI-S-5002
U	UNPLATED CLEAN FINISH NOT SHOT BLASTED
Z	SHOT BLAST FOR NON-REFLECTIVE FINISH
ZB	ZINC COBALT, OLIVE DRAB (5-10 MICRONS) OVER ELECTROLESS NICKEL (2.5 - 7.5 MICRONS)
ZN	ZINC NICKEL BLACK PASSIVATE (5-12 MICRONS) OVER ELECTROLESS NICKEL (8-12 MICRONS), ASTM B 841 CLASS 1

NOTE 2 - TABLES 5 & 6 NOT EXHAUSTIVE. FOR COMPREHENSIVE LIST AND SPECS SEE WEBSITE

DRAWN K.SHEPPARD	DATE 17/08/2011	 3RD ANGLE PROJECTION NOT TO SCALE	 <b>POLAMCO</b> WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP	PAGE 2 OF 2	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES	
SALES APPR						
DESIGN APPR		THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.	ASSY USED ON:			
QUAL APPR			TITLE:	<b>PLUG PROTECTION CAP</b>		
ISSUE 9	DCR 4423		PART NUMBER:	<b>100P237 SERIES</b>		NCAGE CODE U5792
WEIGHT —	GENERAL TOL LINEAR +/-0.1MM ANGULAR +/- 1°				DRAWING NO: P10270	