

# SEMiX653GB176HDs



SEMiX® 3s

## Trench IGBT Modules


### SEMiX653GB176HDs

#### Features

- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$  with positive temperature coefficient
- UL recognised file no. E63532

#### Typical Applications\*

- AC inverter drives
- UPS
- Electronic welders



GB

Absolute Maximum Ratings				
Symbol	Conditions	Values	Unit	
<b>IGBT</b>				
$V_{CES}$		1700	V	
$I_C$	$T_j = 150\text{ °C}$	$T_c = 25\text{ °C}$	619	A
		$T_c = 80\text{ °C}$	438	A
$I_{Cnom}$		450	A	
$I_{CRM}$	$I_{CRM} = 2 \times I_{Cnom}$	900	A	
$V_{GES}$		-20 ... 20	V	
$t_{psc}$	$V_{CC} = 1000\text{ V}$	$T_j = 125\text{ °C}$	10	$\mu\text{s}$
	$V_{GE} \leq 20\text{ V}$			
	$V_{CES} \leq 1700\text{ V}$			
$T_j$		-55 ... 150	$^{\circ}\text{C}$	
<b>Inverse diode</b>				
$I_F$	$T_j = 150\text{ °C}$	$T_c = 25\text{ °C}$	545	A
		$T_c = 80\text{ °C}$	365	A
$I_{Fnom}$		450	A	
$I_{FRM}$	$I_{FRM} = 2 \times I_{Fnom}$	900	A	
$I_{FSM}$	$t_p = 10\text{ ms, sin } 180^{\circ}, T_j = 25\text{ °C}$	2900	A	
$T_j$		-40 ... 150	$^{\circ}\text{C}$	
<b>Module</b>				
$I_{t(RMS)}$		600	A	
$T_{stg}$		-40 ... 125	$^{\circ}\text{C}$	
$V_{isol}$	AC sinus 50Hz, $t = 1\text{ min}$	4000	V	

Characteristics					
Symbol	Conditions	min.	typ.	max.	Unit
<b>IGBT</b>					
$V_{CE(sat)}$	$I_C = 450\text{ A}$ $V_{GE} = 15\text{ V}$ chipelevel	$T_j = 25\text{ °C}$	2	2.45	V
		$T_j = 125\text{ °C}$	2.45	2.9	V
$V_{CE0}$		$T_j = 25\text{ °C}$	1	1.2	V
		$T_j = 125\text{ °C}$	0.9	1.1	V
$r_{CE}$	$V_{GE} = 15\text{ V}$	$T_j = 25\text{ °C}$	2.2	2.8	$\text{m}\Omega$
		$T_j = 125\text{ °C}$	3.4	4.0	$\text{m}\Omega$
$V_{GE(th)}$	$V_{GE} = V_{CE}, I_C = 18\text{ mA}$	5.2	5.8	6.4	V
$I_{CES}$	$V_{GE} = 0\text{ V}$ $V_{CE} = 1700\text{ V}$	$T_j = 25\text{ °C}$		3	$\text{mA}$
		$T_j = 125\text{ °C}$			$\text{mA}$
$C_{ies}$	$V_{CE} = 25\text{ V}$		39.6		nF
$C_{oes}$	$V_{GE} = 0\text{ V}$		1.65		nF
$C_{res}$			1.31		nF
$Q_G$	$V_{GE} = -8\text{ V...} + 15\text{ V}$		4200		nC
$R_{Gint}$	$T_j = 25\text{ °C}$		1.67		$\Omega$
$t_{d(on)}$	$V_{CC} = 1200\text{ V}$	$T_j = 125\text{ °C}$	290		ns
$t_r$	$I_C = 450\text{ A}$	$T_j = 125\text{ °C}$	90		ns
		$T_j = 125\text{ °C}$	300		mJ
$E_{on}$	$R_{Gon} = 3.6\text{ }\Omega$	$T_j = 125\text{ °C}$	975		ns
$t_{d(off)}$	$R_{Goff} = 3.6\text{ }\Omega$	$T_j = 125\text{ °C}$	190		ns
$t_f$		$T_j = 125\text{ °C}$	180		mJ
$E_{off}$		$T_j = 125\text{ °C}$			
$R_{th(j-c)}$	per IGBT			0.054	K/W

# SEMiX653GB176HDs



SEMiX® 3s

## Trench IGBT Modules

### SEMiX653GB176HDs


#### Features

- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$  with positive temperature coefficient
- UL recognised file no. E63532

#### Typical Applications\*

- AC inverter drives
- UPS
- Electronic welders

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
<b>Inverse diode</b>						
$V_F = V_{EC}$	$I_F = 450\text{ A}$ $V_{GE} = 0\text{ V}$ chip	$T_j = 25\text{ °C}$		1.7	1.90	V
		$T_j = 125\text{ °C}$		1.7	1.9	V
$V_{F0}$		$T_j = 25\text{ °C}$	0.9	1.1	1.3	V
		$T_j = 125\text{ °C}$	0.7	0.9	1.1	V
$r_F$		$T_j = 25\text{ °C}$	1.3	1.3	1.3	mΩ
		$T_j = 125\text{ °C}$	1.8	1.8	1.8	mΩ
$I_{RRM}$	$I_F = 450\text{ A}$	$T_j = 125\text{ °C}$		380		A
$Q_{rr}$	$di/dt_{off} = 4200\text{ A}/\mu\text{s}$ $V_{GE} = -15\text{ V}$	$T_j = 125\text{ °C}$		130		μC
$E_{rr}$	$V_{CC} = 1200\text{ V}$	$T_j = 125\text{ °C}$		73		mJ
$R_{th(j-c)}$	per diode				0.11	K/W
<b>Module</b>						
$L_{CE}$				20		nH
$R_{CC'+EE'}$	res., terminal-chip	$T_C = 25\text{ °C}$		0.7		mΩ
		$T_C = 125\text{ °C}$		1		mΩ
$R_{th(c-s)}$	per module			0.04		K/W
$M_s$	to heat sink (M5)		3		5	Nm
$M_t$		to terminals (M6)	2.5		5	Nm
$w$					300	g
<b>Temperatur Sensor</b>						
$R_{100}$	$T_c = 100\text{ °C}$ ( $R_{25} = 5\text{ k}\Omega$ )			$493 \pm 5\%$		Ω
$B_{100/125}$	$R_{(T)} = R_{100} \exp[B_{100/125}(1/T - 1/T_{100})]$ ; $T[\text{K}]$ ;			$3550 \pm 2\%$		K



GB




Fig. 1: Typ. output characteristic, inclusive  $R_{CC'+EE'}$




Fig. 2: Rated current vs. temperature  $I_C = f(T_C)$




Fig. 3: Typ. turn-on /-off energy =  $f(I_C)$




Fig. 4: Typ. turn-on /-off energy =  $f(R_G)$




Fig. 5: Typ. transfer characteristic




Fig. 6: Typ. gate charge characteristic




Fig. 7: Typ. switching times vs.  $I_C$




Fig. 8: Typ. switching times vs. gate resistor  $R_G$




Fig. 9: Typ. transient thermal impedance




Fig. 10: Typ. CAL diode forward charact., incl.  $R_{CC+EE}$




Fig. 11: Typ. CAL diode peak reverse recovery current






Fig. 12: Typ. CAL diode recovery charge

# SEMiX653GB176HDs


Case: SEMiX 3s

screw duct (left top) : F-F (1:1)  
 screw duct (1x centre) : H-H (1:1)





	0,3	connector 1-2 / 3-4
	0,2	each connector A

general tolerance:  
 ISO 2768-mK  
 ISO 8015



All measures in Z-direction valid when mounted to heat sink



\*screw duct left / top with 


	0,2	A	B	C
--	-----	---	---	---

\*\*screw ducts / guide pins / spring ducts with 

	0,2	A	D	C
--	-----	---	---	---

Rules for the contact PCB:  
 - holes guidepins =  $\varnothing 4 \pm 0,1$  / position tolerance  $\pm 0,1$   
 - holes for screws =  $\varnothing 2,9 \pm 0,1$  / position tolerance  $\pm 0,1$   
 - spring contact pad =  $\varnothing 3,6 \pm 0,1$  / position tolerance  $\pm 0,1$

SEMiX 3s



This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX

\* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our personal.