



Features

- HSUPA/HSDPA/UMTS/EDGE/ GPRS high-speed data
- 7.2Mbps Downlink, 5.76Mbps Uplink
- World-wide Roaming and Internet Connectivity
- Supports Data/ SMS functions
- Automatic installation driver, No CD required
- Chip set Qualcomm MSM6290
- Support Micro SD memory, up to 16GB
- Supports data/SMS functions
- Supports Microsoft Windows 7 32/64 bytes, XP/2000/Vista /Mac OS, Linux



Operating Systems

- Windows 7, XP/2000/VISTA
- Mac OS / Linux
-

System Requirements

- Card Slots : USB2.0 Interface
- Memory: 64MB

Part Number	Dimensions (mm)	Weight	Operating Temp	Interface
GSM-HSUPA	80 x 26 x 10	26g	-20 to +85°C	USB2.0 (5V)



Configure GSM Modem with RF Solutions O2 Contract Simcard

We have teamed up with Wireless Logic to provide the lowest cost contract specifically for our low usage products. Unlike Pay as you Go which disconnect after 90days of inactivity, this sim will stay connected.

In order to activate this simcard please complete and submit the Airtime Proposal and return to Wireless Logic.

If using A.N Other SIMCARD you will need to configure the service provider to enable GPRS to the following parameters.

Parameters Required for Mobile Internet	
Required Parameter	Value if using O2
APN	mobile.o2.co.uk
User	mobileweb
Password	password
Authentication	CHAP or PAP

Whilst the information in this document is believed to be correct at the time of issue, RF Solutions Ltd does not accept any liability whatsoever for its accuracy, adequacy or completeness. No express or implied warranty or representation is given relating to the information contained in this document. RF Solutions Ltd reserves the right to make changes and improvements to the product(s) described herein without notice. Buyers and other users should determine for themselves the suitability of any such information or products for their own particular requirements or specification(s). RF Solutions Ltd shall not be liable for any loss or damage caused as a result of user's own determination of how to deploy or use RF Solutions Ltd's products. Use of RF Solutions Ltd products or components in life support and/or safety applications is not authorised except with express written approval. No licences are created, implicitly or otherwise, under any of RF Solutions Ltd's intellectual property rights. Liability for loss or damage resulting or caused by reliance on the information contained herein or from the use of the product (including liability resulting from negligence or where RF Solutions Ltd was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict RF Solutions Ltd's liability for death or personal injury resulting from its negligence.

www.rfsolutions.co.uk

RF Solutions Ltd
Unit 21 Cliffe Industrial Estate, Lewes, East Sussex, United Kingdom, BN8 6JL
Tel. Sales: +44 (0)1273 898 000 • Tech. Support: +44 (0)1273 898 007

