

AC TO AC ADAPTOR

Ideal Power Ltd.

77DE-06-12

INPUT VOLTAGE	230VAC
OUTPUT VOLTAGE	12VAC

ELECTRICAL & MECHANICAL SPECIFICATION





18718



18718



Intertek



ELECTRONICAL SPECIFICATION

Input Voltage	230	Volts
Frequency (Hz)	50	Hz
Power Rated (W)	10	W
Exciting Current With No load	60	mA Max
Exciting Current With Full load	80	mA Max
Output Voltage	12.0	Volts±5%
Output Current	0.5	Amp
Output Voltage Without Load	15.6	Volts±5%

HI-POT :

Test Time	1	Min
PRI TO SEC	3750	Volts
PRI TO CORE	3750	Volts
SEC TO CORE	1250	Volts
Efficiency	70	%
Insulation Class	B (130)	°C


MECHANICAL SPECIFICATION

Dimensions (L*W*H)	67.0*48.5*40.0	mm
Weight	245	g
Environment:		
Operating Temperature	-10 To 40	°C
Storage Temperature	-20 To 70	°C
Relative Temperature	40°C±2°C	

Output Cable: **2468 22AWG*2C 1.8M**
LENGTH+5.5*2.1*12mm(I)PLUG

RELATIVE HUMIDITY 90% RH

ELECTRICAL CIRCUIT



Head Office : Acorn House, Tree Beech Enterprise Park, Gunn, Barnstaple, Devon, England EX32 7NZ

TEL: +44 (0) 845 260 3400

FAX: +44 (0) 845 260 3400

E-Mail: info@idealpower.co.uk

WEB: www.idealpower.co.uk