

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0671300806**

Status: **Active**

Overview: pc card cardbus

Description: 1.27mm Card Bus Header: One Slot, Flush Profile, Top Mount, Right Angle, SMT, with Mylar, Embossed Tape on Reel Packaging, Lead-Free

Documents:

[3D Model](#)

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Memory Card Sockets
Series	<u>67130</u>
Comments	With Mylar
Component Type	Header/Socket (Host)
Overview	<u>pc card</u> <u>cardbus</u>
Product Name	CardBus
Style	Guide and Holder
Type	I, II

Physical

Card Detection Switch	No
Circuits (Loaded)	68
Circuits (maximum)	68
Durability (mating cycles max)	10,000
Ejector Button	No
Ejector Button Side	N/A
Entry Angle	Horizontal
Keying to Mating Part	Yes
PCB Locator	Yes
PCB Mounting Side	Reverse
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	0.64mm
Ports	1
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-20°C to +60°C

Electrical

Current - Maximum per Contact	0.5A
Shielded	No
Voltage - Maximum	3.3V
Voltage Key	N/A

Solder Process Data

Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	2
Process Temperature max. C	245

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-67130-004
---------------	--------------




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

67130Series

Use With

67121 Ejector Mechanism

This document was generated on 01/30/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION