



Safety Data Sheet

Regulation EC No 1907/2006 Art.31

Productname : GRAPHITE LOCK LUBE
Ref.Nr.: BDS001121_3_20120117

Creationdate : 17.01.12 Version : 1.0
Replaces: UK10759

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

GRAPHITE LOCK LUBE
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Lubricants

1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd.
Ambersil House - Wylds Road
Castlefield Industrial Estate
TA6 4DD Bridgwater Somerset
United Kingdom
Tel.: +44 1278 727200
Fax.: +44 1278 425644
E-mail : hse.uk@crcind.com

1.4. Emergency telephone number

(+44)(0)1278 72 7200

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to 67/548/EEC or 1999/45/EC:

Health:	R67: Vapours may cause drowsiness and dizziness.
Physical:	EXTREMELY FLAMMABLE
Environment:	not classified

2.2. Label elements

Warning symbol(s) : EXTREMELY FLAMMABLE



Risk-phrase(s) : R67: Vapours may cause drowsiness and dizziness.

Safety-phrase(s) : S2: Keep out of the reach of children.

Special labelling provisions: Indication of R and S phrases in the labelling are reduced based on provisions for labelling of small packages (Dir. 99/45/EC, art.10§4)

Extra label elements according to Aerosol Dispenser Directive 75/324/EC: Aerosols dispensers with a maximum capacity of less than 50 ml are not subject to the provisions of the Aerosol Dispenser Directive (75/324/EEC, art 1)

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
ethanol; ethyl alcohol	64-17-5	200-578-6	40-60	F	11	B
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	200-661-7	<20	F,Xi	11-36-67	B
Graphite	7782-42-5		<10	-	-	G
Explanation notes						
B : substance with national established workplace exposure limit						
G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006						

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
ethanol; ethyl alcohol		64-17-5	200-578-6	40-60	Flam. Liq. 2	H225	B
propan-2-ol; isopropyl alcohol ;isopropanol	01-2119457558-25	67-63-0	200-661-7	<20	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	B
Explanation notes							
B : substance with national established workplace exposure limit							

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :	If substance has got into eyes, immediately wash out with plenty of water Seek medical attention if irritation persists
Contact with skin :	Remove contaminated clothing immediately and drench affected skin with plenty of water. Then wash with soap and water Seek medical attention if irritation persists
Inhalation :	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
Ingestion :	If swallowed accidentally, do not induce vomiting and seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	May cause irritation. Symptoms : redness and pain
Eye contact :	May cause irritation. Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice :	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material
Place in appropriate container

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed
Use explosion-proof electrical/ventilating/lighting/.../equipment.
Use only non-sparking tools.
Do not breathe aerosols or vapours.
Ensure adequate ventilation
Avoid contact with skin and eyes.
Wash thoroughly after use
Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
Keep in a cool, dry, well ventilated place
Keep out of reach of children.

7.3. Specific end use(s)

Lubricants

SECTION 8: Exposure controls/personal protection**8.1. Control parameters**

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	TWA	400 ppm
		STEL	500 ppm
National established exposure limits, United Kingdom			

ethanol; ethyl alcohol

64-17-5

TWA

1000 ppm

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment. Air purifying respirator equipped with organic gas/vapor cartridge (type A or AX) in combination with an oil proof solid and liquid particulate filter
hands and skin :	Wear suitable protective gloves (nitrile)
eyes :	Wear safety goggles.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Apperance : physical state :	Propane/butane propelled liquid.
colour :	Black.
odour :	Characteristic odor.
pH :	Not applicable.
Boiling point/range :	Not available.
Flash point :	< 0 °C
Evaporation rate :	Not available.
Explosion limits : upper limit :	Not available.
lower limit :	Not available.
Vapour pressure :	400 kPa (@ 20°C).
Relative density :	0.82 g/cm ³ (@ 20°C).
Solubility in water :	Insoluble in water
Auto-ignition :	> 200 °C
Viscosity :	Not available.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information**11.1. Information on toxicological effects**

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	May cause gastrointestinal disturbances
Skin contact :	Prolonged skin contact will result in defatting of the skin, leading to irritation, and in some cases, dermatitis Repeated exposure may cause skin dryness or cracking.
Eye contact :	May cause irritation.

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
ethanol; ethyl alcohol	64-17-5	LD50 oral rat	> 2000 mg/kg
		LD50 derm.rabit	> 2000 mg/kg
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	LD50 oral rat	>2000 mg/kg
		LC50 inhal.rat	>20 mg/l
		LD50 derm.rabit	>2000 mg/kg

SECTION 12: Ecological information**12.1. Toxicity**

not classified

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
ethanol; ethyl alcohol	64-17-5	LC50 fish	> 100 mg/l
propan-2-ol; isopropyl alcohol ;isopropanol	67-63-0	IC50 algae	>100 mg/l
		LC50 fish	>100 mg/l
		EC50 daphnia	>100 mg/l

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product :	This material and its container must be disposed of in a safe way. Do not discharge into drains or the environment, dispose to an authorised waste collection point.
Contaminated packaging :	Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS

14.3. Transport hazard class(es)

Class:	2.1
ADR/RID - Classification code:	5F

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous:	No
IMDG - Marine pollutant:	No

IATA/ICAO - Environmentally hazardous:	No
--	----

14.6. Special precautions for user

IMDG - Ems:	F-D, S-U
IATA/ICAO - PAX:	203
IATA/ICAO - CAO:	203

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
 EU-directive 99/45/EC
 Regulation (EC) No 1907/2006 (REACH)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation risk-phrases:	R11: Highly flammable. R36: Irritating to eyes. R67: Vapours may cause drowsiness and dizziness.
*Explanation hazard statements:	H225 : Highly flammable liquid and vapour. H319 : Causes serious eye irritation. H336 : May cause drowsiness or dizziness.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

