



TYPE - CLR



[Contact your local Sales Representative](#)
[Click Here for Printable Version](#)



Type	US Trade Size	MM	Nw	Nominal	Dimensions	Min. Bend	Inside Radius	Wt. (LBS.)/100Ft	Std.	Footage	
				Inside	Outside	Static	Dynamic		Length	Part #	
CLR-516	5/16"	12	10	.378"(9.6mm)	.512"(13.0mm)	0.8"	20."	1.8	100	790719	
CLR-10	3/8"	16	12	.460"(11.7mm)	.622"(15.8mm)	1.0"	2.6"	3.0	100	790819	
CLR-11	1/2"	20	17	.653"(16.6mm)	.826"(21.0mm)	1.2"	3.5"	4.4	100	791819	
CLR-12	3/4"	25	23	.854"(21.7mm)	1.122"(28.5mm)	1.6"	4.0"	6.7	100	792819	
CLR-13	1"	32	29	1.078"(27.4mm)	1.358"(34.5mm)	2.0"	5.0"	9.0	50	793819	
CLR-14	1-1/4"	40	36	1.410"(35.8mm)	1.673"(42.5mm)	2.4"	7.0"	10.8	50	794819	
CLR-15	1-1/2"	50	48	1.840"(46.7mm)	2.145"(54.5mm)	2.8"	8.0"	15.4	50	795819	
CLR-17	2-1/2"	70	70	2.645"(67.0mm)	3.150"(80.0mm)	6.0"	14.0"	31.6	30	796869	
CLR-350	3-1/2"	95	95	3.600"(91.5mm)	4..170"(106mm)	7.0"	18.0"	51.8	30	798869	

* Reels Available. Consult Factory.

See [Corrlok Information Page](#)

TYPE - CLR

Very light weight and extremely flexible. Ideally suited for robotic equipment. This tubing is intended for applications requiring continuous, repeated flexible motion, such as power track or cable carrier installations.

Fitting Pull-Out:

65lbs.

Material:

Halogen Free Nylon 12

STANDARD COLORS:

Black. Other colors available upon request.

WORKING TEMPERATURES:

-50°C to 95°C Intermitting to 150°C

Flexibility: [See the Flexibility Comparison Guide](#)

Plastic Used: NYLON [See the Chemical Resistance Guide](#)

High Mech. Strength	Listed For Direct Burial	Halogen Free	Low Fire Hazard	Accepts Standard Liquidtight Fittings	Self Extinguish	EMI/RFI Shielding	Oil Resistance	Acid Resistance
		X			X		X	