

DEA1X3F221JA3B

" # " indicates a package specification code.



< List of part numbers with package codes >
DEA1X3F221JA3B

Shape

Lead Code	Coating Extension e	ø d	Style
A2, A3	Up to the end of crimp	0.6±0.05	Fig. 1
C1, CD	3.0 max.	0.5±0.05	Fig. 2
C3	3.0 max.	0.6±0.05	Fig. 2

L size or outer diameter D (mm)	12 mm max.
Lead spacing F	7.5 ± 1.0mm
Product thickness T	6.0mm max.
Lead diameter d	0.6 ± 0.05mm
Paint dripping e	Up to the end of crimp

References

Packaging	Specifications	Minimum quantity
	Packing in bulk	200

Specifications

Capacitance	220pF ± 5%
Rated voltage	3150Vdc
Temperature characteristics (complied standard)	SL(JIS)
Temperature coefficient	+350 to -1000ppm/
Temperature range of temperature characteristics	+20 to +85
Operating temperature range	-25 to +125

⚠ Attention

- This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ' s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.