



American Electronic Components, Inc.
 1101 Lafayette Street, Elkhart, IN 46516, Tel: (574) 295-6330, Fax: (574) 293-8013, sales@aecsensors.com

Series CBC (Closed) 100 Amps

Durakool mercury contactors are a favorite choice for high reliability lighting and heating control. Their low maintenance and excellent tungsten in-rush handling characteristics provide dependable long-term operation. CFC (normally open) and CBC (normally closed) contactors are general purpose rated at 100 Amps. Top and bottom compression-lug connectors provide secure connection.

"C" size Durakool contactors have mercury-to-tungsten contacts for easy handling of inductive, tungsten, motor and resistive loads. Tungsten's resistance to arcing erosion prolongs the life of the contactor.

SPECIFICATIONS

Maximum Time:	Operate	Release
Normally Open:	90 ms	140 ms
Normally Closed:	200 ms	100 ms
Contact Bounce, Release:	Allowed on normally open models	
Recommended DC Load Polarity:	Top Connector Negative	
Load Connectors:	Pressure Connector #1-8 AWG Cu.	
Coil Terminals:	#6-32 Wire Binding Screw, Max. #12 AWG Cu.	
Breakdown Voltage:	5000 VRMS/Min. Across Contacts	



TYPE/SERIES	CBC (Normally Closed)				
	DESCRIPTION	Part Number	Typical Coil Data		
Volts			DC Ohms	Watts	Amps
1 Pole	24	CBC-701	7.1	7.7	0.837
	120	CBC-702	180	8.5	0.179
	208	CBC-703	600	7.6	0.087
	240	CBC-704	680	9.3	0.093
	277	CBC-705	1000	8.0	0.070
	480	CBC-706	2700	9.4	0.046
	12 (DC)	CBC-719	27	5.3	0.441
	24 (DC)	CBC-707	111	5.2	0.217

ELECTRICAL RATINGS	GENERAL PURPOSE 0.7/0.8 UL Power Factor						DC		Tungsten Lamp/60 Hz	AC MOTOR LOAD				
	Volts	120	208	240	277	480	600	1-48	120	240	240	1 Phase	3 Phase	
SERIES	60 Hz Amps						DC Amps		Amps	KW	Hp	Hp	Hp	
CFC 100 (Normally Open)	100	100	100	100	100	100	100	50	30	100	12.0	7.5	10	20
CBC 100 (Normally Closed)	100	90	90	60	60	70	100	50	30	90	10.8	7.5	10	20

American Electronic Components, Inc.
 1101 Lafayette Street, Elkhart, IN 46516, Tel: (574) 295-6330, Fax: (574) 293-8013, sales@aecsensors.com


Series CBC (Closed) 100 Amps

