

## Vishay High Power Products

## "Half Bridge" IGBT MTP (Warp Speed IGBT), 114 A



PRODUCT SUMMARY						
V <sub>CES</sub>	600 V					
V <sub>CE(on)</sub> typical at V <sub>GE</sub> = 15 V	2.3 V					
I <sub>C</sub> at T <sub>C</sub> = 25 °C	114 A					

### **FEATURES**

- Generation 4 warp speed IGBT technology
- HEXFRED<sup>®</sup> antiparallel diodes with ultrasoft reverse recovery



- Very low conduction and switching losses
- Optional SMD thermistor (NTC)
- Very low junction to case thermal resistance
- UL approved file E78996
- Speed 60 kHz to 100 kHz
- Compliant to RoHS directive 2002/95/EC
- Designed and qualified for industrial level

#### **BENEFITS**

- Optimized for welding, UPS and SMPS applications
- Low EMI, requires less snubbing
- Direct mounting to heatsink
- PCB solderable terminals
- Very low stray inductance design for high speed operation

ABSOLUTE MAXIMUM RATINGS					
PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS	
Collector to emitter voltage	V <sub>CES</sub>		600	V	
Continuous collector current	,	T <sub>C</sub> = 25 °C	114		
Continuous collector current	Ic	T <sub>C</sub> = 109 °C	50		
Pulsed collector current	I <sub>CM</sub>		350	A	
Peak switching current	I <sub>LM</sub>		350		
Diode continuous forward current	I <sub>F</sub>	T <sub>C</sub> = 109 °C	34		
Peak diode forward current	I <sub>FM</sub>		200		
Gate to emitter voltage	$V_{GE}$		± 20	V	
RMS isolation voltage	V <sub>ISOL</sub>	Any terminal to case, t = 1 minute	2500	V	
	В	T <sub>C</sub> = 25 °C	658	w	
Maximum power dissipation	P <sub>D</sub>	T <sub>C</sub> = 100 °C	263	VV	

## 50MT060WHTAPbF



Document Number: 94468

Revision: 01-Mar-10

# Vishay High Power Products "Half Bridge" IGBT MTP (Warp Speed IGBT), 114 A

<b>ELECTRICAL SPECIFICATIONS</b> (T <sub>J</sub> = 25 °C unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Collector to emitter breakdown voltage	V <sub>(BR)CES</sub>	$V_{GE} = 0 \text{ V}, I_C = 500 \mu\text{A}$	600	-	-	٧
		V <sub>GE</sub> = 15 V, I <sub>C</sub> = 50 A	-	2.3	3.15	
Collector to emitter voltage	V <sub>CE(on)</sub>	V <sub>GE</sub> = 15 V, I <sub>C</sub> = 100 A	-	2.5	3.2	v
		$V_{GE} = 15 \text{ V}, I_{C} = 50 \text{ A}, T_{J} = 150 ^{\circ}\text{C}$	-	1.72	2.17	V
Gate threshold voltage	$V_{GE(th)}$	$I_{C} = 0.5 \text{ mA}$	3	-	6	
Collector to emitter leaking current		V <sub>GE</sub> = 0 V, I <sub>C</sub> = 600 A	-	-	0.4	mA
	I <sub>CES</sub>	$V_{GE} = 0 \text{ V}, I_{C} = 600 \text{ A}, T_{J} = 150 ^{\circ}\text{C}$	-	-	10	IIIA
		$I_F = 50 \text{ A}, V_{GE} = 0 \text{ V}$	-	1.58	1.80	
Diode forward voltage drop	$V_{FM}$	$I_F$ = 50 A, $V_{GE}$ = 0 V, $T_J$ = 150 °C	-	1.49	1.68	V
		$I_F$ = 100 A, $V_{GE}$ = 0 V, $T_J$ = 25 °C	-	1.9	2.17	
Gate to emitter leakage current	I <sub>GES</sub>	$V_{GE} = \pm 20 \text{ V}$	-	-	± 250	nA

<b>SWITCHING CHARACTERISTICS</b> (T <sub>J</sub> = 25 °C unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Total gate charge (turn-on)	Qg	I <sub>C</sub> = 52 A	-	331	385	
Gate to emitter charge (turn-on)	Q <sub>ge</sub>	V <sub>CC</sub> = 400 V	-	44	52	nC
Gate to collector charge (turn-on)	Q <sub>gc</sub>	V <sub>GE</sub> = 15 V	-	133	176	
Turn-on switching loss	E <sub>on</sub>	Internal gate resistors (see electrical diagram)	-	0.26	-	
Turn-off switching loss	E <sub>off</sub>	$I_C = 50$ A, $V_{CC} = 480$ V, $V_{GE} = 15$ V, $L = 200 \mu H$ Energy losses include tail and diode reverse	-	1.2	-	mJ
Total switching loss	E <sub>ts</sub>	recovery, $T_J = 25  ^{\circ}\text{C}$	-	1.46	-	
Turn-on switching loss	E <sub>on</sub>	Internal gate resistors (see electrical diagram) $I_C = 50$ A, $V_{CC} = 480$ V, $V_{GE} = 15$ V, $L = 200$ $\mu$ H Energy losses include tail and diode reverse recovery, $T_J = 150$ °C	-	0.73	-	
Turn-off switching loss	E <sub>off</sub>		-	1.66	-	mJ
Total switching loss	E <sub>ts</sub>		-	2.39	-	
Input capacitance	C <sub>ies</sub>	V <sub>GE</sub> = 0 V V <sub>CC</sub> = 30 V f = 1.0 MHz	-	7100	-	
Output capacitance	C <sub>oes</sub>		-	510	-	рF
Reverse transfer capacitance	C <sub>res</sub>		-	140	-	
Diode reverse recovery time	t <sub>rr</sub>		-	82	97	ns
Diode peak reverse current	I <sub>rr</sub>	V <sub>CC</sub> = 200 V, I <sub>C</sub> = 50 A dl/dt = 200 A/µs	-	8.3	10.6	Α
Diode recovery charge	Q <sub>rr</sub>	α, αι – 200 /ν μο	-	340	514	nC
Diode reverse recovery time	t <sub>rr</sub>	V <sub>CC</sub> = 200 V, I <sub>C</sub> = 50 A	-	137	153	ns
Diode peak reverse current	I <sub>rr</sub>	dl/dt = 200 A/µs	-	12.7	14.8	Α
Diode recovery charge	Q <sub>rr</sub>	T <sub>J</sub> = 125 °C	-	870	1132	nC



# "Half Bridge" IGBT MTP Vishay High Power Products (Warp Speed IGBT), 114 A

THERMISTOR SPECIFICATIONS						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Resistance	R <sub>0</sub> <sup>(1)</sup>	T <sub>0</sub> = 25 °C	-	30	-	kΩ
Sensitivity index of the thermistor material	β (1)(2)	$T_0 = 25 ^{\circ}\text{C}$ $T_1 = 85 ^{\circ}\text{C}$	-	4000	-	К

#### Notes

 $^{(1)}$   $T_0$ ,  $T_1$  are thermistor's temperatures

(2) 
$$\frac{R_0}{R_1} = exp \left[ \beta \left( \frac{1}{T_0} - \frac{1}{T_1} \right) \right]$$
, temperature in Kelvin

THERMAL AND MECHANICAL SPECIFICATIONS							
PARAMETER		SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Operating junction	IGBT, Diode	т		- 40	-	150	
temperature range	Thermistor	$T_J$		- 40	-	125	°C
Storage temperature	range	T <sub>Stg</sub>		- 40	-	125	
lunction to coop	IGBT	В		-	-	0.38	
Junction to case —	Diode	R <sub>thJC</sub>		-	-	0.8	°C/W
Case to sink per mod	dule	R <sub>thCS</sub>	Heatsink compound thermal conductivity = 1 W/mK	-	0.06	-	
Clearance (1)			External shortest distance in air between 2 terminals	5.5	-	-	
Creepage (1)			Shortest distance along the external surface of the insulating material between 2 terminals	8	-	-	mm
Mounting torque to heatsink			A mounting compound is recommended and the torque should be checked after 3 hours to allow for the spread of the compound. Lubricated threads.		3 ± 10 %		Nm
Weight					66		g

### Note

<sup>(1)</sup> Standard version only i.e. without optional thermistor




Fig. 1 - Typical Output Characteristics




Fig. 2 - Maximum Collector Current vs. Case Temperature

### 50MT060WHTAPbF

# Vishay High Power Products "Half Bridge" IGBT MTP (Warp Speed IGBT), 114 A






Fig. 3 - Typical Collector to Emitter Voltage vs. Junction Temperature




Fig. 4 - Typical Gate Charge vs. Gate to Emitter Votlage




Fig. 5 - Maximum Forward Voltage Drop vs. Instantaneous Forward Current




Fig. 6 - Typical Reverse Recovery Time vs.  $dI_F/dt$ 




Fig. 7 - Typical Reverse Recovery Current vs.  $dI_{\mbox{\scriptsize F}}/dt$ 





Fig. 8 - Typical Stored Charge vs. dl<sub>F</sub>/dt



# "Half Bridge" IGBT MTP Vishay High Power Products (Warp Speed IGBT), 114 A




 $\begin{array}{c} 10 \Omega \\ 11 0 \\ \hline \\ 10 \Omega \\ 12 0 \\ \hline \\ 10 \Omega \\ \hline \\ 10 \Omega \\ \hline \\ \\ 7,8 \\ \end{array}$ 

Fig. 9 - Functional Diagram

Fig. 10 - Electrical Diagram

### **ORDERING INFORMATION TABLE**

**Device code** 



1 - Current rating (50 = 50 A)

2 - Essential part number

Voltage rating (060 = 600 V)

Speed/type (W = Warp IGBT)


5 - Circuit configuration (H = Half bridge)

6 - T = Thermistor

 $\overline{7}$  - A = Al<sub>2</sub>O<sub>3</sub> substrate

8 - Lead (Pb)-free

### **CIRCUIT CONFIGURATION**




LINKS TO RELATED DOCUMENTS				
Dimensions	www.vishay.com/doc?95175			



## Vishay Semiconductors

### **MTP**

### **DIMENSIONS** in millimeters



### Note

• Unused terminals are not assembled in the package



### **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## **Material Category Policy**

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.