



Digital Sound Level Meter w/USB Interface Model 72-947

This Flagship of the Tenma sound level meter line provides features normally exclusive to units costing much more. It is perfect for sound system testing, speaker system measurement and environmental noise level monitoring.

Features:

- USB interface with datalogging software
- Internal datalogging
- A and C weighting
- Selectable fast / slow response time
- Large 1999 count backlit LCD display
- Analog bargraph display and numerous on-screen icons
- AC/DC outputs for level recorder
- Self calibration with internal oscillator
- Selectable MIN or MAX hold and data hold function
- Three measurement ranges
- 0.1dB resolution
- Selectable auto-power-off
- Threaded insert which accepts standard tripod mount
- Removable windscreen
- AC adaptor (included) or battery operation
- Includes manual, 9V battery and rugged blow molded carry case



Specifications

Standard applied:	IEC61672-1 Class 2
Frequency range:	31.5Hz ~ 8KHz
Measuring level range:	30dB ~ 130dB
Frequency weighting:	A/C
Microphone:	1/2 inch electret condenser
Calibration:	External potentiometer for use with external calibrated source
Display	1999 count LCD, plus analog bargraph
	Resolution: 0.1dB
	Refresh rate: 0.5 sec.
Accuracy:	±1.4dB, @1KHz, 94dB (under reference conditions)
Time weighting:	FAST (125ms), SLOW (1 sec.)
Level ranges:	LO: 30dB ~ 80dB
	Med: 50dB ~ 100dB
	Hi: 80dB ~ 130dB
	Auto: 30dB ~ 130dB
Alarm function:	Displays "OVER" when input exceeds maximum level of selected range
	Displays "UNDER" when input falls below minimum level of selected range
AC output	1.0Vrms at full scale, output impedance approximately 100Ω
DC output	10mV / dB, output impedance approx 1KΩ
Data output:	USB data traffic
Internal datalogging memory	32,700
Auto power off:	Meter automatically shuts down after approx. 15 minutes of inactivity
Power supply:	One 9V battery, 006P or NEDA1604 or IEC 6F22, or included AC adaptor
Battery life:	Approximately 30 hours
Operation temperature:	0°C ~ 40°C, (32°F ~ 104°F)
Operation humidity:	10 ~ 90% RH
Storage temperature:	-10°C ~ 60°C
Dimension:	9 3/4" (L) x 2 1/2" (W) x 1" (D)
Weight:	350g (including battery)
Accessories:	Instruction manual, battery, windscreen, case, USB cable and software

Copyright 2008
Tenma Test Equipment
405 S. Pioneer Blvd.
Springboro, Ohio 45066
USA
www.tenma.com