



9002AW1 Foot Switch

FOOT SWITCH 600VAC 5AMP +OPTIONS

Image not available

Stock Item: This item is normally stocked in our distribution facility.

- [Product Information \(#\)](#)

Features and Specifications

Connection Type: 0.75 Inch NPT (Conduit Entrance)

Contact Arrangement: SPDT

Enclosure Rating: NEMA 2/4/13

Approvals: UL Listed File: E42259 CCN NKCR - CSA Certified File Number LR25490 Class 184 N 13.1U

Enclosure Type: Water tight, Dust tight and Oil tight (Indoor/Outdoor)

Maximum Voltage Rating: 600V

Shield: Unshielded

Operator Action: Spring Return

Type: A

Documents and Downloads

- [Product Data Sheet \(datasheet.cfm?partnumber=9002AW1\)](#)
 - [Modicon Quantum automation platform \(http://ecatalog.squared.com/pubs/Machine Control/Machine](http://ecatalog.squared.com/pubs/Machine Control/Machine)
 - [Safeguarding-PREVENTA-R/MKTED208011EN-US.pdf Preventa Machine Safety Products 2009 \(http://ecatalog.squared.com/pubs/Machine Control/Machine](http://ecatalog.squared.com/pubs/Machine Control/Machine)
 - [Safeguarding-PREVENTA-R/MKTED208051EN-US.pdf Preventa 2010 Catalog Supplement - Safety Relay Modules \(http://ecatalog.squared.com/pubs/Machine Control/Machine Safeguarding-PREVENTA-R/MKTED208051EN-](http://ecatalog.squared.com/pubs/Machine Control/Machine Safeguarding-PREVENTA-R/MKTED208051EN-US.pdf)
- [View all documents and downloads in the Technical Library » \(http://ecatalog.squared.com/techlib/\)](#)

Ordering and Shipping Information

- **Category** 21441 - Switches, Foot, Type AW
- **Discount Schedule** CS1
- **Article Number** 785901815433
- **Package Qty** 1
- **Weight (lbs.)** 3.11
- **Availability Code** S
- **Returnability** Y