

## PRODUCT DATA

Date: April 2012

Information Sheet No.: 00554-22

---

# EVO-STIK GENERAL PURPOSE AEROSOL

## SOLVENT BASED PRESSURE SENSITIVE ADHESIVE

---

**EVO-STIK GENERAL PURPOSE AEROSOL** is a solvented pressure sensitive spray adhesive, in an economical and controllable method of application. It exhibits rapid drying with excellent initial grab and adhesion properties. The aerosols have variable setting nozzles and use an ozone friendly propellant.

### RECOMMENDED USE

**EVO-STIK GENERAL PURPOSE AEROSOL** has a wide range of uses including bonding foam, cork, felt and other **lightweight** materials to themselves or to wood, glass, metal and rigid plastics.

**EVO-STIK GENERAL PURPOSE AEROSOL** is particularly suitable for bonding polythene sheeting to itself or to masonry or metal substrates in the construction of temporary tenting.

**EVO-STIK GENERAL PURPOSE AEROSOL** is not suitable for use on solvent sensitive materials such as expanded polystyrene or on plasticised materials.

### BONDING INSTRUCTIONS

#### SURFACE PREPARATION

- All surfaces must be clean, dry and free from dust, grease and any loose materials.
- If degreasing is necessary, a detergent/water treatment should first be considered. If this is inappropriate a suitable solvent e.g. **EVO-STIK Cleaner 5** may be used. It is advisable to check the effects of degreasing solvents on plastics, rubber materials and painted surfaces before carrying out the operation. All traces of cleaning solvents must be allowed to evaporate completely before application of the adhesive.

#### APPLICATION & BONDING

- **EVO-STIK GENERAL PURPOSE AEROSOL** should only be used in a well ventilated area.
- Shake Can thoroughly.
- The variable nozzle can be adjusted by rotation for convenience of application.
- Spray adhesive 150 - 200mm away from the substrates to be bonded.
- On non-porous substrates where maximum bond strength is required apply adhesive to both surfaces to be bonded and allow to dry, then bring the dry surfaces together and press over the entire bond area.
- Drying is dependent on conditions but is in the range 1 - 3 minutes.
- On porous surfaces a one way wet method will allow some positioning.
- On very porous surfaces two coats should be applied, allowing the adhesive to dry between coats.
- Excess adhesive may be cleaned off with white spirit.

## TYPICAL CHARACTERISTICS

Physical Form:	Aerosol
Colour:	Amber
Chemical Type:	Blend of synthetic rubber & resins
Solvent:	Methylene chloride
Solids Content:	Approx. 15%
Flammability:	Wet - Flammable Dry - Burns slowly
Service temperature:	-20 to +60°C
Coverage:	10-12 square metres per unit, depending on nozzle setting and application technique

## PACKAGING

For current pack sizes please contact the Customer Service Department

## STORAGE

Store in a dry place out of direct sunlight in the temperature range 10 - 30°C.

**PROTECT FROM FROST**

## SHELF LIFE

12 months in its original container stored under the above conditions.

## MATERIAL SAFETY DATA

For further information refer to the relevant Health and Safety Data Sheet.

---

### Disclaimer - please read carefully

This disclaimer is issued by Bostik Limited ("the Company") and applies to the use of any products supplied by the Company ("the Products") displayed on this Technical Data Sheet ("TDS"). Please read this disclaimer carefully before using any of the Products. Using this TDS and/or the Product constitutes your acceptance of this disclaimer. Its contents shall prevail over any directions of use and any disclaimer and/or exclusion or limitation of liability of the Company which may appear on the packaging of the Products.

This disclaimer sets out the entire financial liability of the Company (including any liability for the acts or omissions of its employees, agents and sub-contractors) to any user of the Products ("Product User") in respect of any use made or resale by the Product User, of any of the Products in this TDS.

This disclaimer does not affect the Company's liability for death or personal injury arising from the Company's negligence in respect of the Products, or its liability for fraud, or fraudulent misrepresentation, or any other liability which cannot be excluded or limited under applicable law.

The Company's total liability however arising and whether caused by tort (including negligence and breach of statutory duty), breach of contract or otherwise, arising in connection with the use made or resale by the Product User of any of the Products in this TDS shall be limited to the price paid for the Product by the Product User.

The Company shall not be liable to the Product User for any pure economic loss, loss of profit, loss of business, depletion of goodwill or otherwise, in each case whether direct, indirect or consequential, or any claims (including in respect of personal injury insofar as not caused by the Company's negligence) for consequential compensation whatsoever (howsoever caused) which arise out of or in connection with the use made or resale by the Product User of any of the Products in this TDS.

The Company shall not be liable to the Product User in relation to any loss for any use which is inappropriate or use which is otherwise than in accordance with the relevant instructions for use of the Products in this TDS or on the Product. Product Users are advised to confirm the suitability of the Products by their own tests.

This TDS covers just one of a large range of products supplied by the Company. Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This TDS supersedes all previous TDSs relating to the Products and users of it must ensure that it is the current issue. Destroy all previous TDS, and if in any doubt, contact the Company, quoting the code number in the top right hand corner on the front of this document.

Bostik Limited, Ulverscroft Road, Leicester, LE4 6BW England. Tel: +44 (0)1785 272625 Fax: +44 (0)116 253 1943

[www.Bostik.co.uk](http://www.Bostik.co.uk)