

Active Cabinet Speakers

Gamma Series

CPA 5000



High quality active cabinets designed for demanding professional applications. The built in amplifier and crossover eliminates the need for a separate power amplifier enabling easier setup and transportation. The range consists of four full range cabinets complimented by an optional subwoofer cabinet for added low frequency response.

- Scuff resistant injection moulded polypropylene cabinets
- Integral carry handles
- 35mm top hat for pole/stand mounting
- Stackable cabinets
- Tough mesh grille for added protection
- Balanced input and output
- 3 way EQ on full range cabinets
- Gain and volume controls
- LED indicators for power and signal
- XLR connectors for all signal connections
- IEC mains inlet

Gamma 8"

Power Rating 150+50W RMS
 Frequency Response 60Hz to 15KHz
 Low Frequency Driver 12" Cast Frame
 High Frequency Driver 1.35" Compression
 Horn Flare Dispersion 90°x60°
 Sensitivity 96 dB
 Maximum SPL 121 dB
 Dimensions (HxWxD) 630 x 330 x 410mm
 Weight 21Kg
 Power Supply 240V ~ 50Hz

Gamma 10"

Power Rating 250+100W RMS
 Frequency Response 50Hz to 15KHz
 Low Frequency Driver 15" Cast Frame
 High Frequency Driver 1.74" Compression
 Horn Flare Dispersion 90°x60°
 Sensitivity 97 dB
 Maximum SPL 122 dB
 Dimensions (HxWxD) 530x310x343mm
 Weight 25Kg
 Power Supply 240V ~ 50Hz

Gamma 12"

Power Rating 300+100W RMS
 Frequency Response 50Hz to 15kHz
 Low Frequency Driver 12" cast frame
 High Frequency Driver 1.74" Compression
 Horn Flare Dispersion 90°x60°
 Sensitivity 97 dB
 Maximum SPL 122 dB
 Dimensions (HxWxD) 630x330x410mm
 Weight 31Kg
 Power Supply 240V ~ 50Hz

Gamma 15"

Power Rating 300+100W RMS
 Frequency Response 50Hz to 15KHz
 Low Frequency Driver 15" Cast Frame
 High Frequency Driver 1.74" Compression
 Horn Flare Dispersion 90°x60°
 Sensitivity 97 dB
 Maximum SPL 122 dB
 Dimensions (HxWxD) 720 x 365 x 495mm
 Weight 25Kg
 Power Supply 240V ~ 50Hz

Gamma 15" Subwoofer

Power Rating 600W RMS
 Frequency Response 40Hz to 115Hz
 Low Frequency Driver 15" cast frame
 High Frequency Driver N/A
 Horn Flare Dispersion N/A
 Sensitivity 97 dB
 Maximum SPL 126 dB
 Dimensions (HxWxD) 640x480x500
 Weight 31Kg
 Power Supply 240V ~ 50Hz

339781.271661

	Order Code	Price Each
Gamma 8" (Pair)	865-1760	
Gamma 10"	509-5712	
Gamma 12"	509-5724	
Gamma 15"	509-5736	
Gamma 15" Subwoofer	509-5748	
Padded Bags		
Bag for Gamma 8"	102-6715	
Bag for Gamma 10"	102-6716	
Bag for Gamma 12"	102-6717	
Bag for Gamma 15"	102-6718	
Bag for Gamma Subwoofer	102-6721	