
# Primary switch mode power supply

Data sheet



## Order data - Accessories

Туре	Description	Order code
CP-RUD	<b>Redundancy unit</b> The CP-RUD provides decoupling of two CP-E power supply units $\leq$ 35 V and $<$ 5 A.	1SVR 423 418 R9000

## Application

The primary switch mode power supply offers two voltage input ranges. This enables the supply with AC or DC. Furthermore it is equipped with two generous capacitors, which ensure mains buffering of at least 30 ms (at 230 V AC). That is why the devices can be used worldwide also in high fluctuating networks and battery-powered plants.

Primary switch mode power supply

Data sheet

### Operating mode

By means of the potentiometer "OUTPUT Adjust" the output voltage can be adjusted within a range of 24 to 28 V DC. Thus, the power supply can be optimally adapted to the application, e.g. compensating the voltage drop caused by a long line length.

The green LED "OUTPUT OK" is lightening during operation.

## Installation

#### Mounting

The switch mode power supply can be snapped on a DIN rail according to IEC/EN 60715 as shown in the accompanying picture. For that the device is set with its mounting rail slide on the upper edge of the mounting rail and locked by lifting it downwards.

#### Demounting


Remove the switch mode power supply as shown in the accompanying picture. For that the latching lever is pulled downwards by means of the screwdriver. Alternatively you can press the unlock button to release the device. Then in both cases the device can be unhinged from the mounting rail edge and removed.


#### Mounting position

The devices have to be mounted horizontally with the input terminals on the bottom. In order to ensure a sufficient convection, the minimum distance to other modules should not be less than 25 mm in vertical and horizontal direction.

#### **Electrical connection**

Connect the input terminals L and N. The protective earth conductor PE must be connected. The installation must be executed acc. to EN 60950, provide a suitable disconnecting device (e. g. line protection switch) in the supply line. The input side is protected by an internal input fuse. Rate the lines for the maximum output current (considering the short-circuit current) or provide a separate fuse protection. We recommend to choose the cable section as large as possible in order to minimize voltage drops. Observe the polarity. The device is overload, short-circuit and open-circuit proof. The secondary side of the power supply unit is electrically isolated from the input and internally not earthed (SELV) and can therefore be earthed by the user according to the needs with L+ or L- (PELV).






ദ

0


Primary switch mode power supply Data sheet

### Connection diagram



Output voltage Input voltage Signalling output for output voltage OK Protective earth

### Wiring instructions



### Safety instructions and warnings



The device must be installed by qualified persons only and in accordance with the specific national regulations (e.g., VDE, etc.). The devices are maintenance-free chassis-mounted units.

#### Disconnect system from supply network!

Before any installation, maintenance or modification work: Disconnect the system from the supply network and protect against switching on.

#### Before start of operation:

Attention! Improper installation/operation may impair safety and cause operational difficulties or destruction of the unit. Before operation the following must be ensured:

- Connect to main according to the specific national regulations.
- Power supply cables and unit must be sufficiently fused. A disconnecting device has to be provided for the power supply to disengage unit and supply cables from supply mains if required.
- The protective earth conductor must be connected to the terminal PE (Protection class I)
- The secondary side of the power supply unit is not earthed and can be earthed by the user according to the needs with L+ or L-.
- Rate the output lines for the output current of the power supply and connect them with the correct polarity.
- In order to ensure sufficient air-cooling the distance to other devices has to be considered.

#### In operation:

- Do not modify the installation (primary and secondary side)! High current! Risk of electric arcs and electric shocks (danger to life)!
- Risk of burns: Depending on the operation conditions the enclosure can become very hot.
- The internal fuse is not user-replaceable. If the internal fuse blows, most probably the device is defective. In this case, an examination of the switch mode power supply by the manufacturer is necessary.

## Attention! High voltage! Danger to life!



The power supplies contain components with high stored energy and circuits with high voltage! Do not introduce any objects into the unit, and do not open the unit. With some units of this range the output is capable of providing hazardous energy. Ensure that the service personnel is protected against inadvertent contact with parts carrying energy.

Primary switch mode power supply Data sheet

## Technical data

Data at  $T_a$  = 25 °C,  $U_{\text{in}}$  = 230 V AC and rated values, unless otherwise indicated

Туре		CP-E 24/1.25	
Input circuit		L, N	
Rated input voltage U <sub>in</sub>		100-240 V AC	
Input voltage range		85-264 V AC / 90-375 V DC	
Frequency range AC		47-63 Hz	
Typical current consumption	at 115 V AC	560 mA	
	at 230 V AC	330 mA	
Typical power consumption		36.7 W	
Inrush current limiting	at 115 V AC	20 A (max. 3 ms)	
	at 230 V AC	40 A (max. 3 ms)	
Discharge current	input / output	0.25 mA	
	input / PE	3.5 mA	
Power failure buffering time	at 115 V AC	min. 20 ms	
	at 230 V AC	min. 30 ms	
Internal input fuse		2 A slow-acting / 250 V AC	
Power factor correction (PFC)		no	
Indication of operational states			
Output voltage	OUTPUT OK: green LED	l: output voltage OK	
Output circuit		L+, L+, L-, L-	
Rated output voltage		24 V DC	
Tolerance of the output voltage		0 +1 %	
Adjustment range of the output voltage	ge	24-28 V DC	
Rated output power		30 W	
Rated output current I <sub>r</sub> $T_a \le 60 \text{ °C}$		1.25 A	
Derating of the output current	$60 \text{ °C} < T_a \leq 70 \text{ °C}$	2.5 %/°C	
Signalling output for output voltage O	K DC OK	Transistor	
Maximum deviation with	load change statical	±0.5 %	
	change of output voltage within the input voltage range	±0.5 %	
Control time		< 2 ms	
Starting time after applying the supply	y voltage at I <sub>r</sub>	max. 1 s	
with 3500 µF		max. 2 s	
Rise time at		max. 150 ms	
	with 3500 µF	max. 500 ms	
Fall time		max. 150 ms	
Residual ripple and switching peaks	BW = 20 MHz	50 mV	
Parallel connection		yes, to enable redundancy	
Series connection		yes, to increase voltage	
Resistance to reverse feed		1 s - max. 35 V DC	
Output circuit - No-load, overload a	and short-circuit behaviour		
Characteristic curve of output		U/I characteristic curve	
Short-circuit protection		continuous short-circuit proof	
Short-circuit behaviour		continuation with output power limiting	
Overload protection		output power limiting	
No-load protection			
No-load protection		continuous no-load stability	

Primary switch mode power supply Data sheet


Туре		CP-E 24/1.25
General data		
Power dissipation		typ. 5.5 W
Efficiency		typ. 86 %
Duty time		100 %
Dimensions (W x H x D)		40.5 x 90 x 114 mm (1.59 x 3.54 x 4.49 in)
Weight		0.27 kg (0.60 lb)
Material of housing		Plastic
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool
Mounting position		horizontal
Minimum distance to other units	horizontal / vertical	25 mm / 25 mm (0.98 in / 0.98 in)
Degree of protection	housing / terminals	IP20 / IP20
Protection class		
Electrical connection - input circuit	/ output circuit	
Wire size	fine-strand with wire end ferrule	
	fine-strand without wire end ferrule	0.2-2.5 mm <sup>2</sup> (24-14 AWG)
	rigid	
Stripping length	<b>3</b> *	6 mm (0.24 in)
Tightening torque		0.6 Nm (5 lb.in)
Environmental data		
Ambient temperature range	operation	-40+70 °C
	rated load	-40+60 °C
	storage	-40+85 °C
Damp heat		95 % RH, without condensation
Vibration (sinusoidal) (IEC/EN 60068-2	2-6)	10-500 Hz, 2 G, along X, Y, Z each axis, 60 min. for each axis
Shock (half-sine) (IEC/EN 60068-2-27)		15 G, 11 ms, 3 axis, 6 faces, 3 times for each face
Isolation data	,	,,,
Rated insulation voltage U <sub>i</sub>	input / output	3 kV AC
	input / PE	1.5 kV AC
Pollution degree		2
Overvoltage category (UL/IEC/EN 609	950-1)	
Standards		
Product standard		EN 61204-3
Low Voltage Directive		2006/95/EC
EMC directive		2004/108/EC
RoHS directive		2002/95/EC
Electrical safety		EN 60950-1, UL 60950-1, UL 508, EN 61558-1, EN 61558-2-17, EN 60204-1
Protective low voltage		SELV (EN 60950)
Electromagnetic compatibility		
Interference immunity to		IEC/EN 61000-6-2
		Level 4 (air discharge 15 kV / contact discharge 8 kV)
electrostatic discharge	IEC/EN 61000-4-2	
electrostatic discharge radiated, radio-frequency, electro- magnetic field	IEC/EN 61000-4-2	Level 3 (10 V/m)
radiated, radio-frequency, electro-		
radiated, radio-frequency, electro- magnetic field	IEC/EN 61000-4-3	Level 3 (10 V/m)
radiated, radio-frequency, electro- magnetic field electrical fast transient / burst	IEC/EN 61000-4-3 IEC/EN 61000-4-4	Level 3 (10 V/m) Level 4 (4 kV / 5 kHz)

## Power supply CP-E 24/1.25 Primary switch mode power supply

Data sheet

Туре		CP-E 24/1.25
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	dip: >95 % 10 ms / >30 % 500 ms interruptions: >95 % 5000 ms
Interference emission		IEC/EN 61000-6-3
high-frequency radiated	IEC/CISPR 22, EN 55022	Class B
high-frequency conducted	IEC/CISPR 22, EN 55022	Class B
limits for harmonic current emissions	IEC/EN 61000-3-2	Class A

### Technical diagrams




Characteristic curve of output at  $T_a = 25 \ ^{\circ}C$ 

The switch mode power supply CP-E 24/1.25 is able to supply at 24 V DC output voltage and

- at an ambient temperature of:
  - ≤ 60 °C a continuous output current of approx. 1.25 A
- at ambient temperatures of:

60 °C < T<sub>a</sub> ≤ 70 °C the output power has to be reduced by 2.5 % per °C temperature increase. If the switch mode power supply is loaded with an output current > 1.25 Å, the operating point is passing through the U/I characteristic curve shown.







Characteristic curve of temperature at rated load

Primary switch mode power supply Data sheet

### Dimensions



# Dimensions accessories



**CP-RUD** 

## **Further Documentation**

Document title	Document type	Document number
Electronic Products and Relays	Technical catalogue	2CDC 110 004 C020x
Power Supply Units	Application manual	2CDC 114 048 M020x
Redundancy unit CP-RUD	Data sheet	2CDC 114 032 D0201

You can find the documentation on the internet at www.abb.com/lowvoltage 
ightarrow Control Products 
ightarrow Power Supplies



As part of the on-going product improvement, ABB reserves the right to modify the characteristics of the products described in this document. The information given is non-contractual. For further details please contact (www.abb.com/contacts) the ABB company marketing these products in your country.

#### ABB STOTZ-KONTAKT GmbH

Eppelheimer Strasse 82, 69123 Heidelberg, Germany Postfach 10 16 80, 69006 Heidelberg, Germany Internet http://www.abb.com/lowvoltage  $\rightarrow$  Control Products

Contact: http://www.abb.com/contacts  $\rightarrow$  Low Voltage Products and Systems