CURRENTWATCHTM SENSORS

ECSJ Series Current Switch CurrentWatch Current Sensors

Contents

Overview 7-9
Model Selection,
Switches 7-10
Model Selection,
Accessories
Wiring Diagrams 7-11
Specifications 7-12
Dimensions 7-13

The CurrentWatch ECSJ Series current operated switches from Eaton's electrical business provide the same dependable indication of status offered by the CurrentWatch ECS Series, but with the added benefit of increased setpoint precision. A choice of three, jumper-selectable input ranges allows the ECSJ Series to be tailored to an application, providing more precise control through improved setpoint resolution. Selfpowering, isolated solid-state outputs, 1 – 6A, 6 – 40A and 40 – 200A input ranges, and a choice of split- or solid-core enclosures are standard.

For typical applications of the Current-Watch ECSJ Series, see listing to the right.

Approvals


- UL Listed
- C-UL Listed

 ϵ

Jumper Selectable AC Switches with Solid-State Output

CurrentWatch™ Current Sensors

ECSJ Series Current Switch



Product Features


- Choice of N.O. or N.C. Solid-State Outputs
 - 1A @ 240V AC
 - 0.15A @ 30V DC
 - 15A @ 120V AC
 - 3A @ 120V AC
 - 0.15A @ 30V DC, Dual Contact
- Self-Powered Cuts installation and operating costs
- Easily Adjustable Setpoint Speeds start-up and reduces inventory
- Solid- or Split-Core Housings Choose the appropriate version for your application
- LED Indication Provides quick visual indication of output contact status
- Built-In Mounting Feet Provide for a secure installation
- UL, C-UL and CE Approved Accepted worldwide

Typical Applications

- Electronic Proof of Flow Current operated switches eliminate the need for multiple pipe or duct penetrations and are more reliable than electromechanical pressure or flow switches
- Conveyors Detect jams and overloads
- Lighting Circuits Easier to install and more accurate than photocells
- Fans, Pumps and Heating Elements Faster response than temperature sensors
- **■** Critical Motors
- Ancillary Equipment

Example Application — CurrentWatch ECSJ Series

Pump Jam & Suction Loss Protection



Model Selection — CurrentWatch ECSJ Series

	Power Supply	Aperture Size	Output Type, Voltage and Rating	Setpoint and LED Configuration	Catalog Number				
Front and Top Terminal Switches									
Solid-Core Housings with Front Terminals	Self-Powered (No External Power Needed)	0.55 in. (14 mm)	Normally Open, 1A @ 240V AC	Adjustable 1 – 6, 6 – 40 or 40 – 175A Setpoint with LED	ECSJ400SC				
			Normally Open, 15A @ 120V AC	Adjustable 1 – 6, 6 – 40 or 40 – 175A Setpoint with LED	ECSJ406SC				
			Normally Closed, 1A @ 240V AC	Adjustable 1 – 6, 6 – 40 or 40 – 175A Setpoint with LED	ECSJ401SC				
			Normally Closed, 15A @ 120V AC	Adjustable 1 – 6, 6 – 40 or 40 – 175A Setpoint with LED	ECSJ407SC				
			Dual Contact, N.O. and N.C., 0.15A @ 30V DC	Adjustable 1 – 6, 6 – 40 or 40 – 175A Setpoint with LED	ECSJ430SC				
			Normally Open, 0.15A @ 30V DC	Adjustable 1 – 6, 6 – 40 or 40 – 175A Setpoint with LED	ECSJ420SC				
				Adjustable 1 – 6, 6 – 40 or 40 – 175A Setpoint with LED	ECSJ424SC				
			Normally Closed, 0.15A @ 30V DC	Adjustable 1 – 6, 6 – 40 or 40 – 175A Setpoint with LED	ECSJ421SC				
Solid-Core Housings with Top Terminals		0.74 in. (19 mm)	Normally Open, 3A @ 120V AC	Adjustable 1 – 6, 6 – 40 or 40 – 175A Setpoint with LED	ECSJ404SC				
			Normally Closed, 3A @ 120V AC	Adjustable 1 – 6, 6 – 40 or 40 – 175A Setpoint with LED	ECSJ405SC				
Split-Core Housings		0.85 in. (21.6 mm)	Normally Open, 1A @ 240V AC	Adjustable 1.75 – 6, 6 – 40 or 40 – 200A Setpoint with LED	ECSJ402SP				
			Normally Closed, 1A @ 240V AC	Adjustable 1.75 – 6, 6 – 40 or 40 – 200A Setpoint with LED	ECSJ403SP				
			Normally Open, 0.15A @ 30V DC	Adjustable 1.75 – 6, 6 – 40 or 40 – 200A Setpoint with LED	ECSJ422SP				
			Normally Closed, 0.15A @ 30V DC	Adjustable 1.75 – 6, 6 – 40 or 40 – 200A Setpoint with LED	ECSJ423SP				

Specifications — CurrentWatch ECSJ Series

CurrentWatch™ Current Sensors

ECSJ Series Current Switch

Specifications — C	urrentWatch ECS.	J Series							
Description	AC Solid-State Out	AC Solid-State Output DC Solid-State Output							
Power Supply		Self-Powered — No Power Supply Needed							
Output		Isolated Solid-State Switch							
Output Rating	1.0A @ 240V AC High Current Swi ECSJ404SC and Very High Currer ECSJ406SC and 15A @ 240V AC	Standard Models: 1.0A @ 240V AC High Current Switching Models: ECSJ404SC and ECSJ405SC: 3.0A @ 120V AC Very High Current Switching Models: ECSJ406SC and ECSJ407SC: 15A @ 240V AC 10A @ 240V AC							
Off-State Leakage	N.O. Models: < 10 N.C. Models: 2.5		N.O. Models: < 10 µA N.C. Models: 1.4 mA						
Response Time		40 – 120 mS							
Setpoint Range (Adjustable)		Solid-Core Models: 1 – 6, 6 – 40 and 40 – 175A Split-Core Models: 1.75 – 6, 6 – 40 and 40 – 200A							
Hysteresis		Low: 6%; Mid: 4%; High: 3%							
Overload	Housing	Range	Range Maxim		num Amps				
			6 sec.		1 sec.				
	Solid-Core	1 – 6 A	400 A		600 A				
		6 – 40 A	500 A		800 A				
		40 – 175 A	800 A		1200 A				
	Split-Core	1.75 – 6 A	400 A		600 A				
		6 – 40 A	500 A		800 A				
		40 – 200 A	800 A		1200 A				
Isolation Voltage		UL Listed to 1,270V AC, tested to 5,000V AC							
Frequency Range		6 – 100 Hz							
Sensing Aperture		Solid-Core, Front Terminal Models: 0.55 in. (14 mm) Solid-Core, Top Terminal Models: 0.74 in. (19 mm) Split-Core Models: 0.85 in. (21.6 mm) sq.							
Housing		UL94 V0 Flammability Rated							
Environmental		Operating Temperature: -58 to 122°F (-50 to 50°C) Humidity: 0 – 95% RH, Non-condensing							
Approvals	UL 508 Ir	UL 508 Industrial Control Equipment (USA and Canada), CE Certified							

Approximate Dimensions — CurrentWatch ECSJ Series

Cutler-Hammer

