



SAFETY DATA SHEET FLUXCLENÉ Aerosol

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME FLUXCLENÉ Aerosol
PRODUCT NO. FLU-a
EFLU200D
EFLU400D
ZE
APPLICATION Manufacture of electrical equipment
SUPPLIER ELECTROLUBE. A division of
HK WENTWORTH LTD
ASHBY PARK, COALFIELD
WAY,
ASHBY DE LA ZOUCH,
LEICESTERSHIRE LE65 1JR
UNITED KINGDOM
+44 (0)1530 419600
+44 (0)1530 416640
info@hkw.co.uk
EMERGENCY TELEPHONE +44 (0)1530 419600 between 8.30am - 5.00pm Mon – Fri

2 HAZARDS IDENTIFICATION

Highly flammable.

Vapours may cause drowsiness and dizziness.

Irritating to eyes and skin.

Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

CLASSIFICATION (1999/45) Xi;R36/38. F;R11. N;R50/53. R67.

ENVIRONMENT

Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. Do not empty into drains, dispose of this material and its container at hazardous or special waste collection point. Use appropriate containment to avoid environmental contamination. Avoid release to the environment. Refer to special instructions/safety data sheets.

Dispose of waste and residues in accordance with local authority requirements.

PHYSICAL AND CHEMICAL HAZARDS

Aerosol containers can explode when heated, due to excessive pressure build-up. When sprayed on a naked flame or any incandescent material the aerosol vapours can be ignited.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content %	Classification (67/548/EEC)
CYCLOHEXANE	203-806-2	110-82-7	30-60%	F;R11 Xn;R65 Xi;R38 R67 N;R50/53
PROPAN-2-OL	200-661-7	67-63-0	10-30%	F;R11 Xi;R36 R67
1-METHOXY-2-PROPANOL	203-539-1	107-98-2	10-30%	R10 R67
HEXANE MIXTURE OF ISOMERS (MAX 5% n-HEXANE (203-777-6))	-	-	5-10%	F;R11 Xn;R65 Xi;R38 R67 N;R51/53
HEPTANE	205-563-8	142-82-5	1-5%	F;R11 Xn;R65 Xi;R38 R67 N;R50/53
Orange Terpenes	232-433-8	8028-48-6	1-5%	Xn;R65. Xi;R38. R10,R52/53.
HEXANE-norm	203-777-6	110-54-3	< 1%	F;R11 Repr. Cat. 3;R62 Xn;R48/20,R65 Xi;R38 R67 N;R51/53

The Full Text for all R-Phrases is Displayed in Section 16

FLUXCLENE Aerosol

COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels

4 FIRST-AID MEASURES

NOTES TO THE PHYSICIAN

Treat symptomatically

INHALATION

Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention. Get medical attention.

INGESTION

Not relevant.

SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

SPECIAL FIRE FIGHTING PROCEDURES

Move container from fire area if it can be done without risk.

UNUSUAL FIRE & EXPLOSION HAZARDS

Aerosol cans may explode in a fire.

6 ACCIDENTAL RELEASE MEASURES

SPILL CLEAN UP METHODS

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Absorb in vermiculite, dry sand or earth and place into containers.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Avoid spilling, skin and eye contact. Provide good ventilation.

STORAGE PRECAUTIONS

Store at moderate temperatures in dry, well ventilated area.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
		ppm	mg/m ³	ppm	mg/m ³	
1-METHOXY-2-PROPANOL	WEL	100 ppm	375 mg/m ³	150 ppm	560 mg/m ³	Sk
CYCLOHEXANE	WEL	100 ppm	350 mg/m ³	300 ppm	1050 mg/m ³	
HEPTANE	WEL	500 ppm				
PROPAN-2-OL	WEL	400 ppm	999 mg/m ³	500 ppm	1250 mg/m ³	

WEL = Workplace Exposure Limit.

Sk = Can be absorbed through skin.

PROTECTIVE EQUIPMENT



EYE PROTECTION

Wear approved, tight fitting safety glasses where splashing is probable.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

FLUXCLENE Aerosol

HYGIENE MEASURES

Wash at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke. DO NOT SMOKE IN WORK AREA!

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Aerosol Liquid
COLOUR	Colourless
ODOUR	Lemon
VOLATILITY DESCRIPTION	Volatile.
SOLUBILITY	Insoluble in water
BOILING POINT (°C)	>80 (176 F)
MELTING POINT (°C)	<-29 (-20.2 F)
RELATIVE DENSITY	0.780 @ 20 °C (68 F)
VAPOUR PRESSURE	11.52 kPa @ 20 °C (68 F)
FLASH POINT (°C)	0 (32 F) CC (Closed cup).
AUTO IGNITION TEMPERATURE (°C)	> 200 (392 F)
FLAMMABILITY LIMIT - LOWER(%)	0.6
FLAMMABILITY LIMIT - UPPER(%)	8.3

10 STABILITY AND REACTIVITY

STABILITY

Stable under normal temperature conditions.

CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition. Avoid contact with acids and alkalis.

11 TOXICOLOGICAL INFORMATION

INHALATION

Vapours may cause headache, fatigue, dizziness and nausea. High concentrations of vapours may irritate respiratory system and lead to headache, fatigue, nausea and vomiting.

SKIN CONTACT

May cause sensitisation by skin contact. Prolonged or repeated exposure may cause severe irritation. Product has a defatting effect on skin. Prolonged contact may cause dryness of the skin.

EYE CONTACT

Irritating to eyes.

OTHER HEALTH EFFECTS

This substance has no evidence of carcinogenic properties.

ROUTE OF ENTRY

Skin and/or eye contact. Inhalation.

Name	HEPTANE
Toxic Dose 1 - LD 50	222 mg/kg (ivn-mouse)
Toxic Conc. - LC 50	103 ppm/4h (inh-rat)
Name	CYCLOHEXANE
Toxic Dose 1 - LD 50	12705 mg/kg (oral rat)
Toxic Dose 2 - LD 50	813 mg/kg (oral-mouse)
Name	HEXANE-norm
Toxic Dose 1 - LD 50	28700 mg/kg (oral rat)
Toxic Conc. - LC 50	48000 ppm/4h (inh-rat)
Name	PROPAN-2-OL
Name	1-METHOXY-2-PROPANOL
Toxic Dose 1 - LD 50	5200 mg/kg (oral rat)
Toxic Dose 2 - LD 50	11700 mg/kg (oral-mouse)
Name	Orange Terpenes
Toxic Dose 1 - LD 50	>5000 mg/kg (oral rat)

12 ECOLOGICAL INFORMATION

FLUXCLENE Aerosol

ECOTOXICITY

Dangerous for the environment if discharged into watercourses.

Name	HEPTANE
LC 50, 96 Hrs, Fish mg/l	4.924
Name	CYCLOHEXANE
LC 50, 96 Hrs, Fish mg/l	42.3
Name	PROPAN-2-OL
	1-METHOXY-2-PROPANOL
LC 50, 96 Hrs, Fish mg/l	20800
EC 50, 48 Hrs, Daphnia, mg/l	23300
Name	Orange Terpenes
EC 50, 48 Hrs, Daphnia, mg/l	12.3

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements. Empty containers must not be burned because of explosion hazard.

14 TRANSPORT INFORMATION



PROPER SHIPPING NAME	AEROSOLS (CYCLOHEXANE)
PROPER SHIPPING NAME	CONSUMER COMMODITY
UN NO. ROAD	1950
ADR CLASS NO.	2
ADR CLASS	Class 2: Gases
ADR PACK GROUP	N/A
TUNNEL RESTRICTION CODE	(D)
ADR LABEL NO.	2.1
UN NO. SEA	1950
IMDG CLASS	2.1
IMDG PACK GR.	N/A
EMS	F-D, S-U
UN NO. AIR	1950
AIR CLASS	2.1
AIR PACK GR.	N/A

15 REGULATORY INFORMATION

LABELLING



Irritant



Highly Flammable



Dangerous for the environment

RISK PHRASES

R11	Highly flammable.
R36/38	Irritating to eyes and skin.
R50/53	Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R67	Vapours may cause drowsiness and dizziness.

FLUXCLENE Aerosol

SAFETY PHRASES

A1	Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.
A2	Do not spray on a naked flame or any incandescent material.
S2	Keep out of the reach of children.
S9	Keep container in a well-ventilated place.
S16	Keep away from sources of ignition - No smoking.
S23	Do not breathe vapour/spray.
S24/25	Avoid contact with skin and eyes.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S37	Wear suitable gloves.
S38	In case of insufficient ventilation, wear suitable respiratory equipment.
S57	Use appropriate containment to avoid environmental contamination.
S61	Avoid release to the environment. Refer to special instructions/safety data sheets.

UK REGULATORY REFERENCES

Chemicals (Hazard Information & Packaging) Regulations.

The Control of Substances Hazardous to Health Regulations 2002 (S.I 2002 No. 2677) with amendments.

ENVIRONMENTAL LISTING

Rivers (Prevention of Pollution) Act 1961. Control of Pollution Act 1974.

EU DIRECTIVES

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

GUIDANCE NOTES

Workplace Exposure Limits EH40.

16 OTHER INFORMATION

ISSUED BY

Helen O'Reilly

REVISION DATE

FEBRUARY 2012

REV. NO./REPL. SDS

4

GENERATED

SDS NO.

10371

FLUXCLENE Aerosol

RISK PHRASES IN FULL

R10	Flammable.
R52/53	Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R48/20	Harmful: danger of serious damage to health by prolonged exposure through inhalation.
R65	Harmful: may cause lung damage if swallowed.
R11	Highly flammable.
R36	Irritating to eyes.
R38	Irritating to skin.
R62	Possible risk of impaired fertility.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R67	Vapours may cause drowsiness and dizziness.
R50/53	Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.