

# V4N

## Snap-action Microswitches

Subminiature

### V4N

- Characteristics
- Peg mounting option
  - Solder terminals
  - 2.8 mm faston (quick connect) terminals
  - PCB terminals
  - Sealed (IP 67) / unsealed (IP 40)
  - Pre-wired option
  - Snap-on terminal covers

Dimensions (mm)

V4N	20 × 10,3 × 6,4
V4NS	20 × 16,6 × 6,4

Actuator Plunger, plain lever, roller lever

Approvals UL, CSA and ENEC




### Preferred Range

Ordering Reference	Actuating Force (N) (ozf)		Sealing	Operating pos. (mm) (in)		Terminal	Circuit	Actuator	Contacts	Electrical rating
V4NT7UL	1,40	5,0	IP40	8,40	0,33	Solder	CO	Plain plunger	Silver	250 VAC, 5 A
V4NST7UL	2,50	9,0	IP67	8,40	0,33	Solder	CO	Plain plunger	Silver	250 VAC, 5 A
V4NSUL	2,50	9,0	IP67	8,40	0,33	Pre-wired	CO	Plain plunger	Silver	250 VAC, 5 A
V4NT7Y1UL	0,50	1,8	IP40	10,7	0,42	Solder	CO	Straight lever	Silver	250 VAC, 5 A
V4NST7Y1UL	0,90	3,2	IP67	10,6	0,42	Solder	CO	Straight lever	Silver	250 VAC, 5 A
V4NSY1UL	0,90	3,2	IP67	10,6	0,42	Pre-wired	CO	Straight lever	Silver	250 VAC, 5 A
V4NT7YRUL	0,50	1,8	IP40	15,7	0,62	Solder	CO	Roller lever	Silver	250 VAC, 5 A
V4NST7YRUL	0,90	3,2	IP67	15,6	0,62	Solder	CO	Roller lever	Silver	250 VAC, 5 A
V4NSYRUL	0,90	3,2	IP67	15,6	0,62	Pre-wired	CO	Roller lever	Silver	250 VAC, 5 A


Specifications

Housing	Flame-retardant glass-fibre reinforced nylon
Plunger	Polyacetal (POM)
Mechanism	Snap-action coil spring mechanism with stainless steel spring
Functions	Change-over, normally-closed or normally-open
Contacts	Silver
Terminals	Gold flashed
Temperature range °C	-40°C to +85°C
Mechanical life	5 × 10 <sup>6</sup> cycles minimum (impact free actuation) for the cowl 3 × 10 <sup>6</sup>
Protection	IP40 (V4N - enclosure), IP67 (V4NS - enclosure)
Mounting	Side mounting
Actuators	Plain lever, Roller lever
Accessories	Insulating sheet - N04619, Clip-on terminal cover - TC102, Long overtravel actuator - QA4

Circuit diagram






Dimensions



Recommended maximum electrical ratings

	Voltage (max)	Load (A)	Inductive load (A)	Approval
V4NT7UL/ V4NST7-UL	250 VAC	5 (0.75 pf)		UL 1054/CSA 22.2 No. 55 - 6,000 operations - 65°C EN61058-1, T85, 10,000 operations
	250 VAC	5	2	
	0 - 15 VDC	5	3	General rating - 50,000 operations (85°C)
	15 - 30 VDC	5	3	General rating - 50,000 operations (85°C)
V4NS-UL	250 VAC	3 (0.75 pf)		UL 1054/CSA 22.2 No. 55 - 6,000 operations - 65°C EN61058-1, T85, 10,000 operations
	250 VAC	5	2	
	0 - 15 VDC	3	3	General rating - 50,000 operations (85°C)
	15 - 30 VDC	3	3	General rating - 50,000 operations (85°C)

Operating Characteristics

Actuator	Reference	Actuating Force		Release Force		Free Position		Operating Position		Movement Differential	
		Maximum (N)	(ozf)	Minimum (N)	(ozf)	Maximum (mm)	(in)	(mm)	(in)	Maximum (mm)	(in)
Plunger 	V4NT7UL	1,4	5,00	0,28	1,00	9,2	0,36	8,4 ± 0,3	0,33 ± 0,012	0,1	0,004
	V4NST7UL	2,5	9,00	0,30	1,00	9,2	0,36	8,4 ± 0,3	0,33 ± 0,012	0,1	0,004
	V4NSUL	2,5	9,00	0,3	1,00	9,2	0,36	8,4 ± 0,3	0,33 ± 0,012	0,1	0,004
Y1 lever 	V4NT7Y1UL	0,5	1,80	0,07	0,25	13,2	0,52	10,7 ± 1,0	0,42 ± 0,04	0,4	0,016
	V4NST7Y1UL	0,9	3,20	0,07	0,25	13,2	0,52	10,6 ± 1,2	0,42 ± 0,05	0,4	0,016
	V4NSY1UL	0,9	3,20	0,07	0,25	13,2	0,52	10,6 ± 1,2	0,42 ± 0,05	0,4	0,016
Width of lever 4.0 mm/0.16 in											
YR lever 	V4NT7YRUL	0,5	1,80	0,07	0,25	17,8	0,70	15,7 ± 1,0	0,62 ± 0,04	0,4	0,016
	V4NST7YRUL	0,9	3,20	0,07	0,25	17,8	0,70	15,6 ± 1,2	0,61 ± 0,05	0,4	0,016
	V4NSYRUL	0,9	3,20	0,07	0,25	17,8	0,70	15,6 ± 1,2	0,61 ± 0,05	0,4	0,016
Width of lever 4.0 mm/0.16 in											

Over travel: Plunger can be depressed flush with housing. The housing should not be used as an end stop.

## Ordering Reference

Type	V4N	
Type of sealing	No symbol	Unsealed standard travel
E	Unsealed	with extended overtravel (0,5 mm)
S	Sealed IP67	standard travel
B	Sealed IP67	with extended overtravel (0,5 mm)
Terminals	No symbol	Pre-wired 500 mm with cable box (V4NS/B only)
T6	Faston	2.03 × 0.5 × 6.6 long
T7	Solder	2.95 × 0.5 × 3.6 long
T8	PCB	0.8 × 0.5 × 4.0 long
T9	Faston	2.8 × 0.5 × 8.1 long
T81	Bent PCB	0.8 × 0.5 × 3.8 long
T82	Bent PCB	0.8 × 0.5 × 3.8 long
T84	Short PCB	0.8 × 0.5 × 2.0 long
T85	Long PCB	0.8 × 0.5 × 6.85 long
T11	Solder	2.95 × 0.5 × 3.6 long
Circuit	No symbol	Change-over
C2	Normally closed	
C4	Normally open	
Actuators	No symbol	Without lever
Y1	Plain lever	18.0 mm
Y2	Plain lever	25.0 mm
Y3	Plain lever	32.0 mm
YC	Cam follower lever	18.5 mm
YR	Roller lever	16.0 mm
A1	Plain lever	18.0 mm
A2	Plain lever	25.0 mm
A3	Plain lever	32.0 mm
AC	Cam follower lever	18.5 mm
AR	Roller lever	16.0 mm
Actuator Position	No symbol	Without lever, or lever fitted at the end nearest to the Plunger
0	With lever fitted at end opposite to plunger	
Contact Material	No symbol	Fine silver
G	Gold plate on silver	
X	Gold alloy on silver palladium crosspoint	
Approvals	No symbol	Without approval
UL	UL, CSA and ENEC approval	