

Inductors, Epoxy Conformal Coated, Uniform Roll Coated, Axial Leaded



ELECTRICAL SPECIFICATIONS

Inductance Tolerance: $\pm 5\%$, $\pm 10\%$, $\pm 20\%$

Other tolerances available on request

Insulation Resistance: 1000 M Ω minimum per MIL-STD-202, method 302, test condition B

Operating Temperature: - 55 °C to + 105 °C

MATERIAL SPECIFICATIONS

Coating: Epoxy-uniform roll coated

Lead: Tinned copper

Core: Ferrite

MECHANICAL SPECIFICATIONS

Terminal Strength: 5 pounds pull per MIL-STD-202, method 211, test condition A

Weight: IRF-1 = 0.3 g maximum

IRF-3 = 0.6 g maximum

TEST EQUIPMENT ⁽¹⁾

- H/P 4342A Q-meter
- Measurements corporation megacycle meter, model 59
- Whearstone bridge


Note

⁽¹⁾ Test procedures per MIL-PRF-15305

FEATURES

- Flame-retardant coating and color band identification 
- Uniform coating is excellent for automatic insertion **RoHS**
- Available in bulk, ammo and reel pack per EIA COMPLIANT RS/296
- Superior electrical specifications high Q and self resonant frequency, low DC resistance, high rated DC current
- Compliant to RoHS directive 2002/95/EC

DIMENSIONS in inches [millimeters]



MODEL	A (Max.)	B (Max.)	C (Max.)	D
IRF-1	0.260 [6.60]	0.120 [3.05]	0.330 [8.38]	0.0200 $\pm$ 0.0015 [0.508 $\pm$ 0.038]
IRF-3	0.385 [9.78]	0.165 [4.19]	0.410 [10.41]	0.025 $\pm$ 0.002 [0.635 $\pm$ 0.051]

ENVIRONMENTAL PERFORMANCE

TEST	CONDITIONS	SPECIFICATIONS
Flammability	-	MIL-STD-202, Method 111
Overload	-	MIL-PRF-15305
Resistance to Soldering Heat	Test Condition A	MIL-STD-202, Method 210
Resistance to Solvents	-	MIL-STD-202, Method 215

STANDARD ELECTRICAL SPECIFICATIONS

MODEL	IND. (μ H)	TOL.	Q MIN.	TEST FREQ. L AND Q (MHz)	SELF-RESONANT FREQ MIN. (MHz) ⁽¹⁾	DCR MAXIMUM (Ω)	RATED DC CURRENT (mA) ⁽²⁾
IRF-1	0.10	$\pm 20\%$	40	25.0	400.0	0.06	1350
IRF-1	0.12	$\pm 20\%$	40	25.0	400.0	0.06	1270
IRF-1	0.15	$\pm 20\%$	40	25.0	400.0	0.07	1200
IRF-1	0.18	$\pm 20\%$	40	25.0	400.0	0.075	1155
IRF-1	0.22	$\pm 20\%$	40	25.0	380.0	0.075	1150
IRF-1	0.27	$\pm 20\%$	40	25.0	360.0	0.08	1110
IRF-1	0.33	$\pm 20\%$	40	25.0	350.0	0.08	1110
IRF-1	0.39	$\pm 20\%$	40	25.0	320.0	0.09	1000
IRF-1	0.47	$\pm 20\%$	40	25.0	300.0	0.10	1000
IRF-1	0.56	$\pm 20\%$	40	25.0	280.0	0.11	950
IRF-1	0.68	$\pm 20\%$	40	25.0	250.0	0.12	900
IRF-1	0.82	$\pm 20\%$	40	25.0	200.0	0.12	900
IRF-1	1.0	$\pm 10\%$	50	25.0	180.0	0.15	815
IRF-1	1.2	$\pm 10\%$	50	7.9	165.0	0.18	740
IRF-1	1.5	$\pm 10\%$	50	7.9	150.0	0.20	700
IRF-1	1.8	$\pm 10\%$	50	7.9	125.0	0.23	655
IRF-1	2.2	$\pm 10\%$	50	7.9	115.0	0.25	630
IRF-1	2.7	$\pm 10\%$	50	7.9	100.0	0.28	595
IRF-1	3.3	$\pm 10\%$	50	7.9	90.0	0.30	575
IRF-1	3.9	$\pm 10\%$	50	7.9	80.0	0.32	555
IRF-1	4.7	$\pm 10\%$	50	7.9	75.0	0.35	530
IRF-1	5.6	$\pm 10\%$	50	7.9	65.0	0.40	500
IRF-1	6.8	$\pm 10\%$	50	7.9	60.0	0.45	470
IRF-1	8.2	$\pm 10\%$	50	7.9	55.0	0.55	425
IRF-1	10.0	$\pm 10\%$	50	7.9	50.0	0.72	370
IRF-1	12.0	$\pm 10\%$	50	2.5	40.0	0.80	350
IRF-1	15.0	$\pm 10\%$	50	2.5	35.0	0.88	335
IRF-1	18.0	$\pm 10\%$	50	2.5	30.0	1.0	315
IRF-1	22.0	$\pm 10\%$	50	2.5	25.0	1.2	285
IRF-1	27.0	$\pm 10\%$	50	2.5	20.0	1.35	270

STANDARD ELECTRICAL SPECIFICATIONS

MODEL	IND. (μ H)	TOL.	Q MIN.	TEST FREQ. L AND Q (MHz)	SELF-RESONANT FREQ MIN. (MHz) ⁽¹⁾	DCR MAXIMUM (Ω)	RATED DC CURRENT (mA) ⁽²⁾
IRF-1	33.0	$\pm 10\%$	50	2.5	24.0	1.5	255
IRF-1	39.0	$\pm 10\%$	50	2.5	22.0	1.7	240
IRF-1	47.0	$\pm 10\%$	60	2.5	20.0	2.3	205
IRF-1	56.0	$\pm 10\%$	60	2.5	18.0	2.6	195
IRF-1	68.0	$\pm 10\%$	60	2.5	15.0	2.9	185
IRF-1	82.0	$\pm 10\%$	60	2.5	14.0	3.2	175
IRF-1	100.0	$\pm 10\%$	60	2.5	13.0	3.5	165
IRF-1	120.0	$\pm 10\%$	60	0.79	5.40	3.8	160
IRF-1	150.0	$\pm 10\%$	60	0.79	4.75	4.4	150
IRF-1	180.0	$\pm 10\%$	60	0.79	4.35	5.0	140
IRF-1	220.0	$\pm 10\%$	60	0.79	4.0	5.7	130
IRF-1	270.0	$\pm 10\%$	60	0.79	3.70	6.5	120
IRF-1	330.0	$\pm 10\%$	60	0.79	3.40	9.5	100
IRF-1	390.0	$\pm 10\%$	60	0.79	2.80	10.5	95
IRF-1	470.0	$\pm 10\%$	60	0.79	2.55	11.6	90
IRF-1	560.0	$\pm 10\%$	60	0.79	2.35	13.0	85
IRF-1	680.0	$\pm 10\%$	60	0.79	2.0	18.0	75
IRF-1	820.0	$\pm 10\%$	60	0.79	1.85	23.0	65
IRF-1	1000.0	$\pm 10\%$	60	0.79	1.40	26.0	60
IRF-3	0.22	$\pm 20\%$	55	25.0	380.0	0.10	1400
IRF-3	0.27	$\pm 20\%$	55	25.0	340.0	0.11	1320
IRF-3	0.33	$\pm 20\%$	55	25.0	300.0	0.12	1280
IRF-3	0.39	$\pm 20\%$	55	25.0	280.0	0.13	1200
IRF-3	0.47	$\pm 20\%$	55	25.0	250.0	0.14	1150
IRF-3	0.56	$\pm 20\%$	55	25.0	230.0	0.15	1100
IRF-3	0.68	$\pm 20\%$	55	25.0	210.0	0.16	1030
IRF-3	0.82	$\pm 20\%$	55	25.0	172.0	0.17	980
IRF-3	1.0	$\pm 10\%$	55	25.0	157.0	0.19	920
IRF-3	1.2	$\pm 10\%$	50	7.9	144.0	0.21	880
IRF-3	1.5	$\pm 10\%$	50	7.9	131.0	0.23	830
IRF-3	1.8	$\pm 10\%$	55	7.9	121.0	0.25	790
IRF-3	2.2	$\pm 10\%$	55	7.9	110.0	0.28	750
IRF-3	2.7	$\pm 10\%$	60	7.9	100.0	0.30	720
IRF-3	3.3	$\pm 10\%$	65	7.9	94.0	0.34	670
IRF-3	3.9	$\pm 10\%$	65	7.9	86.0	0.37	640
IRF-3	4.7	$\pm 10\%$	70	7.9	80.0	0.39	620
IRF-3	5.6	$\pm 10\%$	70	7.9	74.0	0.43	590
IRF-3	6.8	$\pm 10\%$	75	7.9	68.0	0.48	550
IRF-3	8.2	$\pm 10\%$	80	7.9	53.0	0.52	530
IRF-3	10.0	$\pm 10\%$	85	7.9	45.0	0.58	500
IRF-3	12.0	$\pm 10\%$	75	2.5	42.0	0.63	480
IRF-3	15.0	$\pm 10\%$	70	2.5	40.0	0.72	460
IRF-3	18.0	$\pm 10\%$	65	2.5	34.0	0.77	430
IRF-3	22.0	$\pm 10\%$	60	2.5	30.0	0.84	410
IRF-3	27.0	$\pm 10\%$	55	2.5	25.0	0.94	390
IRF-3	33.0	$\pm 10\%$	55	2.5	19.0	1.03	370
IRF-3	39.0	$\pm 10\%$	50	2.5	14.5	1.12	350
IRF-3	47.0	$\pm 10\%$	45	2.5	13.0	1.22	340
IRF-3	56.0	$\pm 10\%$	40	2.5	12.0	1.34	320
IRF-3	68.0	$\pm 10\%$	40	2.5	11.0	1.47	305
IRF-3	82.0	$\pm 10\%$	35	2.5	10.3	1.62	290
IRF-3	100.0	$\pm 10\%$	30	2.5	9.5	1.8	275
IRF-3	120.0	$\pm 10\%$	70	0.79	3.8	3.7	185
IRF-3	150.0	$\pm 10\%$	70	0.79	3.5	4.2	175
IRF-3	180.0	$\pm 10\%$	70	0.79	3.3	4.6	165
IRF-3	220.0	$\pm 10\%$	70	0.79	3.0	5.1	155
IRF-3	270.0	$\pm 10\%$	70	0.79	2.8	5.8	145
IRF-3	330.0	$\pm 10\%$	70	0.79	2.6	6.4	137
IRF-3	390.0	$\pm 10\%$	65	0.79	2.4	7.0	133
IRF-3	470.0	$\pm 10\%$	65	0.79	2.25	7.7	126
IRF-3	560.0	$\pm 10\%$	65	0.79	2.1	8.5	120
IRF-3	680.0	$\pm 10\%$	65	0.79	1.95	9.4	113
IRF-3	820.0	$\pm 10\%$	65	0.79	1.85	10.5	105
IRF-3	1000.0	$\pm 10\%$	65	0.79	1.4	14.0	100

Notes⁽¹⁾ Measured with full length lead⁽²⁾ Rated DC Current based on maximum temperature rise of 15 °C at + 90 °C ambient

**ORDERING INFORMATION**

IRF-1	10 μH	$\pm 10 \%$	ER	e2
MODEL	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC LEAD (Pb)-FREE STANDARD

GLOBAL PART NUMBER INFORMATION

I	R	F	0	1	E	R	1	0	0	K
MODEL					PACKING CODE		INDUCTANCE VALUE			TOL.



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.