


Item no.: 231-302/026-000  
 Product description: Female plug 2 pole pin spacing 5.08 mm / 0.2 in with codig fingers closed end



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	3 (Multi Conn. System)
Weight	3.81 g
Color	orange
No. of connection Points	2
No. of potentials	2
pole count	2
Height	14.3 mm
Height	0.563 in
Width	11.66 mm
Width	0.459 in
Depth	26.45 mm
Depth	1.041 in
Pin spacing from	5.08 mm
Pin spacing from	0.2 in
Rating based on	IEC/EN 60664-1
Overvoltage category EN I	III
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	4 kV

Current intensity EN  
Overvoltage category EN II  
Pollution degree

16 A  
II  
2



Measured voltage EN	630 V
Measured shock voltage	4 kV
Current intensity EN	16 A
Overvoltage category EN III	III
Degree of pollution	3
Rated voltage EN	320 V
Rated surge voltage	4 kV
Nominal current	16 A
Connection method	CAGE CLAMP®CONNECTION
Cross section [mm²]	0.08 - 2.5 mm²
Wiring method	solid
Cross section [mm²]	0.08 - 2.5 mm²
Wiring method	fine-stranded
Cross section [mm²]	0.25 - 1.5 mm²
Wiring method	fine-stranded (with ferrule and plastic collar)
Cross section [mm²]	0.25 - 2.5 mm²
Wiring method	fine-stranded (with ferrule, without plastic collar)
Cross section [AWG]	28 - 12 AWG
Strip length from	8 mm
Strip length to	9 mm
Strip length from [inch]	0.31 in
Strip length up to [inch]	0.35 in



Material group	I
Insulating material	PA 6.6
Temperature stability	-60 °C to +85 °C
Flammability category, based on UL 94	V0
Clamping spring material	Nickel-chromium spring steel (CrNi)
Contact material	Copper base alloy
Contact plating	tin-plated
xxx-xxx/032-000	Strain relief plate 11,5 mm



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
231-302/026-000	ABS	04-HG469925/1-PDA	400	16	0,08-2,5
231-302/026-000	BV	11915/A0	400	16	2,5
231-302/026-000	CCA	5764	250	16	0,08-2,5
231-302/026-000	CSA	154112-1466354	300	15	22-12
231-302/026-000	GL	17296-00HH	400	16	0,08-2,5
231-302/026-000	KEMA	2083746.02	250	16	0,08-2,5
231-302/026-000	KR	HMB05880-EL003	250/400/600	12/16	2,5
231-302/026-000	LR	96/20035	400	16	0,08-2,5
231-302/026-000	RMR	11130002	400	16	0,08-2,5
231-302/026-000	UR	E45171	600	15	28-12
231-302/026-000	UR	E45172	300	15	22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected