



TLS 2200®/TLS PC Link™ Labels - # PTL-17-498

MATERIAL:	Repositionable Vinyl Cloth
SIZE:	1.000" W x 0.500" H (25.400 mm W x 12.700 mm H)
QTY/UOM:	500/Roll
CATALOG #:	PTL-17-498
PRODUCT #:	62663

OVERVIEW **SPECIFICATIONS**

Description for TLS 2200®/TLS PC Link™ Labels

Labels for the TLS 2200® & TLS-PC Link™ Thermal Transfer Portable Printers. Please Note: This material is UL recognized with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.

Specification Of TLS 2200®/TLS PC Link™ Labels

Application(s): Bottles, Circuit Board & Component ID, Conical Tube, Deep Well Plate, Laboratory Identification, Panel Identification, Petri Dish, Through Hole - Top, Wire & Cable Marking

Agency Approval(s)/Compliance: UL Recognized

Size: 1.000" W x 0.500" H (25.400 mm W x 12.700 mm H)

Printable Area: 1.000" W x 0.500" H (25.400 mm W x 12.700 mm H)

Max Characters Per Line For Font #2: 24

Max Lines of Text For Font #2: 5

Label Type/Style: Label

Color: White

Wire Gauge: 12 to 10

Finish: Semi-Gloss

Qty Per Row: 1

Material Type: Vinyl Cloth

Material Description: Repositionable Vinyl Cloth

Brady Material #: [B-498](#)

Safety Catalog: [pg. 117](#)

General ID Catalog: [pg. 31](#)

Recommended Ribbon Series: R6210

Suggested Ribbon Part#: R6210

Acceptable Ribbon Series: R4310

After Process: Yes, this material will work with this application

Environment: Freezer

Printer Compatibility: BMP71, TLS 2200, TLS-PC Link

Surface: Smooth, Textured/Rough

Surface Mount Technology: No, this material does not work with this application

Through Hole Technology: Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No

Special Properties: Repositionable

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 500/Roll