

TLS 2200®/TLS PC Link™ Labels - # PTL-29-498

SIZE:	1.500" W x 0.500" H (38.100 mm W x 12.700 mm H)
MATERIAL:	Repositionable Vinyl Cloth
QTY/UOM:	500/Roll
CATALOG #:	PTL-29-498
PRODUCT #:	62669



OVERVIEW **SPECIFICATIONS**

Description for TLS 2200®/TLS PC Link™ Labels

Labels for the TLS 2200® & TLS-PC Link™ Thermal Transfer Portable Printers. Please Note: This material is UL recognized with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.

Specification Of TLS 2200®/TLS PC Link™ Labels

Application(s):	Bottles, Circuit Board & Component ID, Conical Tube, Cryo Vial, Deep Well Plate, Laboratory Identification, Panel Identification, Petri Dish, Through Hole - Top, Wire & Cable Marking
Agency	UL Recognized
Approval(s)/Compliance:	
Size:	1.500" W x 0.500" H (38.100 mm W x 12.700 mm H)
Printable Area:	1.500" W x 0.500" H (38.100 mm W x 12.700 mm H)
Max Characters Per Line For Font #2:	11
Max Lines of Text For Font #2:	16
Label Type/Style:	Label
Color:	White
Wire Gauge:	10 to 4
Finish:	Semi-Gloss
Qty Per Row:	1
Material Type:	Vinyl Cloth
Material Description:	Repositionable Vinyl Cloth
Brady Material #:	B-498
Safety Catalog:	pg. 117
General ID Catalog:	pg. 41
Recommended Ribbon Series:	R6210
Suggested Ribbon Part#:	R6210
Acceptable Ribbon Series:	R4310
After Process:	Yes, this material will work with this application
Environment:	Freezer
Printer Compatibility:	BMP71, TLS 2200, TLS-PC Link
Surface:	Smooth, Textured/Rough
Surface Mount Technology:	No, this material does not work with this application
Through Hole Technology:	Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No
Special Properties:	Repositionable
RoHS Compatibility:	Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.
QTY/UOM:	500/Roll