

TLS 2200®/TLS PC Link™ Tags - # PTL-12-109

SIZE:	0.750" W x 3.000" H (19.050 mm W x 76.200 mm H)
MATERIAL:	Polyethylene Tag
QTY/UOM:	100/Roll
CATALOG #:	PTL-12-109
PRODUCT #:	18347



OVERVIEW [SPECIFICATIONS](#)

Description for TLS 2200®/TLS PC Link™ Tags

Tags for the TLS 2200® & TLS-PC Link™ Thermal Transfer Portable Printers

Specification Of TLS 2200®/TLS PC Link™ Tags

Application(s): Communications Cables, Non-Adhesive, Panel Identification, Voice/Data Identification, Wire & Cable Marking

Agency Approval(s)/Compliance: Halogen-Free (DIN VDE 0472/parts 815)

Size: 0.750" W x 3.000" H (19.050 mm W x 76.200 mm H)

Printable Area: 0.700" W x 2.050" H (17.780 mm W x 52.070 mm H)

Max Characters Per Line For Font #2: 45

Max Lines of Text For Font #2: 6

Label Type/Style: Tag

Color: White

Finish: Matte

Qty Per Row: 1

Material Type: Polyethylene

Material Description: Polyethylene Tag

Brady Material #: [B-109](#)

General ID Catalog: [pg. 34](#)

Recommended Ribbon Series: R4310

Suggested Ribbon Part#: R4310

Cable Type: Cable Bundles, Power & Ground Cables

Printer Compatibility: BMP71, TLS 2200, TLS-PC Link

Special Properties: Excellent cold-weather performance, Tear resistant

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 100/Roll