


## **ENERGIZER 391**

# **ZEROMERCURY**°

SILVER OXIDE



## **Industry Standard Dimensions**



0.03 (0.001) Minimum Ref. (Applies to top edge of gasket or edge of crimp, whichever is higher.)

DESIGNED FOR USE ON CONTINUOUS LOW DRAIN HIGH PULSE ON DEMAND

### **Specifications**

**Chemical System:** Silver Oxide (Zn/Ag<sub>2</sub>O)

**Designation:** ANSI-1160SO/1170SO, IEC-SR55

Nominal Voltage: 1.55 Volts

Typical Capacity: 60 mAh\* (to 1.2 volts)


Capacity Test: 15K ohm continuous drain at 21°C

Typical Weight: 0.92 grams (0.03 oz.)

**Typical Volume:** 0.22 cubic centimeters (0.013 cubic inch)

Impedance (40 Hz): 5 to 7 ohms


#### **Cross Section**



## **Typical Discharge Characteristics**

Typical Performance at 21°C (70°F)


Schedule: Continuous Typical Drain @1.55V: 0.103 milliamperes Load: 15K ohm




<u>Schedule</u>	<u>Typical Drains</u> at 1.55V	<u>Load</u>	Cutoff 1.2V
	(milliamperes)	(ohm)	(hours)
Continuous	0.103	15K	581

### **Temperature Characteristics**

Typical Performance at Low Discharge Rates





#### **Important Notice**

This datasheet contains typical information specific to products manufactured at the time of its publication.

© Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

Form No. EBC - 4365A-Z Page 1 of 1

<sup>\*</sup> Varies according to the applied load, temperature, and cutoff voltage.