


3W High Power LED



Package Dimensions:



All dimensions are in mm
Tolerance: $\pm 0.25\text{mm}$


Absolute Maximum Ratings at $T_a=25^\circ\text{C}$

Parameter	Rating	Unit
Power Dissipation	2,975	mA
LED Junction Temperature	120	$^\circ\text{C}$
Reverse Voltage	5	V
D.C. Forward Current	700	mA
Pulsed Forward Current ($t_p \leq 100\mu\text{s}$, Duty Cycle = 0.005×1)	1400	mA
Operating Temperature Range	-40 to +75	$^\circ\text{C}$
Storage Temperature Range	-40 to +100	$^\circ\text{C}$
Soldering Temperature	Reflow Soldering : 260°C for 10sec Hand Soldering: 350°C for 3sec.	
Electric Static Discharge (HBM)	6,000	V

3W High Power LED



Duty Cycle:



- Proper current derating must be observed to maintain junction temperature below the maximum.
- All products no sensitive to ESD damage (6000 Volts by HBM condition)
- Be careful with a powered up current limited power supply, because of current spikes during power up and/or connection. Best practice is to connect the LED then turn up the voltage gradually. People building their own power supplies should design for minimum current spikes during power up and connection.
- For best results the customer needs to provide proper control of the thermal path, protect against electrical overstress conditions and ensure they are properly attached to the heat sink.
- It is strongly recommended that the temperature of lead does not exceed 55°C.
- It is strongly recommended to apply an electrically isolated heat conducting film between the slug and contact surfaces

Electrical & Optical Characteristics

Parameter	Symbol	Condition	Values			Unit
			Min.	Typ.	Max.	
Luminous Flux	FULL	IF=700mA		170		lm
	Rank T1		72		83	
	Rank T2		83		96	
	Rank U1		96		113	
	Rank U2		113		134	
	Rank V1		134		161	
	Rank V2		161		195	
Forward Voltage	Rank V01	IF=700mA	2.7		3	V
	Rank V02		3		3.5	
	Rank V03		3.25		3.75	
	Rank V04		2.75		4	
	Rank V05		4		4.25	
Correlated Colour Temperature	CCT	IF=700mA	5,250		6,000	
CIE Chromaticity Coordinates: X Axis	X	IF=700mA		0.3287		
CIE Chromaticity Coordinates: Y Axis	Y	IF=700mA		0.3417		
Reverse Current	IR	IF=700mA			50	µA
Viewing Angle at 50% IV	2 θ ½	IF=700mA		120		deg
Thermal resistance Junction to Case	Rθ J-C	IF=700mA		15		°C/W

Notes: 1. The data is tested by an IS tester.
2. Customer's special requirements are also welcome.



3W High Power LED



Typical Electrical & Optical Characteristics Curves:

(25°C Ambient temperature unless otherwise noted)







Fig.1 WHITE LED Spectrum VS. WAVELENGTH




Forward Current VS. Applied Voltage



Forward Current VS. Luminous Flux



Ambient Temperature VS. Forward Current



Radiation Diagram



3W High Power LED



Chromaticity Coordinates Specifications for Bin Grading:


Colour Ranks (IF=350mA. Ta=25°C)

Bin	Rank					Bin	Rank				
WB6	X	0.3327	0.3394	0.3390	0.3324	WB7	X	0.3324	0.3390	0.3385	0.3324
	Y	0.3650	0.3719	0.3591	0.3519		Y	0.3519	0.3591	0.3465	0.3388
WC6	X	0.3264	0.3327	0.3324	0.3268	WC7	X	0.3268	0.3324	0.3324	0.3272
	Y	0.3551	0.3650	0.3519	0.3430		Y	0.3430	0.3519	0.3388	0.3305
WD6	X	0.3210	0.3264	0.3268	0.3218	WD7	X	0.3218	0.3268	0.3272	0.3227
	Y	0.3468	0.3551	0.3430	0.3353		Y	0.3353	0.3430	0.3305	0.3233

Note: X. Y

Tolerance each Bin limit is ± 0.01

Chromaticity Coordinates & Bin Grading Diagram:



3W High Power LED



Recommended Storage Environment:

- Temperature: 5°C ~ 30°C (41°F ~ 86°F)
- Humidity: 60% RH Max.
- Use within 7 days after opening of sealed vapour/ESD barrier bags.
- If moisture absorbent material (silica gel) has faded away or LEDs have exceeded the storage time, baking treatment should be performed using the following conditions:
- Baking Treatment: 60 ± 5°C for 24 hours
- Fold the opened bag firmly and keep in dry environment.


Soldering

Reflow Soldering			
	Lead Solder	Lead-free Solder	
Pre-heat	120 ~ 150°C	180 ~ 200°C	Temperature
Pre-heat Time	120sec. max.	120sec. max.	Soldering time
Peak Temperature	240°C max.	260°C max.	
Soldering Time	10sec. max.	10sec. max.	
Condition	Refer to temperature-profile 1	Refer to temperature-profile 2	
			350°C max.
			3sec max. (one time only)

*After reflow soldering rapid cooling should be avoided.


Temperature-profile (surface of circuit board):

Use the conditions shown under figure.



Recommended Soldering Pad Design:

Use the following conditions shown in figure.



Part Number Table

LED Chip		Lens Colour	Part Number
Material	Emitting Colour		
InGaN / Metal Alloy	White	Water clear	703-1048

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

