


1" Single Digit Display




Package Dimensions:



All dimensions are in mm
 Tolerance: $\pm 0.25\text{mm}$
 The slope angle of any PIN may be $\pm 5^\circ$ max

Internal Circuit Diagram:



Absolute Maximum Ratings at $T_a=25^\circ\text{C}$

Parameter	Symbol	Rating	Unit	
Power Dissipation - Pre Segment	P_D	DP	78	mW
		Seg	156	
Pulse Current (1/10 Duty Cycle, 0.1ms Pulse Width)	I_{FP}	100	mA	
Forward Current - Per Chip	I_F	30	mA	
Reverse (Leakage) Current - Per Chip	I_r	100	μA	
Reverse Voltage - Per Chip	V_R	5	V	
Operating Temperature Range	$T_{opr.}$	-25 to +85	$^\circ\text{C}$	
Storage Temperature Range	$T_{stg.}$	-40 to +100	$^\circ\text{C}$	
Soldering Temperature	$T_{sol.}$	Dip Soldering: 260°C for 5sec. Hand Soldering: 350°C for 3 sec.		



1" Single Digit Display



Electrical & Optical Characteristics:

Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
Luminous Intensity - Per Segment	I_v	$I_f=10\text{mA} / \text{seg}$	3.7	8.5		mcd
Forward Voltage	V_f	DP		2.1	2.6	V
		Seg		4.2		
Peak Wavelength	λ_p	$I_f=20\text{mA} / \text{seg}$		635		nm
Dominant Wavelength	λ_d	$I_f=20\text{mA} / \text{seg}$		626		nm
Reverse Current - Per Chip (Leakage Current - Per Chip)	I_r	$V_r=5\text{V}$			100	μA
Spectrum Line Halfwidth	$\Delta\lambda$	$I_f=20\text{mA} / \text{seg}$		35		deg
Response Time	T			250		nm

Note: Customer's special requirements are also welcome.

Typical Electrical & Optical Characteristics Curves:

(25°C Ambient temperature unless otherwise noted)




Fig.1 RELATIVE INTENSITY VS. WAVELENGTH




Fig.2 MAXIMUM TOLERABLE PEAK CURRENT VS. PULSE DURATION




Fig.3 FORWARD CURRENT VS. FORWARD VOLTAGE PER CHIP




Fig.4 FORWARD CURRENT VS. DERATING CURVE



1" Single Digit Display




Fig.5 RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT




Fig.6 LUMINOUS INTENSITY VS. AMBIENT TEMPERATURE

Part Number Table

LED Chip		Face Colour		Part Number
Material	Emitting Colour	Surface	Segments	
GaAsP / Gap	Orange	Grey	White	703-0174
GaAsP / Gap	Orange	Grey	White	703-0175

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

