



Emerg.stop/swit.off,60mm,illum.,rot.rel.



Powering Business Worldwide™

Part no. **M22-PVLT60P**  
Article no. **121461**

### Delivery programme

Product range			RMQ-Titan (drilling dimensions 22.5 mm)
Basic function			Emergency stop pushbutton/ emergency-stop button
Construction type			Palm-tree shape
Diameter		mm	60
Colour			
Mushroom head			Red
RAL Value			RAL 3000
Function			pull or rotate released
Illumination			Illuminated with LED element
Front ring			without front ring
Connection to SmartWire-DT			no
<b>Instructions</b>			Release by turning
<b>Notes</b>			
Release by turning or pulling			
Palm-tree shape, diameter 60 mm			

### Approvals

NA Certification

Request filed for UL and CSA

### General

Standards			IEC/EN 60947 VDE 0660
Lifespan, mechanical	Operations	x 10 <sup>6</sup>	> 0.1
Operating frequency	Operations/ h		600
Actuating force		n	50
Protection type			IP67, IP69K
Climatic proofing			Damp heat, constant to IEC 60068-2-78 Damp heat, cyclic to IEC 60068-2-30
Ambient temperature		°C	
Open		°C	- 25 - + 70
Mounting position			As required
Mechanical shock resistance		g	50 Shock duration 11 ms Sinusoidal according to IEC 60068-2-27

### Technical data ETIM 4.0

With bezel			No
Unlocking method			Turn unlatching mechanism
Lens design			Round
Suitable for illumination			No
Hole diameter		mm	22
Suitable for emergency switching off			YES
Color button			red

Width of opening	mm	22
Height meter opening	mm	6
Protection type (IP)		IP67
Material front ring		-
Diameter cap	mm	60
Momentary		No
Switching function latching		YES
Design of button		flush

## Dimensions





