

This document was generated on 06/27/2012 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	<u>43650-0323</u>		
Status: Overview: Description:	Active <u>Micro-Fit 3.0[™] Connectors</u> 3.00mm Pitch Micro-Fit 3.0 [™] Header, Surface Mount Compatible, Single Row, Vertical, with Press-fit Metal Retention Clip, 3 Circuits, 0.76µm Gold (Au) Selective Plating, Glow Wire Compatible		
Documents: <u>3D Model</u> Drawing (PDF) Product Specification	<u>PS-43650 (PDF)</u>	Test Summary TS-43045-002 (PDF) RoHS Certificate of Compliance (PDF) Product Literature (PDF)	Series image - Reference only
Agency Certifica CSA TUV UL General Product Family Series Application Comments	tion	LR19980 R72081037 E29179 PCB Headers <u>43650</u> Power, Wire-to-Board "High Temperature Square Pin Solder Type <p><p>This Molex product is manufactured from material that has</p></p>	EU RoHS ELV and RoHS Compliant REACH SVHC Contains SVHC: No Low-Halogen Status Not Reviewed Need more information on product environmental compliance?
Overview Product Literature Or	dor No	Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13 b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <p><p> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <p> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options." <u>Micro-Fit 3.0TM Connectors</u> 087650-5084</p></p></p>	Email productcompliance@molex.com For a multiple part number RoHS Certificate of Compliance, click here Please visit the Contact Us section for any non-product compliance questions. Search Parts in this Series 43650Series Mates With 43645 Micro-Fit 3.0™ Receptacle Housing
Product Literature Or Product Name	der No	987650-5984 Micro-Fit 3.0™	
PhysicalBreakawayCircuits (Loaded)Circuits (maximum)Color - ResinDurability (mating cycFlammabilityGlow-Wire CompliantMated HeightMaterial - MetalMaterial - Plating MatMaterial - Plating Terr	ing	No 3 3 Black 30 94V-0 Yes 17.27mm Brass Gold, Tin Tin	

Material - Resin		High Temperature Thermoplastic	
Number of Rows		1	
Orientation		Vertical	
PCB Locator		Yes	
PCB Retention		Yes	
PCB Thickness - Recommended		1.60mm	
Packaging Type		Embossed Tape on Reel	
Pitch - Mating Interface		3.00mm	
Plating min - Mating		0.762µm	
Plating min - Termination		2.540µm	
Polarized to PCB		Yes	
Shrouded		Fully	
Stackable		No	
Temperature Range - Opera	ting	-40°C to +105°C	
Termination Interface: Style	-	Surface Mount	
Electrical			
Current - Maximum per Cont	act	5A	
Voltage - Maximum		250V	
Ū.		2001	
Solder Process Data			
Duration at Max. Process Te		30	
Lead-free Process Capability		Reflow Capable (SMT only)	
Max. Cycles at Max. Process		3	
Process Temperature max. (2	260	
Material Info			
UPC		800754778282	
Reference - Drawing N	umbers		
Product Specification		PS-43650	
Sales Drawing		SD-43650-008	
Test Summary		TS-43045-002	

This document was generated on 06/27/2012 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION