

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

22-12-4052

Status:

Active

Overview:

KK® Interconnection System

Description:

2.54mm Pitch KK® Wire-to-Board Header, Right Angle, with Friction Lock, 5 Circuits



image - Reference only

Series

Documents:

3D Model

Product Specification PS-99020-0088 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

7395

Application

Signal, Wire-to-Board

Overview

KK® Interconnection System

Product Name

KK®

Physical

Breakaway

No

Circuits (Loaded)

5

Circuits (maximum)

5

Color - Resin

Natural (White)

Durability (mating cycles max)

100

First Mate / Last Break

No

Flammability

94V-0

Glow-Wire Compliant

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Metal

Brass

Material - Plating Mating

Gold

Material - Plating Termination

Gold

Material - Resin

Nylon

Number of Rows

1

Orientation

Right Angle

PC Tail Length

3.80mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

2.54mm

Plating min - Mating

0.508µm

Plating min - Termination

0.508µm

Polarized to PCB

Yes

Shrouded

Partial

Stackable

No

Temperature Range - Operating

0°C to +75°C

Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact

4A

Voltage - Maximum

250V

Solder Process Data

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

7395Series

Mates With

2695 KK® Crimp Terminal Housing, 6471 KK® Crimp Terminal Housing, 7720 KK® IDT Double Cantilever

Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	235

Material Info

Old Part Number	739505BG
-----------------	----------

Reference - Drawing Numbers

Product Specification	PS-99020-0088
Sales Drawing	SD-7395-001

This document was generated on 06/01/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION